Product datasheet

Specifications





TeSys K control relay - 3 NO + 1 NC - <= 690 V - 230...240 V AC coil

CA2KN31U72

() Discontinued on: 10 Oct 2020

① Discontinued

EAN Code: 3389110482485

Main

RangeTeSysProduct NameTeSys CAKProduct Or Component TypeControl relayDevice Short NameCA2KContactor ApplicationControl circuitUtilisation CategoryDC-13 AC-15Pole Contact Composition3 NO + 1 NC[Ue] Rated Operational Voltage<= 690 V <= 400 Hz		
Product Or Component Type Control relay Device Short Name CA2K Contactor Application Control circuit Utilisation Category DC-13 AC-15 Pole Contact Composition 3 NO + 1 NC [Ue] Rated Operational Voltage <= 690 V <= 400 Hz Control Circuit Type AC at 50/60 Hz	Range	TeSys
Device Short Name CA2K Contactor Application Control circuit Utilisation Category DC-13 AC-15 Pole Contact Composition 3 NO + 1 NC [Ue] Rated Operational Voltage <= 690 V <= 400 Hz Control Circuit Type AC at 50/60 Hz	Product Name	TeSys CAK
Contactor Application Control circuit Utilisation Category DC-13 AC-15 Pole Contact Composition 3 NO + 1 NC [Ue] Rated Operational Voltage <= 690 V <= 400 Hz	Product Or Component Type	Control relay
Utilisation Category DC-13 AC-15 Pole Contact Composition 3 NO + 1 NC [Ue] Rated Operational Voltage <= 690 V <= 400 Hz	Device Short Name	CA2K
AC-15 Pole Contact Composition 3 NO + 1 NC [Ue] Rated Operational Voltage <= 690 V <= 400 Hz	Contactor Application	Control circuit
[Ue] Rated Operational Voltage <= 690 V <= 400 Hz	Utilisation Category	
Control Circuit Type AC at 50/60 Hz	Pole Contact Composition	3 NO + 1 NC
	Je] Rated Operational Voltage <= 690 V <= 400 Hz	
[Uc] Control Circuit Voltage 230240 V AC 50/60 Hz	Control Circuit Type	AC at 50/60 Hz
	[Uc] Control Circuit Voltage	230240 V AC 50/60 Hz

Complementary

Coil Technology	Built-in bidirectional peak limiting diode suppressor
[Ith] Conventional Free Air Thermal Current	10 A (at 50 °C)
Irms Rated Making Capacity	110 A conforming to IEC 60947
Associated Fuse Rating	10 A gG conforming to IEC 60947 10 A gG conforming to VDE 0660
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947 750 V conforming to VDE 0110 group C 690 V conforming to BS 5424 600 V conforming to CSA C22.2 No 14
Mounting Support	Plate Rail
Connections - Terminals	Screw clamp terminals 1 cable(s) 1.54 mm ² solid Screw clamp terminals 2 cable(s) 1.54 mm ³ solid Screw clamp terminals 1 cable(s) 0.754 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 0.754 mm ² flexible without cable end Screw clamp terminals 1 cable(s) 0.341.5 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 0.341.5 mm ² flexible without cable end
Tightening Torque	1.3 N.m - on screw clamp terminals - with screwdriver flat \emptyset 6 mm 1.3 N.m - on screw clamp terminals - with screwdriver Philips No 26 mm
Control Circuit Voltage Limits	Drop-out: 0.20.75 Uc (at <50 °C) Operational: 0.81.15 Uc (at <50 °C)
Operating Time	1020 ms coil de-energisation and NO opening 1020 ms coil energisation and NO closing 1525 ms coil de-energisation and NC closing 515 ms coil energisation and NC opening

Mechanical Durability	10 Mcycles
Maximum Operating Rate	10000 cyc/h
Immunity To Microbreaks	2 ms
Inrush Power In Va	30 VA (at 20 °C)
Hold-In Power Consumption In Va	4.5 VA (at 20 °C)
Heat Dissipation	1.3 W
Minimum Switching Voltage	17 V
Minimum Switching Current	5 mA
Non Overlap Distance	0.5 mm
Insulation Resistance	> 10 MOhm
Height	58 mm
Width	45 mm
Depth	57 mm
Net Weight	0.18 kg

Environment

Standards	EN/IEC 60947-4-1 GB/T 14048.4 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1
Product Certifications	CB Scheme CCC UL CSA EAC CE UKCA
Ip Degree Of Protection	IP2X
Protective Treatment	TC conforming to IEC 60068
Ambient Air Temperature For Operation	-2550 °C
Ambient Air Temperature For Storage	-5080 °C
Operating Altitude	2000 m without derating
Flame Retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102
Mechanical Robustness	Vibrations contactor open: 2 Gn, 5300 Hz conforming to IEC 60068-2-6 Vibrations contactor closed: 4 Gn, 5300 Hz conforming to IEC 60068-2-6 Shocks contactor open: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed: 15 Gn for 11 ms conforming to IEC 60068-2-27

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	6.2 cm
Package 1 Length	4.8 cm
Package 1 Weight	182 g

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information