# **Product datasheet**

Specifications





# TeSys SK control relay - 1 NO + 1 NC - <= 690 V - 230 V AC coil

Local distributor code: 388804478

CA2SK11P7

EAN Code: 3389110564105

#### Main

Range	TeSys
Product Name	TeSys CASK
Product Or Component Type	Control relay
Device Short Name	CA2SK
Contactor Application	Control circuit
Utilisation Category	DC-13 AC-15
Pole Contact Composition	1 NO + 1 NC
[Ue] Rated Operational Voltage	<= 690 V <= 400 Hz
Control Circuit Type	AC at 50/60 Hz
[Uc] Control Circuit Voltage	230 V AC 50/60 Hz

### Complementary

<u> </u>	
[Ith] Conventional Free Air Thermal Current	10 A (at 55 °C)
Associated Fuse Rating	10 A gL conforming to VDE 0660
	10 A gL conforming to IEC 60947
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947
	690 V conforming to VDE 0110 group C
	690 V conforming to BS 5424
	690 V conforming to UL 508
	690 V conforming to CSA C22.2 No 14
Mounting Support	Plate
	Rail
Connections - Terminals	Screw clamp terminals 1 cable(s) 1.56 mm <sup>2</sup> solid
	Screw clamp terminals 2 cable(s) 1.54 mm <sup>2</sup> solid
	Screw clamp terminals 1 cable(s) 0.56 mm <sup>2</sup> flexible without cable end
	Screw clamp terminals 1 cable(s) 0.356 mm <sup>2</sup> flexible with cable end
	Screw clamp terminals 2 cable(s) 0.351.5 mm <sup>2</sup> flexible with cable end
	Screw clamp terminals 2 cable(s) 0.352.5 mm <sup>2</sup> flexible without cable end
Tightening Torque	0.8 N.m - on screw clamp terminals pozidriv No 1 screw head
Control Circuit Voltage Limits	Drop-out: 0.20.75 Uc (at <50 °C)
-	Operational: 0.851.1 Uc (at <50 °C)
Operating Time	68 ms coil de-energisation and NO opening
	714 ms coil energisation and NO closing
	810 ms coil de-energisation and NC closing
	816 ms coil energisation and NC opening
Mechanical Durability	10 Mcycles
Maximum Operating Rate	1200 cyc/h
Inrush Power In Va	16 VA (at 20 °C)

Hold-In Power Consumption In Va	4.2 VA (at 20 °C)
Heat Dissipation	1.4 W
Height	56 mm
Width	27 mm
Depth	55.5 mm
Net Weight	0.132 kg

### Environment

Standards	EN/IEC 60947-5-1 UL 60947-5-1 CSA C22.2 No 60947-5-1
Product Certifications	CB Scheme cULus EAC CE UKCA
Ip Degree Of Protection	IP2X
Protective Treatment	TC conforming to IEC 60068
Ambient Air Temperature For Operation	-2050 °C
Ambient Air Temperature For Storage	-5070 °C
Operating Altitude	2000 m without derating

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.500 cm
Package 1 Width	6.000 cm
Package 1 Length	6.500 cm
Package 1 Weight	123.500 g
Unit Type Of Package 2	S01
Number Of Units In Package 2	40
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.074 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	1280
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	170.368 kg

### **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information