Product datasheet

Specification





power supply module X80 - 24..48 V DC - 31.2 W

Local distributor code:

389737243 BMXCPS3020

EAN Code: 3595863908985

Main

Range Of Product	Modicon X80	
Product Or Component Type	Power supply module	
Backplane Compatibility	Not compatible with BMEXBP02	
Primary Voltage	2448 V isolated	
Supply Circuit Type	DC	
Secondary Power	15 W 3.3 V DC I/O module logic power supply	

Complementary

Primary Voltage Limit	1862.4 V
Input Current	0.83 A 48 V 1.65 A 24 V
Inrush Current	30 A 24 V 60 A 48 V
I ² T On Activation	1 A ² .s 24 V 3 A ² .s 48 V
It On Activation	0.2 A.s 24 V 0.3 A.s 48 V
Mtbf Reliability	4600000 H
Protection Type	Internal fuse not accessible for primary circuit Overload protection for secondary circuit, 24 V sensor power supply Overvoltage protection for secondary circuit, 24 V sensor power supply Short-circuit protection for secondary circuit, 24 V sensor power supply
Current At Secondary Voltage	1.3 A 24 V DC I/O module power supply and processor 4.5 A 3.3 V DC I/O module logic power supply
Maximum Power Dissipation In W	8.5 W
Status Led	1 LED (green) rack voltage OK
Control Type	RESET push-button cold restart
Electrical Connection	1 connector 2 pin(s)alarm relay 1 connector 5 pin(s)line supply, protective earth
Maximum Cable Distance Between Devices	10 m power supply cable copper 1.5 mm² 15 m power supply cable copper 2.5 mm²
Insulation Resistance	>= 10 MOhm primary/ground >= 10 MOhm primary/secondary
Net Weight	0.34 kg

Environment

Immunity To Microbreaks	1 ms
Dielectric Strength	1500 V primary/ground 1500 V primary/secondary
Vibration Resistance	3 gn
Shock Resistance	30 gn
Ip Degree Of Protection	IP20
Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility
Ambient Air Temperature For Storage	-4085 °C
Ambient Air Temperature For Operation	060 °C
Relative Humidity	595 % at 55 °C without condensation
Protective Treatment	TC
Operating Altitude	02000 m 20005000 m with derating factor

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.183 cm
Package 1 Width	15.437 cm
Package 1 Length	15.654 cm
Package 1 Weight	500.0 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	12
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	7.22 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	48
Package 3 Height	75 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	40 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

BMXCPS3020

Dimensions Drawings

Modules Mounted on Racks

Dimensions




- (1) With removable terminal block (cage, screw or spring).
- (2) With FCN connector.
- (3) On AM1 ED rail: 35 mm wide, 15 mm deep. Only possible with BMXXBP0400/0400H/0600/0600H/0800/0800H rack.

Rack references	a in mm	a in in.
BMXXBP0400 and BMXXBP0400H	242.4	09.54
BMXXBP0600 and BMXXBP0600H	307.6	12.11
BMXXBP0800 and BMXXBP0800H	372.8	14.68
BMXXBP1200 and BMXXBP1200H	503.2	19.81

Connections and Schema


Connection of Direct Current Power Supply Modules to a 24 Vdc or 48 Vdc Floating Direct Current Network



24 VDC floating network for the power supply of sensors, actuators and input/out modules.

Connection of Direct Current Power Supply Modules to an Alternating Current Network

Connection of a Single Rack PLC Station




Q General isolator

KM Line contactor or circuit breaker

(1) Insulation connector bar for locating grounding errors

Connection of a Multi-Rack PLC Station

BMXCPS3020



Q General isolator

KM Line contactor or circuit breaker

(1) Insulation connector bar for locating grounding errors