Product datasheet

Specifications





TeSys K control relay - 4 NO - <= 690 V - 110 V AC coil

Local distributor code: 21098583

CA2KN40F7

EAN Code: 3389110428391

Main

Range	TeSys	
Product Name	TeSys CAK	
Product Or Component Type	Control relay	
Device Short Name	CA2K	
Contactor Application	Control circuit	
Utilisation Category	DC-13 AC-15	
Pole Contact Composition	4 NO	
[Ue] Rated Operational Voltage	tional Voltage <= 690 V <= 400 Hz	
Control Circuit Type	Circuit Type AC at 50/60 Hz	
[Uc] Control Circuit Voltage	110 V AC 50/60 Hz	

Complementary

10 A (at 50 °C)
110 A conforming to IEC 60947
10 A gG conforming to IEC 60947 10 A gG conforming to VDE 0660
690 V conforming to IEC 60947 750 V conforming to VDE 0110 group C 690 V conforming to BS 5424 600 V conforming to CSA C22.2 No 14
Rail Plate
Screw clamp terminals 1 cable(s) 1.54 mm ² solid Screw clamp terminals 2 cable(s) 1.54 mm ² solid Screw clamp terminals 1 cable(s) 0.754 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 0.754 mm ² flexible without cable end Screw clamp terminals 1 cable(s) 0.341.5 mm ² flexible with cable end Screw clamp terminals 2 cable(s) 0.341.5 mm ² flexible without cable end
 1.3 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm 1.3 N.m - on screw clamp terminals - with screwdriver Philips No 26 mm 1.3 N.m - on screw clamp terminals - with screwdriver pozidriv No 2
Drop-out: 0.20.75 Uc (at <50 °C) Operational: 0.81.15 Uc (at <50 °C)
1020 ms coil de-energisation and NO opening 1020 ms coil energisation and NO closing
10 Mcycles
10000 cyc/h

Immunity To Microbreaks	2 ms
Inrush Power In Va	30 VA (at 20 °C)
Hold-In Power Consumption In Va	4.5 VA (at 20 °C)
Heat Dissipation	1.3 W
Minimum Switching Voltage	17 V
Minimum Switching Current	5 mA 0.5 mm > 10 MOhm
Non Overlap Distance	
Insulation Resistance	
Height	58 mm
Width	45 mm
Depth	57 mm
Net Weight	0.18 kg

Environment

Standards	EN/IEC 60947-4-1 GB/T 14048.4 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1	
Product Certifications	CB Scheme CCC UL CSA EAC CE UKCA	
Ip Degree Of Protection	IP2X	
Protective Treatment	TC conforming to IEC 60068	
Ambient Air Temperature For Operation	-2550 °C	
Ambient Air Temperature For Storage	-5080 °C	
Operating Altitude	2000 m without derating	
Flame Retardance	Retardance V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102	
Mechanical Robustness	Vibrations contactor open: 2 Gn, 5300 Hz conforming to IEC 60068-2-6 Vibrations contactor closed: 4 Gn, 5300 Hz conforming to IEC 60068-2-6 Shocks contactor open: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed: 15 Gn for 11 ms conforming to IEC 60068-2-27	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.8 cm
Package 1 Width	6.3 cm
Package 1 Length	6.6 cm
Package 1 Weight	179.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	50

Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	9.271 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information