# **Product datasheet**

Specifications





## TeSys K control relay - 3 NO + 1 NC - <= 690 V - 24 V DC standard

coil

Local distributor code: 386284139

CA3KN315BD

EAN Code: 3389110484410

#### Main

Range	TeSys
Product Name	TeSys CAK
Product Or Component Type	Control relay
Device Short Name	САЗК
Contactor Application	Control circuit
Utilisation Category	AC-15 DC-13
Pole Contact Composition	3 NO + 1 NC
[Ue] Rated Operational Voltage	<= 690 V <= 400 Hz
Control Circuit Type	DC standard
[Uc] Control Circuit Voltage	24 V DC

#### Complementary

[Ith] Conventional Free Air Thermal Current	10 A (at 50 °C)
Irms Rated Making Capacity	110 A conforming to IEC 60947
Associated Fuse Rating	10 A gG conforming to IEC 60947 10 A gG conforming to VDE 0660
[Ui] Rated Insulation Voltage	690 V conforming to IEC 60947 750 V conforming to VDE 0110 group C 690 V conforming to BS 5424 600 V conforming to CSA C22.2 No 14
Mounting Support	Plate Rail
Connections - Terminals	Solder pins - busbar cross section: 1.5 x 0.9 mm
Control Circuit Voltage Limits	Operational: 0.81.15 Uc (at <50 °C) Drop-out: 0.10.75 Uc (at <50 °C)
Operating Time	10 ms coil de-energisation and NO opening 3040 ms coil energisation and NO closing 15 ms coil de-energisation and NC closing 2535 ms coil energisation and NC opening
Mechanical Durability	20 Mcycles
Maximum Operating Rate	10000 cyc/h
Immunity To Microbreaks	2 ms
Inrush Power In W	3 W (at 20 °C)
Hold-In Power Consumption In W	3 W at 20 °C
Heat Dissipation	3 W

Minimum Switching Voltage	17 V
Minimum Switching Current	5 mA
Non Overlap Distance	0.5 mm
Insulation Resistance	> 10 MOhm
Height	58 mm
Width	45 mm
Depth	57 mm
Net Weight	0.255 kg

### Environment

Standards	EN/IEC 60947-4-1 GB/T 14048.4 UL 60947-4-1 CSA C22.2 No 60947-4-1
	JIS C8201-4-1
Product Certifications	CB Scheme
	CCC
	UL
	CSA
	EAC
	CE
	UKCA
Ip Degree Of Protection	IP2X
Protective Treatment	TC conforming to IEC 60068
Ambient Air Temperature For Operation	-2550 °C
Ambient Air Temperature For Storage	-5080 °C
Operating Altitude	2000 m without derating
Flame Retardance	V1 conforming to UL 94
	Requirement 2 conforming to NF F 16-101
	Requirement 2 conforming to NF F 16-102
Mechanical Robustness	Vibrations contactor open: 2 Gn, 5300 Hz conforming to IEC 60068-2-6 Vibrations contactor closed: 4 Gn, 5300 Hz conforming to IEC 60068-2-6
	Shocks contactor open: 10 Gn for 11 ms conforming to IEC 60068-2-27
	Shocks contactor closed: 15 Gn for 11 ms conforming to IEC 60068-2-27

#### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	6.0 cm
Package 1 Length	4.8 cm
Package 1 Weight	252.0 g

#### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information