Product datasheet

Specifications





Shaft extension, TeSys GS, length 400mm, cross section 12 x 12 mm, for switches 600-1250 A

Local distributor code:
393394753 GS2AE51

EAN Code: 3389119412070

Main

••••		
Range	TeSys	
Device Short Name	GS2AE	
Product Or Component Type	Shaft extension	
Accessory / Separate Part Category	Control accessory	
Range Compatibility	TeSys TeSys GS GS2S TeSys TeSys GS GS2T TeSys TeSys GS GS2V FuPact FuPacT GS GSB630 FuPact FuPacT GS GSD630 FuPact FuPacT GS GSB800 FuPact FuPacT GS GSD800 FuPact FuPacT GS GSB800 FuPact FuPacT GS GSB1250 FuPact FuPacT GS GSD1250	
Switch Rated Current	600 A 630 A 800 A 1250 A	

Complementary

Length	400 mm
Shaft Cross Section	12 x 12 mm
Net Weight	0.42 kg

Packing Units

17 May 2024

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.200 cm
Package 1 Width	2.100 cm
Package 1 Length	40.000 cm
Package 1 Weight	448.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	28
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	13.118 kg

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information