Product datasheet

Specifications





External rotary handle, TeSys GS, black handle, right side mounting, 2 positions I-O, IP65, for GS 32-63A IEC

Local distributor code: 393394973

GS2AH210

EAN Code: 3389119411691

Main

Range Of Product	TeSys	
Range	TeSys	
Device Short Name	GS2AH	
Product Or Component Type	Rotary handle	
Range Compatibility	TeSys TeSys GS GS1D TeSys TeSys GS GS2F TeSys TeSys GS GS2G FuPact FuPacT GS GSB32 FuPact FuPacT GS GSC50	
Type Of Operating Handle	External right side	
Handle Colour	our Black	
landle Front Plate Colour Grey		

Complementary

Handle Positions	O-I Lockable in O position	
Rotary Handle Padlocking		
Switch Rated Current	32 A	
	50 A	
	63 A	
Standards	IEC	
Net Weight	0.2 kg	

Environment

Ip Degree Of Protection IP65

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	16 cm
Package 1 Length	15 cm
Package 1 Weight	181 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	25

Package 2 Height	30 cm	
Package 2 Width	30 cm	
Package 2 Length	40 cm	
Package 2 Weight	5.053 kg	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information