
Product datasheet

Specifications





TeSys GV2 & GV3 - auxiliary contact - 1 NO + 1 NC

Local distributor code: 381798332

GVAE113

EAN Code: 3389110346633

Main

Range	TeSys TeSys Deca
Device Short Name	GVAE
Product Or Component Type	Auxiliary contact block
Product Compatibility	GV2L GV2ME GV3L GV2RT GV2P GV3P GV2LE LS1D323
Mounting Location	Front side
Pole Contact Composition	1 NO + 1 NC
Quantity Per Set	Set of 10

Complementary

[Ui] Rated Insulation Voltage	300 V conforming to UL 508 300 V conforming to CSA C22.2 No 14 250 V conforming to IEC 60947-1
[Ue] Rated Operational Voltage	24240 V AC 2460 V DC
[Ith] Conventional Free Air Thermal Current	2.5 A
Mechanical Durability	100000 cycles
Minimum Switching Current	5 mA
Minimum Switching Voltage	17 V
Protection Type	GG fuse 10 A GB2CB06 circuit breaker 10 A
Rated Operational Power In Va	120 VA at 110120 V AC-15 - electrical durability: 100000 cycles 120 VA at 230240 V AC-15 - electrical durability: 100000 cycles 48 VA at 24 V AC-15 - electrical durability: 100000 cycles 60 VA at 48 V AC-15 - electrical durability: 100000 cycles
Rated Operational Power In W	15 W at 48 V DC-13 - electrical durability: 100000 cycles 24 W at 24 V DC-13 - electrical durability: 100000 cycles 9 W at 60 V DC-13 - electrical durability: 100000 cycles
Height	13 mm
Width	44.5 mm
Depth	31.5 mm
Net Weight	0.05 kg

Colour	Dark grey
Environment	
Environmental Characteristic	Normal environment
Product Certifications	UKCA
Packing Units	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.2 cm
Package 1 Width	12.1 cm
Package 1 Length	7.3 cm
Package 1 Weight	17.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	6.2 cm
Package 2 Width	12.1 cm
Package 2 Length	7.3 cm
Package 2 Weight	180.0 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	220
Package 3 Height	15.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	4.269 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information