Product datasheet

Specification





Blown fuse signalling contact, TeSys GS, 1st C/O, for GS1 GS2 3 poles 250-400 A, DIN fuse size 1-2

Local distributor code: 402716895

GS1AF43

EAN Code: 3389110563344

Main

TeSys	
GS1AF	
Auxiliary contact	
Blown fuse signalling	
1 C/O	
Instantaneous	
16 A (at 40 °C)	
12 A at 24 V DC-13 2 A at 48 V DC-13 3 A at 400 V AC-15 4 A at 230 V AC-15 0.4 A at 220 V DC-13 0.6 A at 110 V DC-13	

Complementary

Range Compatibility	TeSys TeSys GS fuse-switch disconnector	
Mechanical Durability	30000 cycles	
Electrical Durability	30000 cycles AC-15	
Product Compatibility	GS	
Poles Description	3P	
Switch Rated Current	250 A 400 A	
Fuse Type	DIN NFC	
Fuse Size	2 1	
Net Weight	0.038 kg	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	12.0 cm
Package 1 Length	15.0 cm
Package 1 Weight	38.0 g

Unit Type Of Package 2	S01
Number Of Units In Package 2	20
Package 2 Height	15.0 cm
Package 2 Width	15.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	992.0 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information