Specifications





# 7W Touch Advanced Display WVGA

Local distributor code: 402743033

HMIDT351

EAN Code: 3606480687280

#### Main

Range Of Product	
Range Of Froduct	Harmony GTU
Product Or Component Type	Advanced touchscreen panel
Terminal Type	Touchscreen display
[Us] Rated Supply Voltage	1224 V DC power supply
Supply Voltage Limits	10.828.8 V
Power Consumption In W	6.5 W
Inrush Current	30 A

## Complementary

Touchscreen Resolution	1024 x 1024
Pixel Resolution	800 x 480
Display Size	7 inch
Aspect Ratio	4:3
Display Type	Colour TFT LCD
Display Resolution	800 x 480 pixels WVGA
Display Colour	262144 colors
Backlight Lifespan	50000 hours
Touch Panel	Single touch analogue resistive
Type Of Cooling	Natural convection
Type Of Installation	Indoor installation
Cut-Out Dimensions	190 (+ 1/- 0) x 135 (+ 1/- 0) mm
Width	203.6 mm
Height	148.6 mm
Depth	36 mm
Net Weight	1.2 kg

### Environment

Ip Degree Of Protection	Front panel: IP66 Front panel: IP67
Nema Degree Of Protection	NEMA 4X front panel

Standards	UL 508 ANSI/ISA 12-12-01 Class I division 2 CSA C22.2 No 213 CSA C22.2 No 142 IEC 61132-2	
Product Certifications	CULus RCM CE KC UKCA UKEX	
Ambient Air Temperature For Operation	060 °C conforming to IEC 61131-2	
Ambient Air Temperature For Storage	-2060 °C	
Relative Humidity	1090 % non-condensing	
Operating Altitude	2000 m	
Vibration Resistance	3.5 mm constant amplitude (f = 59 Hz) conforming to IEC 61131-2 9.8 m/s <sup>2</sup> (f = 9150 Hz) conforming to IEC 61131-2	
Shock Resistance	147 m/s <sup>2</sup> conforming to IEC 61131-2	
Electromagnetic Compatibility	Electrostatic discharge immunity test level 3 conforming to IEC 61000-4-2	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.5 cm
Package 1 Width	21 cm
Package 1 Length	26.5 cm
Package 1 Weight	1.6 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	2
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	3.78 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	8
Package 3 Height	33.5 cm
Package 3 Width	45.5 cm
Package 3 Length	55 cm
Package 3 Weight	13.012 kg

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information


#### **Certifications & Standards**

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	End of Life Information	

**Dimensions Drawings** 

#### **External Dimensions**

#### **Display Unit with Box Module**




1 Front

2 Left

3 Bottom

#### Installation with Installation Fasteners and Dimensions with Cables



(A) Rotation area of the fastener

(B) Pitch of the center of installation fastner screws

1 Right

2 Front

3 Left


4 Bottom

**5** Top

Mounting and Clearance

#### Mounting

#### **Panel Cut Dimensions**



Dimensions in mm


А	В	С	R
190 (+1/-0)	135 (+1/-0)	1.65	3 max.

Dimensions in in.

А	В	С	R
7.48 (+0.04/-0)	5.31 (+0.04/-0)	0.060.2	0.12 max.

#### Installation Requirements

#### **Mounting Angle**



When installing this product in a slanted position with an incline more than  $30^{\circ}$ , the ambient temperature must not exceed 40 °C (104 °F). You may need to use forced air cooling (fan, A/C) to ensure the ambient operating temperature is 40 °C or less (104 °F or less).

#### Clearance

