# **Product datasheet**

Specification





# advanced touchscreen panel stainless 640 x 480 pixels VGA-10.4" TFT - 96 MB

Local distributor code: 398059226 HMIGTO5315

EAN Code: 3595864150291

### Main

Range Of Product	Harmony GTO					
Product Or Component Type	Advanced touchscreen panel					
Display Colour	65536 colours					
Display Size	10.4 inch					
Supply	External source					
Operating System	Harmony					
Battery Type	Lithium battery for internal RAM, autonomy: 100 days, charging time = 5 day(s), battery life = 10 year(s)					
Provided Equipment	1 protective cover					

## Complementary

Terminal Type	Touchscreen display					
Display Type	Backlit colour TFT LCD					
Display Resolution	640 x 480 pixels VGA					
Touch Sensitive Zone	1024 x 1024					
Touch Panel	Resistive film, 1000000 cycles					
Backlight Lifespan	50000 hours white at 25 °C					
Brightness	16 levels - control by touch panel 16 levels - control by software					
Character Font	Chinese (simplified Chinese) Japanese (ANK, Kanji) Taiwanese (traditional Chinese) Korean ASCII					
[Us] Rated Supply Voltage	24 V DC					
Supply Voltage Limits	19.228.8 V					
Inrush Current	30 A					
Maximum Power Consumption In W	12 W when power is not supplied to external devices 7 W when backlight is OFF 8 W when backlight is dimmed 17 W					
Local Signalling	Status LED green, steady for offline Status LED green, steady for operating Status LED orange, flashing for software starting up Status LED red, steady for power supply (ON) Status LED clear, faded for power supply (OFF) COM2 LED yellow, steady for data is being transmitted COM2 LED yellow, faded for no data transmission SD card LED green, steady for card is inserted SD card LED green, faded for card is not inserted or is not being accessed					

Software Designation	Vijeo Designer configuration software >= V6.1					
Memory Description	Flash EPROM, 96 MB					
Data Backed Up	512 KB internal RAM (SRAM)					
Data Storage Equipment	SD card, <= 32 GB SDHC card, <= 32 GB					
Downloadable Protocols	Schneider Electric Modicon Modbus Schneider Electric Modicon Uni-TE Schneider Electric Modicon Modbus Plus Schneider Electric Modicon FIPWAY Mitsubishi Melsec third party protocols Omron Sysmac third party protocols Rockwell Automation Allen-Bradley third party protocols Siemens Simatic third party protocols Schneider Electric Modicon Modbus TCP					
Integrated Connection Type	COM1 serial link SUB-D 9, interface: RS232C, transmission rate: 2400115200 bps COM2 serial link RJ45, interface: RS485, transmission rate: 2400115200 bps COM2 serial link RJ45, interface: RS485, transmission rate: 187.5 kbps compatible with Siemens MPI Ethernet RJ45, interface: 10BASE-T/100BASE-TX Ethernet RJ45, interface: IEEE 802.3 USB 2.0 type A USB 2.0 type mini B					
Product Mounting	Flush mounting					
Fixing Mode	By 8 nuts By 4 L brackets					
Front Material	Stainless steel 304					
Enclosure Material	РРТ					
Type Of Cooling	Natural convection					
Width	316.5 mm					
Height	258.5 mm					
Depth	57 mm					
Net Weight	2.5 kg					
Environment						
Standards	IEC 61131-2 IEC 61000-6-2 UL 508					
Product Certifications	C-Tick cULus CE KCC UKCA UKEX					
Ambient Air Temperature For Operation	055 °C					
Ambient Air Temperature For Storage	-2060 °C					
Deletine Houselelle						

Shock Resistance	147 m/s $^2$ 3 chocks in each direction X, Y and Z conforming to IEC 61131-2

NEMA 4X front panel (indoor use)

10...90 % without condensation

IP20 (rear panel) conforming to IEC 60529 IP66K (front panel) conforming to IEC 60529 IP66K (front panel) conforming to DIN 40050-9

< 2000 m

**Relative Humidity** 

Operating Altitude

**Ip Degree Of Protection** 

Nema Degree Of Protection

Vibration Resistance	3.5 mm (f = 59 Hz) - X, Y, Z directions for 10 cycles (approx. 100 min) - conforming to IEC 61131-2 1 gn (f = 9150 Hz) - X, Y, Z directions for 10 cycles (approx. 100 min) - conforming to IEC 61131-2
Resistance To Electrostatic Discharge	6 kV contact discharge conforming to IEC 61000-4-2 level 3

# **Packing Units**

r aciming Critico	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.000 cm
Package 1 Width	30.000 cm
Package 1 Length	35.500 cm
Package 1 Weight	3.439 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	30
Package 2 Height	115.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	115.170 kg

# **Contractual warranty**

Warranty 18 months

# Sustainability Green Premium\*

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes


### **Certifications & Standards**

Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins			
Circularity Profile	End of Life Information			

**Dimensions Drawings** 

### **Dimensions**


#### **External Dimensions**



- 1 Front
- 2 Right Side
- 3 Тор

#### **Installation with Installation Fasteners**


### **HMIGTO5315**



- 1 Left Side
- 2 Front
- 3 Right Side
- 4 Top
- 5 Bottom

### **Dimensions with Cables**

## **HMIGTO5315**




- 1 Left Side
- 2 Rear
- 3 Right Side
- 4 Top
- 5 Bottom

## Mounting and Clearance


### Mounting

#### **Panel Cut Dimensions**




A		В		С		R	
mm	in.	mm	in.	mm	in.	mm	in.
298 (+1, -0)	11.73 (+0.04, -0)	240 (+1, -0)	9.45 (+0.04, -0)	1.65	0.060.2	3 max.	0.12 max.

#### **Installation Fastener Dimensions**



### **Installation Requirements**

#### **Mounting Angle**



When installing the panel in a slanted position with an incline more than  $30^{\circ}$ , the ambient temperature must not exceed  $40^{\circ}$ C ( $104^{\circ}$ F). You may need to use forced air cooling (fan,A/C) to ensure the ambient operating temperature is  $40^{\circ}$ C or less ( $104^{\circ}$ F or less).

#### Clearance

