Product datasheet





TeSys GV2 & GV3 - shunt trip -415 V AC 60Hz

GVAS416

! Discontinued on: 10 Oct 2020

EAN Code: 3389110344134

① Discontinued

Main

Range	TeSys
Product Or Component Type	Shunt trip release
Device Short Name	GVAS

Complementary

Complementary	
Range Compatibility	TeSys GV2ME TeSys GV2LE TeSys GV2L TeSys GV2P TeSys GV3L TeSys GV3L
[Uc] Control Circuit Voltage	415 V AC 60 Hz
Control Circuit Voltage Limits	0.71.1 Un
[Ui] Rated Insulation Voltage	690 V AC conforming to IEC 60947-1 600 V AC conforming to UL 60947-4-1 600 V AC conforming to CSA C22.2 No 60947-4-1
Threshold Tripping Voltage	0.750.2 Un
Inrush Power In Va	14 VA AC
Inrush Power In W	10.5 W
Hold-In Power Consumption In Va	5 VA AC
Hold-In Power Consumption In W	1.6 W
Operating Time	1015 ms conforming to IEC 60947-1
On-Load Factor	100 %
Connections - Terminals	Screw clamp terminals 1 cable(s) 12.5 mm²solid Screw clamp terminals 2 cable(s) 12.5 mm²solid Screw clamp terminals 1 cable(s) 0.752.5 mm²flexible without cable end Screw clamp terminals 2 cable(s) 0.752.5 mm²flexible without cable end Screw clamp terminals 1 cable(s) 0.751.5 mm²flexible with cable end Screw clamp terminals 2 cable(s) 0.751.5 mm²flexible with cable end
Tightening Torque	< 1.4 N.m on screw clamp terminals
Mechanical Durability	10000 cycles with GV3P and GV3L 30000 cycles with GV2ME and GV2P
Quantity Per Set	Set of 10
Height	89 mm
Width	18 mm
Depth	66 mm
Net Weight	0.105 kg

Life Is On Schneider 19 Apr 2024

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.1 cm
Package 1 Width	3.6 cm
Package 1 Length	8.3 cm
Package 1 Weight	113 g

Contractual warranty

Warranty 18 months

19 Apr 2024



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Connections and Schema

GVAS***

