Product datasheet





12W Touch Advanced Display **WXGA**

Local distributor code:

402743143 HMIDT651

EAN Code: 3606480687266

Main

Range Of Product	Harmony GTU
Product Or Component Type	Advanced touchscreen panel
Terminal Type	Touchscreen display
[Us] Rated Supply Voltage	1224 V DC power supply
Supply Voltage Limits	10.828.8 V
Power Consumption In W	11.5 W
Inrush Current	30 A

Complementary

Touchscreen Resolution	1024 x 1024
Pixel Resolution	1280 x 800
Display Size	12.1 inch
Aspect Ratio	4:3
Display Type	Colour TFT LCD
Display Resolution	1280 x 800 pixels WVGA
Display Colour	262144 colors
Backlight Lifespan	50000 hours
Touch Panel	Single touch analogue resistive
Type Of Cooling	Natural convection
Type Of Installation	Indoor installation
Cut-Out Dimensions	295 (+ 1/- 0) x 217 (+ 1/- 0) mm
Width	308.5 mm
Height	230.5 mm
Depth	67 mm
Net Weight	3 kg

Environment

Ip Degree Of Protection	Front panel: IP66 Front panel: IP67
Nema Degree Of Protection	NEMA 4X front panel

Standards	UL 508 ANSI/ISA 12-12-01 Class I division 2 CSA C22.2 No 213 CSA C22.2 No 142 IEC 61132-2	
Product Certifications	CULus KC CE RCM UKCA UKEX	
Ambient Air Temperature For Operation	060 °C conforming to IEC 61131-2	
Ambient Air Temperature For Storage	-2060 °C	
Relative Humidity	1090 % non-condensing	
Operating Altitude	2000 m	
Vibration Resistance	3.5 mm constant amplitude (f = 59 Hz) conforming to IEC 61131-2 9.8 m/s ² (f = 9150 Hz) conforming to IEC 61131-2	
Shock Resistance	147 m/s ² conforming to IEC 61131-2	
Electromagnetic Compatibility	Electrostatic discharge immunity test level 3 conforming to IEC 61000-4-2	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.6 cm
Package 1 Width	33.0 cm
Package 1 Length	43.0 cm
Package 1 Weight	4.6 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	2
Package 2 Height	42.0 cm
Package 2 Width	34.5 cm
Package 2 Length	46.0 cm
Package 2 Weight	9.292 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	20
Package 3 Height	110.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	103.62 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards


Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Circularity Profile	End of Life Information		

HMIDT651

Dimensions Drawings

External Dimensions

Display Unit with Box Module




- 1 Front
- 2 Left
- 3 Bottom

Installation with Installation Fasteners and Dimensions with Cables

Product datasheet

HMIDT651




- (A) Rotation area of the fastener(B) Pitch of the center of installation fastner screws
- 1 Right
- 2 Front
- 3 Left
- 4 Bottom
- **5** Top

HMIDT651

Mounting and Clearance

Mounting

Panel Cut Dimensions



Dimensions in mm


Α	В	С	R
295 (+1/-0)	217 (+1/-0)	1.65	3 max.

Dimensions in in.

Α	В	С	R
11.61 (+0.04/-0)	8.54 (+0.04/-0)	0.060.2	0.12 max.

Installation Requirements

Mounting Angle



When installing this product in a slanted position with an incline more than 30°, the ambient temperature must not exceed 40 °C (104 °F). You may need to use forced air cooling (fan, A/C) to ensure the ambient operating temperature is 40 °C or less (104 °F or less).

Clearance

