Specifications





advanced touchscreen panel 640 x 480 pixels VGA- 7.5" - TFT - 96

MB

Local distributor code: 398059190

HMIGTO4310

EAN Code: 3595864150277

Main

Range Of Product	Harmony GTO Advanced touchscreen panel				
Product Or Component Type					
Display Colour	65536 colours				
Display Size	7.5 inch				
Supply	External source				
Operating System	Harmony				
attery Type Lithium battery for internal RAM, autonomy: 100 days, charging time = 5 day(- battery life = 10 year(s)					

Complementary

Terminal Type	Touchscreen display					
Display Type	Backlit colour TFT LCD					
Display Resolution	640 x 480 pixels VGA					
Touch Sensitive Zone	1024 x 1024					
Touch Panel	Resistive film, 1000000 cycles					
Backlight Lifespan	50000 hours white at 25 °C					
Brightness	16 levels - control by touch panel 16 levels - control by software					
Character Font	Korean Taiwanese (traditional Chinese) Japanese (ANK, Kanji) ASCII Chinese (simplified Chinese)					
[Us] Rated Supply Voltage	24 V DC					
Supply Voltage Limits	19.228.8 V					
Inrush Current	30 A					
Maximum Power Consumption In W	8 W when power is not supplied to external devices 5 W when backlight is OFF 5.5 W when backlight is dimmed 12 W					
Local Signalling	Status LED green, steady for offline Status LED green, steady for operating Status LED orange, flashing for software starting up Status LED red, steady for power supply (ON) Status LED clear, faded for power supply (OFF) COM2 LED yellow, steady for data is being transmitted COM2 LED yellow, faded for no data transmission SD card LED green, steady for card is inserted SD card LED green, faded for card is not inserted or is not being accessed					
Software Designation Vijeo Designer configuration software >= V6.1						

Memory Description	Flash EPROM, 96 MB				
Data Backed Up	512 KB internal RAM (SRAM)				
Data Storage Equipment	SD card, <= 32 GB SDHC card, <= 32 GB				
Downloadable Protocols	Schneider Electric Modicon Modbus Schneider Electric Modicon Uni-TE Schneider Electric Modicon Uni-TE Schneider Electric Modicon Modbus Plus Schneider Electric Modicon FIPWAY Mitsubishi Melsec third party protocols Omron Sysmac third party protocols Rockwell Automation Allen-Bradley third party protocols Siemens Simatic third party protocols Schneider Electric Modicon Modbus TCP COM1 serial link SUB-D 9, interface: RS232C, transmission rate: 2400115200 bps COM2 serial link RJ45, interface: RS485, transmission rate: 2400115200 bps COM2 serial link RJ45, interface: RS485, transmission rate: 187.5 kbps compatible with Siemens MPI Ethernet RJ45, interface: 10BASE-T/100BASE-TX Ethernet RJ45, interface: IEEE 802.3 USB 2.0 type A USB 2.0 type mini B				
Integrated Connection Type					
Product Mounting	Flush mounting				
Fixing Mode	By 4 screw clamps				
Front Material	РРТ				
Enclosure Material	РРТ				
Type Of Cooling	Natural convection				
Width	218 mm				
Height	173 mm				
Depth	60 mm				
Net Weight	1.2 kg				

Environment

Standards	IEC 61131-2				
	IEC 61000-6-2				
	UL 508				
Product Certifications	CE				
	cULus				
	KCC				
	C-Tick				
	UKCA				
	UKEX				
Ambient Air Temperature For Operation	055 °C				
Ambient Air Temperature For					
Storage	-2060 °C				
Relative Humidity	1090 % without condensation				
Operating Altitude	< 2000 m				
Ip Degree Of Protection	IP20 (rear panel) conforming to IEC 60529				
	IP65 (front panel) conforming to IEC 60529				
Nema Degree Of Protection	NEMA 4X front panel (indoor use)				
Shock Resistance	147 m/s ² 3 chocks in each direction X, Y and Z conforming to IEC 61131-2				
Vibration Resistance	3.5 mm (f = 59 Hz) - X, Y, Z directions for 10 cycles (approx. 100 min) - conforming				
	to IEC 61131-2				
	1 gn (f = 9150 Hz) - X, Y, Z directions for 10 cycles (approx. 100 min) - conforming				
	to IEC 61131-2				
Resistance To Electrostatic Discharge	6 kV contact discharge conforming to IEC 61000-4-2 level 3				

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.500 cm
Package 1 Width	26.400 cm
Package 1 Length	30.500 cm
Package 1 Weight	1.532 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	64
Package 2 Height	105.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	124.000 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance



Rohs Exemption Information


Certifications & Standards

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Circularity Profile	End of Life Information		

Dimensions Drawings


Dimensions

External Dimensions




- 1 Front
- 2 Right Side
- 3 Top


Installation with Installation Fasteners



- 1 Left Side
- 2 Front
- 3 Right Side
- 4 Top
- 5 Bottom

Dimensions with Cables








- 1 Left Side
- 2 Rear
- 3 Right Side
- 4 Top
- 5 Bottom

Mounting and Clearance


Mounting


Panel Cut Dimensions




Α		В		С		R	
mm	in.	mm	in.	mm	in.	mm	in.
204.5 (+1, -0)	8.05 (+0.04, -0)	159.5 (+1, -0)	6.28 (+0.04, -0)	1.65	0.060.2	3 max.	0.12 max.

Installation Fastener Dimensions










Installation Requirements

Mounting Angle



When installing the panel in a slanted position with an incline more than 30° , the ambient temperature must not exceed 40 °C (104 °F). You may need to use forced air cooling (fan,A/C) to ensure the ambient operating temperature is 40° C or less (104 °F or less).

Clearance

