# **Product datasheet**

Specification





# touch panel screen 3"4 Monochrome W/P/R for Zelio

HMISTO501

- ! Discontinued on: 27 Dec 2019
- ! To be end-of-service on: 31 Dec 2025

① Discontinued

EAN Code: 3595864127835

### Main

Range Of Product	Harmony STO & STU
Product Or Component Type	Touch panel screen
Software Designation	Vijeo Designer
Operating System	Harmony
Processor Name	CPU RISC

## Complementary

Display Size	3.4 inch				
Display Type	Backlit monochrome STN LCD				
Background Colour	White, pink and red				
Display Resolution	200 x 80 pixels				
Touch Panel	Analogue				
Backlight Lifespan	10000 hours with red 50000 hours with pink 50000 hours with white				
Brightness	8 levels				
Contrast	16 levels via touch panel				
Character Font	Korean Japanese (ANK, Kanji) Taiwanese (traditional Chinese) Chinese (simplified Chinese) ASCII				
[Us] Rated Supply Voltage	24 V DC +/- 20 %				
Inrush Current	30 A				
Local Signalling	1 LED (green) for normal operation				
Power Consumption In W	5 W				
Number Of Pages	Limited by internal memory capacity				
Processor Frequency	333 MHz				
Memory Description	Application memory 16 MB Back up of data 128 kB				
Integrated Connection Type	1 USB 2.0 type mini B 1 USB 2.0 type A power supply - removable screw terminal block serial link - 9-pin terminal block - RS232C				
Supply	External source				

Realtime Clock	Access to the PLC real-time clock				
Downloadable Protocols	Zelio				
Range Compatibility	Zelio Logic				
Fixing Mode	By 2 spring clips, mounting on 1.65 mm thick panel				
Enclosure Material	PPT				
Marking	CE				

## **Environment**

Immunity To Microbreaks	3 ms			
Standards	IEC 61000-6-2			
	FCC Class A			
	UL 508			
	UL 1604			
	EN 61131-2			
Product Certifications	CE			
	UL Class 1 Division 2 T5			
	UL Class 1 Division 2 T4A			
	C-Tick			
	cULus			
Ambient Air Temperature For Operation	050 °C			
Ambient Air Temperature For Storage	-2060 °C			
Relative Humidity	090 % without condensation			
Operating Altitude	<= 2000 m			
Ip Degree Of Protection	IP20 (rear panel) conforming to IEC 60529			
	IP65 (front panel) conforming to IEC 60529			
Nema Degree Of Protection	NEMA 4X front panel (indoor use)			
Shock Resistance	15 gn for 11 ms conforming to IEC 60068-2-27			
Vibration Resistance	+/- 3.5 mm (f = 59 Hz) conforming to IEC 60068-2-6			
	1 gn (f = 9150 Hz) conforming to IEC 60068-2-6			
Electromagnetic Compatibility	Resistance to radiated electromagnetic fields - test level: 10 V/m conforming to IEC 61000-4-3			

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	13.0 cm
Package 1 Length	19.0 cm
Package 1 Weight	382.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.099 kg

# **Contractual warranty**

Warranty

30 Apr 2024

18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

# Well-being performance

✓ Reach Free Of Svhc
 ✓ Mercury Free
 ✓ Rohs Exemption Information


#### **Certifications & Standards**


Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins		
Environmental Disclosure	Product Environmental Profile		
China Rohs Regulation	China RoHS declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)		
Reach Regulation	REACh Declaration		

## HMISTO501

#### **Dimensions Drawings**


#### **Dimensions with Spring Clips**





- **(1)** Top
- (2) Front

#### **Dimensions without Spring Clips**



- **(1)** Top
- (2) Front
- (3) Right Side


# **Product datasheet**


## HMISTO501

# Mounting and Clearance


#### Clearance







#### **Panel Cut-out Dimensions**



#### (1) Panel

A (mm)	A (in.)	B (mm)	B (in.)	C (mm) Spring Clips	C (in.) Spring Clips	R (mm)	R (in.)
+1 105 -0	+0.04 4.13 -0	+1 66 -0	+0.04 2.59 -0	1.5 to 6.0	0.059 to 0.236	2.0 to 3.0	0.078 to 0.118