Product datasheet

Specifications





integrated drive ILS with stepper motor - 24..48 V - DeviceNet - 5 A

ILS2D851PC1F0

- () Discontinued on: 15 Jun 2023
- () To be end-of-service on: 31 Dec 2026

EAN Code: 3389119228015

	•	
ΝЛ	^	n
IVI	ai	
		•••

Range Of Product Lexium integrated drive Product Or Component Type Motion integrated drive Device Short Name ILS Motor Type 3-phase stepper motor Number Of Motor Poles 6 Network Number Of Phases Single phase [Us] Rated Supply Voltage 48 V 24 V Network Type DC Communication Interface DeviceNet, integrated Length 187.3 mm Winding Type Medium speed of rotation and medium torque Electrical Connection Industrial connector Holding Brake With Gear Box Type Without Nominal Speed 300 rpm at 24 V 600 rpm at 48 V Nominal Torque 2 N.m		
Device Short Name ILS Motor Type 3-phase stepper motor Number Of Motor Poles 6 Network Number Of Phases Single phase [Us] Rated Supply Voltage 48 V 24 V Network Type DC Communication Interface DeviceNet, integrated Length 187.3 mm Winding Type Medium speed of rotation and medium torque Electrical Connection Industrial connector Holding Brake With Gear Box Type Without Nominal Speed 300 rpm at 24 V 600 rpm at 48 V Nominal Torque 2 N.m Holding Torque 6 N.m holding brake	f Product Lexium inte	agrated drive
Motor Type 3-phase stepper motor Number Of Motor Poles 6 Network Number Of Phases Single phase [Us] Rated Supply Voltage 48 V 24 V 24 V Network Type DC Communication Interface DeviceNet, integrated Length 187.3 mm Winding Type Medium speed of rotation and medium torque Electrical Connection Industrial connector Holding Brake With Gear Box Type Without Nominal Speed 300 rpm at 24 V Nominal Torque 2 N.m Holding Torque 6 N.m holding brake	Or Component Type Motion inte	grated drive
Number Of Motor Poles 6 Network Number Of Phases Single phase [Us] Rated Supply Voltage 48 V 24 V 24 V Network Type DC Communication Interface DeviceNet, integrated Length 187.3 mm Winding Type Medium speed of rotation and medium torque Electrical Connection Industrial connector Holding Brake With Gear Box Type Without Nominal Speed 300 rpm at 24 V 600 rpm at 48 V 600 rpm at 48 V Nominal Torque 2 N.m Holding Torque 6 N.m holding brake	hort Name ILS	
Network Number Of Phases Single phase [Us] Rated Supply Voltage 48 V 24 V 24 V Network Type DC Communication Interface DeviceNet, integrated Length 187.3 mm Winding Type Medium speed of rotation and medium torque Electrical Connection Industrial connector Holding Brake With Gear Box Type Without Nominal Speed 300 rpm at 24 V 600 rpm at 48 V 400 rpm at 48 V Nominal Torque 2 N.m Holding Torque 6 N.m holding brake	vpe 3-phase ste	epper motor
[Us] Rated Supply Voltage 48 V 24 V 24 V Network Type DC Communication Interface DeviceNet, integrated Length 187.3 mm Winding Type Medium speed of rotation and medium torque Electrical Connection Industrial connector Holding Brake With Gear Box Type Without Nominal Speed 300 rpm at 24 V Nominal Torque 2 N.m Holding Torque 6 N.m holding brake	Of Motor Poles 6	
24 V Network Type DC Communication Interface DeviceNet, integrated Length 187.3 mm Winding Type Medium speed of rotation and medium torque Electrical Connection Industrial connector Holding Brake With Gear Box Type Without Nominal Speed 300 rpm at 24 V 600 rpm at 48 V Nominal Torque 2 N.m Holding Torque 6 N.m holding brake	Number Of Phases Single phase	se
Communication Interface DeviceNet, integrated Length 187.3 mm Winding Type Medium speed of rotation and medium torque Electrical Connection Industrial connector Holding Brake With Gear Box Type Without Nominal Speed 300 rpm at 24 V 600 rpm at 48 V Nominal Torque 2 N.m Holding Torque 6 N.m holding brake		
Length 187.3 mm Winding Type Medium speed of rotation and medium torque Electrical Connection Industrial connector Holding Brake With Gear Box Type Without Nominal Speed 300 rpm at 24 V 600 rpm at 48 V Nominal Torque 2 N.m Holding Torque 6 N.m holding brake	Type DC	
Winding Type Medium speed of rotation and medium torque Electrical Connection Industrial connector Holding Brake With Gear Box Type Without Nominal Speed 300 rpm at 24 V 600 rpm at 48 V Nominal Torque 2 N.m Holding Torque 6 N.m holding brake	nication Interface DeviceNet,	integrated
Electrical Connection Industrial connector Holding Brake With Gear Box Type Without Nominal Speed 300 rpm at 24 V 600 rpm at 48 V Nominal Torque 2 N.m Holding Torque 6 N.m holding brake	187.3 mm	
Holding Brake With Gear Box Type Without Nominal Speed 300 rpm at 24 V 600 rpm at 48 V Nominal Torque 2 N.m Holding Torque 6 N.m holding brake	Type Medium sp	eed of rotation and medium torque
Gear Box Type Without Nominal Speed 300 rpm at 24 V 600 rpm at 48 V Nominal Torque 2 N.m Holding Torque 6 N.m holding brake	al Connection Industrial c	onnector
Nominal Speed 300 rpm at 24 V 600 rpm at 48 V Nominal Torque 2 N.m Holding Torque 6 N.m holding brake	Brake With	
600 rpm at 48 V Nominal Torque 2 N.m Holding Torque 6 N.m holding brake	x Type Without	
Holding Torque 6 N.m holding brake	•	
	Torque 2 N.m	
	Torque 6 N.m hold 2 N.m	ing brake

Complementary

Transmission Rate	125, 250, 500 kbauds
Mounting Support	Flange
Motor Flange Size	85 mm
Number Of Motor Stacks	1
Centring Collar Diameter	60 mm
Centring Collar Depth	2 mm
Number Of Mounting Holes	4
Mounting Holes Diameter	6.5 mm
Circle Diameter Of The Mounting Holes	99 mm

Feedback Type	Index pulse
Shaft End	Untapped
Second Shaft	Without second shaft end
Shaft Diameter	12 mm
Shaft Length	30 mm
Supply Voltage Limits	1855 V
Current Consumption	5000 mA maximum continuous
Associated Fuse Rating	16 A
Commissioning Interface	RS485 Modbus TCP (9.6, 19.2 and 38.4 kbauds)
Input/Output Type	4 signals (each be used as input or output)
Voltage State 0 Guaranteed	-34.5 V
Voltage State 1 Guaranteed	1530 V
Discrete Input Current	10 mA at 24 V for safety input 2 mA at 24 V for 24 V signal interface
Discrete Output Voltage	2325 V
Maximum Switching Current	100 mA per output 200 mA total
Protection Type	Safe torque off Overload of output voltage Short circuit of the output voltage
Peak Stall Torque	2 N.m
Continuous Stall Torque	2 N.m
Speed Feedback Resolution	20000 points/turn
Accuracy Error	+/- 6 arc min
Rotor Inertia	1.3 kg.cm ²
Maximum Mechanical Speed	3000 rpm
Maximum Radial Force Fr	100 N
Maximum Axial Force Fa	170 N (tensile force) 30 N (force pressure)
Service Life In Hours	20000 h bearing
Brake Pull-In Power	22 W
Brake Release Time	40 ms
Brake Application Time	20 ms
Marking	CE
Type Of Cooling	Natural convection
Net Weight	4.4 kg

Environment

Standards

EN 61800-3:2001, second environment EN/IEC 50178 EN 61800-3 : 2001-02 EN 50347 IEC 60072-1 EN/IEC 61800-3 IEC 61800-3, Ed 2

Product Certifications	UL TÜV cUL
Ambient Air Temperature For Operation	4055 °C (with power derating of 2 % per °C) 040 °C (without derating)
Permissible Ambient Air Temperature Around The Device	105 °C power amplifier 110 °C motor
Ambient Air Temperature For Storage	-2570 °C
Operating Altitude	<= 1000 m without derating
Relative Humidity	1585 % without condensation
Vibration Resistance	20 m/s² (f= 10500 Hz) 10 cycles conforming to EN/IEC 60068-2-6
Shock Resistance	150 m/s ² 1000 shocks conforming to EN/IEC 60068-2-29
Ip Degree Of Protection	IP41 shaft bushing: conforming to EN/IEC 60034-5 IP54 total except shaft bushing: conforming to EN/IEC 60034-5

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.5 cm
Package 1 Width	19.0 cm
Package 1 Length	39.0 cm
Package 1 Weight	3.4 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Dimensions Drawings

Integrated Drive with Holding Brake


Dimensions



- 1 Accessories: I/O signal insert with industrial connectors
- 2 Option: industrial connectors
- 3 Earth (ground) terminal
- 4 Accessories: cable entries $\emptyset = 3 \dots 9 \text{ mm}/0.12 \dots 0.35 \text{ in.}$
- L 187.3 mm/7.37 in.
- D 12 mm/0.47 in.


Connections and Schema

Connection Example with 4 I/O Signals



Performance Curves

Torque Characteristics



- X Speed of rotation in rpm
- Y Torque in Nm
- 1.1 Max. torque at 24 V
- 1.2 Max. torque at 48 V