# **Product datasheet**

Specification



## FLEXIBLE LENGTH 40A 0.5M

Local distributor code:

21469918 KBA40DF405W



EAN Code: 3606480000331

### Main

Range Of Product	Canalis	
Product Name	КВА	
Offer Type	Classic Control system	
Product Or Component Type	Flexible element	
Busbar Description	Flexible length	
Device Application	Lighting Power socket distribution	
Direction Change Type	3 dimensions	
[le] Rated Operational Current	40 A at 35 °C 25 A	
[Ue] Rated Operational Voltage	230400 V	
Network Frequency	50/60 Hz	
Number Of Circuits	1	
Busbar Trunking Polarity	3L + N + PE	
Control Type	Communicating	
Communication Port Protocol	DALI	
Colour	White (RAL 9003)	

### Complementary

Mounting Mode	By clips
Thermal Stress Limit	900 kA².s
Maximum Radiated Magnetic Field	2 pT
[Uimp] Rated Impulse Withstand Voltage	4 kV
[Ui] Rated Insulation Voltage	690 V
[Icw] Rated Short-Time Withstand Current	0.94 kA
[lpk] Rated Peak Withstand Current	9.6 kA
Thdi	015 % 40 A 1533 % 32 A 33100 % 28 A
Length	0.5 m
Depth	30 mm
Height	46 mm

Net Weight	50 g
Standards	IEC 61439-1
	IEC 61439-6

### **Environment**

Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK06 conforming to IEC 62262
Ambient Air Temperature For Operation	035 °C without derating

#### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	6.000 cm
Package 1 Length	65.000 cm
Package 1 Weight	750.000 g
Unit Type Of Package 2	PAL
Number Of Units In Package 2	20
Package 2 Height	36.000 cm
Package 2 Width	80.000 cm
Package 2 Length	69.000 cm
Package 2 Weight	22.000 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Halogen Free Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

#### **Dimension Drawings**



