

## Specifications



389353339

KNB25CF5

EAN Code: 3606480003295

Range Of Product	Canalis
Range Compatibility	Canalis KN busbar trunking
Product Or Component Type	Tap-off unit
Busbar Trunking Compatibility	Canalis KN busbar trunkingplug-in
[Ie] Rated Operational Current	25 A at 35 °C
Protection Type	fuse isolator: for aM cylindrical fuse, size 10 x 38 mm - 25 A conforming to NF fuse isolator: for gG cylindrical fuse, size 10 x 38 mm - 20 A conforming to NF
Provided Equipment	fuse to be ordered separately cable clamp
Mounting Mode	Plug-in with fixed polarity
Tap-Off Unit Polarity	3L+N+PE 3L+PE
Colour	White (RAL 9001)

Device Application	Low power distribution
[Ue] Rated Operational Voltage	230...500 V depending on protective device
[Uimp] Rated Impulse Withstand Voltage	4.6 kV
[Ui] Rated Insulation Voltage	500 V depending on protective device
Network Frequency	50/60 Hz
Electrical Connection	Cable clamp terminal 6 mm² flexible Cable clamp terminal 10 mm² rigid
Door/Cover Opening Side	Front
Tap-Off Unit Disconnection Mode	By drawing out
Standards	IEC 61439-1 IEC 61439-6
Width	103 mm
Depth	48.8 mm
Height	161 mm
Net Weight	0.38 kg

Ip Degree Of Protection	IP55 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.800 cm
Package 1 Width	11.800 cm
Package 1 Length	15.800 cm
Package 1 Weight	291.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	24
Package 2 Height	17.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	7.617 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	384
Package 3 Height	82.300 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	133.872 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability






**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
	Halogen Free Product	
Reach Regulation	<a href="#">REACH Declaration</a>	
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>	
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	