Product datasheet

Specifications





TeSys D contactor - 3P(3 NO) -AC-3 - <= 440 V 32 A - 240 V AC 50/60 Hz coil

Local distributor code: 381818597

LC1D32U7

EAN Code: 3389110351729

Main

Range	TeSys TeSys Deca
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load Motor control
Utilisation Category	AC-4 AC-1 AC-3 AC-3e
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC
[le] Rated Operational Current	32 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 50 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 32 A (at <60 °C) at <= 440 V AC AC-3e for power circuit
[Uc] Control Circuit Voltage	240 V AC 50/60 Hz

Complementary

Motor Power Kw	7.5 kW at 220230 V AC 50/60 Hz (AC-3)
	15 kW at 380400 V AC 50/60 Hz (AC-3)
	15 kW at 415440 V AC 50/60 Hz (AC-3)
	18.5 kW at 500 V AC 50/60 Hz (AC-3)
	18.5 kW at 660690 V AC 50/60 Hz (AC-3)
	7.5 kW at 400 V AC 50/60 Hz (AC-4)
	7.5 kW at 220230 V AC 50/60 Hz (AC-3e)
	15 kW at 380400 V AC 50/60 Hz (AC-3e)
	15 kW at 415440 V AC 50/60 Hz (AC-3e)
	18.5 kW at 500 V AC 50/60 Hz (AC-3e)
	18.5 kW at 660690 V AC 50/60 Hz (AC-3e)
Motor Power Hp	2 hp at 115 V AC 50/60 Hz for 1 phase motors
	5 hp at 230/240 V AC 50/60 Hz for 1 phase motors
	10 hp at 200/208 V AC 50/60 Hz for 3 phases motors
	10 hp at 230/240 V AC 50/60 Hz for 3 phases motors
	20 hp at 460/480 V AC 50/60 Hz for 3 phases motors
	25 hp at 575/600 V AC 50/60 Hz for 3 phases motors
Compatibility Code	LC1D
Pole Contact Composition	3 NO
Protective Cover	With
[Ith] Conventional Free Air	10 A (at 60 °C) for signalling circuit
Thermal Current	50 A (at 60 °C) for power circuit

Irms Poted Making Canaaity	
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1
	550 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	550 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand	60 A 40 °C - 10 min for power circuit
Current	138 A 40 °C - 1 min for power circuit
	260 A 40 °C - 10 s for power circuit
	430 A 40 °C - 1 s for power circuit
	100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
J.	63 A gG at <= 690 V coordination type 1 for power circuit
	63 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2 mOhm - Ith 50 A 50 Hz for power circuit
Power Dissipation Per Pole	2 W AC-3
	5 W AC-1
	2 W AC-3e
[Ui] Rated Insulation Voltage	Power circuit: 600 V CSA certified
	Power circuit: 600 V UL certified
	Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified
	Signalling circuit: 600 V UL certified
	Power circuit: 690 V conforming to IEC 60947-4-1
Overvoltage Category	
Pollution Degree	3
[Uimp] Rated Impulse Withstand	6 kV conforming to IEC 60947
Voltage	
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1
	B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO
	13849-1
Mechanical Durability	15 Mcycles
Electrical Durability	1.65 Mcycles 32 A AC-3 at Ue <= 440 V
	1.4 Mcycles 50 A AC-1 at Ue <= 440 V
	1.65 Mcycles 32 A AC-3e at Ue <= 440 V
Control Circuit Type	AC at 50/60 Hz
Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz
	0.81.1 Uc (-4060 °C):operational AC 50 Hz
	0.851.1 Uc (-4060 °C):operational AC 60 Hz
	11.1 Uc (6070 °C):operational AC 50/60 Hz
Inrush Power In Va	70 VA 60 Hz cos phi 0.75 (at 20 °C)
	70 VA 50 Hz cos phi 0.75 (at 20 °C)
Hold-In Power Consumption In Va	7.5 VA 60 Hz cos phi 0.3 (at 20 °C)
	7 VA 50 Hz cos phi 0.3 (at 20 °C)
Heat Dissipation	23 W at 50/60 Hz
Operating Time	419 ms opening
	1222 ms closing
Maximum Operating Rate	3600 cyc/h 60 °C

Connections - Terminals	Control circuit: screw clamp terminals 2 12.5 mm ² - cable stiffness: flexible with cable end
	Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: flexible without cable end
	Control circuit: screw clamp terminals 2 14 mm ² - cable stiffness: flexible without cable end
	Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: flexible with cable end
	Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: solid without cable end
	Control circuit: screw clamp terminals 2 14 mm ² - cable stiffness: solid without cable end
	Power circuit: screw clamp terminals 1 2.510 mm ² - cable stiffness: flexible without cable end
	Power circuit: screw clamp terminals 2 2.510 mm ² - cable stiffness: flexible without cable end
	Power circuit: screw clamp terminals 1 110 mm ² - cable stiffness: flexible with cable end
	Power circuit: screw clamp terminals 2 1.56 mm ² - cable stiffness: flexible with cable end
	Power circuit: screw clamp terminals 1 1.510 mm ² - cable stiffness: solid without cable end
	Power circuit: screw clamp terminals 2 2.510 mm ² - cable stiffness: solid without cable end
Tightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver Philips No 2 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2 Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver pozidriv No 2
Auxiliary Contact Composition	1 NO + 1 NC
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1
Signalling Circuit Frequency	25400 Hz
Minimum Switching Voltage	17 V for signalling circuit
Minimum Switching Current	5 mA for signalling circuit
	5 mA for signalling circuit > 10 MOhm for signalling circuit
Minimum Switching Current Insulation Resistance Non-Overlap Time	

Environment

Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 IEC 60335-1
Product Certifications	GOST RINA BV CCC CSA DNV UL LROS (Lloyds register of shipping) GL
Ip Degree Of Protection	IP20 front face conforming to IEC 60529
Protective Treatment	TH conforming to IEC 60068-2-30
Climatic Withstand	conforming to IACS E10 exposure to damp heat conforming to IEC 60947-1 Annex Q category D exposure to damp heat

Permissible Ambient Air	-4060 °C
Temperature Around The Device	
	6070 °C with derating
Operating Altitude	03000 m
Fire Resistance	850 °C conforming to IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	
Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz)
	Vibrations contactor closed (4 Gn, 5300 Hz)
	Shocks contactor closed (15 Gn for 11 ms)
	Shocks contactor open (8 Gn for 11 ms)
Height	85 mm
Width	45 mm
Depth	92 mm
Net Weight	0.375 kg

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.900 cm
Package 1 Width	11.100 cm
Package 1 Length	8.900 cm
Package 1 Weight	414.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	20
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.698 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	320
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	151.627 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information