## **Product datasheet**

Specification





# TeSys D contactor - 3P(3 NO) - AC-3 - <= 440 V 25 A - 24 V DC coil

Local distributor code:

381803706 LC1D25BD

EAN Code: 3389110355994

#### Main

Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Motor control Resistive load
Utilisation Category	AC-4 AC-3 AC-1 AC-3e
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC
[le] Rated Operational Current	25 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 40 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 25 A (at <60 °C) at <= 440 V AC AC-3e for power circuit
[Uc] Control Circuit Voltage	24 V DC

#### Complementary

Motor Power Kw	5.5 kW at 220230 V AC 50/60 Hz (AC-3) 11 kW at 380400 V AC 50/60 Hz (AC-3) 11 kW at 415440 V AC 50/60 Hz (AC-3) 15 kW at 500 V AC 50/60 Hz (AC-3) 15 kW at 660690 V AC 50/60 Hz (AC-3) 5.5 kW at 400 V AC 50/60 Hz (AC-4) 5.5 kW at 220230 V AC 50/60 Hz (AC-3e) 11 kW at 380400 V AC 50/60 Hz (AC-3e) 11 kW at 415440 V AC 50/60 Hz (AC-3e) 15 kW at 500 V AC 50/60 Hz (AC-3e) 15 kW at 660690 V AC 50/60 Hz (AC-3e)
Motor Power Hp	3 hp at 230/240 V AC 50/60 Hz for 1 phase motors 2 hp at 115 V AC 50/60 Hz for 1 phase motors 7.5 hp at 230/240 V AC 50/60 Hz for 3 phases motors 15 hp at 460/480 V AC 50/60 Hz for 3 phases motors 20 hp at 575/600 V AC 50/60 Hz for 3 phases motors 7.5 hp at 200/208 V AC 50/60 Hz for 3 phases motors
Compatibility Code	LC1D
Pole Contact Composition	3 NO
Protective Cover	With
[Ith] Conventional Free Air Thermal Current	10 A (at 60 °C) for signalling circuit 40 A (at 60 °C) for power circuit
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 450 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	450 A at 440 V for power circuit conforming to IEC 60947

23 Apr 2024 Life Is On Schneider

[Icw] Rated Short-Time Withstand	240 A 40 °C - 10 s for power circuit
Current	380 A 40 °C - 1 s for power circuit
	50 A 40 °C - 10 min for power circuit
	120 A 40 °C - 1 min for power circuit
	100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
	63 A gG at <= 690 V coordination type 1 for power circuit
	40 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2 mOhm - Ith 40 A 50 Hz for power circuit
Power Dissipation Per Pole	3.2 W AC-1
	1.25 W AC-3
	1.25 W AC-3e
[Ui] Rated Insulation Voltage	Power circuit: 690 V conforming to IEC 60947-4-1
_	Power circuit: 600 V CSA certified
	Power circuit: 600 V UL certified
	Signalling circuit: 690 V conforming to IEC 60947-1
	Signalling circuit: 600 V CSA certified
	Signalling circuit: 600 V UL certified
Overvoltage Category	ш
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1
carety remaining zero.	B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO
	13849-1
	10070 1
Mechanical Durability	30 Mcycles
Electrical Durability	1.65 Mcycles 25 A AC-3 at Ue <= 440 V
	1.4 Mcycles 40 A AC-1 at Ue <= 440 V
	1.65 Mcycles 25 A AC-3e at Ue <= 440 V
Control Circuit Type	DC standard
Coil Technology	Built-in bidirectional peak limiting diode suppressor
Control Circuit Voltage Limits	0.10.25 Uc (-4070 °C):drop-out DC
-	0.71.25 Uc (-4060 °C):operational DC
	11.25 Uc (6070 °C):operational DC
Inrush Power In W	5.4 W (at 20 °C)
Hold-In Power Consumption In W	5.4 W at 20 °C
Operating Time	63 ±15 % ms closing
-	20 ±20 % ms opening
Time Constant	28 ms
Maximum Operating Rate	3600 cyc/h 60 °C

Connections - Terminals	Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible without cable end	
	Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: flexible without	
	cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible with cable	
	end Control circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: flexible with	
	cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: solid without	
	cable end Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without	
	cable end	
	Power circuit: screw clamp terminals 1 2.510 mm² - cable stiffness: flexible without cable end	
	Power circuit: screw clamp terminals 2 2.510 mm² - cable stiffness: flexible without cable end	
	Power circuit: screw clamp terminals 1 110 mm <sup>2</sup> - cable stiffness: flexible with cable end	
	Power circuit: screw clamp terminals 2 1.56 mm <sup>2</sup> - cable stiffness: flexible with cable end	
	Power circuit: screw clamp terminals 1 1.510 mm² - cable stiffness: solid without	
	cable end  Power circuit: screw clamp terminals 2 2.510 mm² - cable stiffness: solid without	
	cable end	
Tightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver Philips No 2 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2 Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver pozidriv No 2	
auxiliary Contact Composition 1 NO + 1 NC		
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1	
Signalling Circuit Frequency	25400 Hz	
Minimum Switching Voltage	17 V for signalling circuit	
Minimum Switching Current	5 mA for signalling circuit	
Insulation Resistance	> 10 MOhm for signalling circuit	
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact	
Mounting Support	Plate	
	Rail	
Environment		
Standards	CSA C22.2 No 14	
	EN 60947-4-1 EN 60947-5-1	
	IEC 60947-4-1	
	IEC 60947-5-1 UL 508	
	IEC 60335-1	
Product Certifications	LROS (Lloyds register of shipping)	
	BV GL	
	CCC	
	RINA GOST	
	CSA	
	DNV	
	UL UKCA	
Ip Degree Of Protection	IP20 front face conforming to IEC 60529	
Protective Treatment	TH conforming to IEC 60068-2-30	
Climatic Withstand	conforming to IACS E10 exposure to damp heat conforming to IEC 60947-1 Annex Q category D exposure to damp heat	
	3. , p	

Permissible Ambient Air Temperature Around The Device	-4060 °C 6070 °C with derating	
Operating Altitude	03000 m	
Fire Resistance	850 °C conforming to IEC 60695-2-1	
Flame Retardance	V1 conforming to UL 94	
Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz) Vibrations contactor closed (4 Gn, 5300 Hz) Shocks contactor closed (15 Gn for 11 ms) Shocks contactor open (8 Gn for 11 ms)	
Height	85 mm	
Width	45 mm	
Depth	101 mm	
Net Weight	0.53 kg	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	9.300 cm
Package 1 Length	11.300 cm
Package 1 Weight	586.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	15
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	9.034 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	240
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	152.000 kg

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Pvc Free	


#### **Certifications & Standards**

Reach Regulation	REACh Declaration	
Eu Rohs Directive Compliant with Exemptions		
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	End of Life Information	

#### LC1D25BD

#### **Dimensions Drawings**

#### **Dimensions**



#### (1) Minimum electrical clearance

LC1		D25D38	D183D323
b		85	99
	without cover or add-on blocks	99	99
С	with cover, without add-on blocks	101	101
с1	with LAD N or C (2 or 4 contacts)	132	132
c2	with LA6 DK10	144	144
сЗ	with LAD T, R, S	152	152
	with LAD T, R, S and sealing cover	156	156

Connections and Schema

Wiring

