



TeSys D contactor - 3P(3 NO) - AC-3 - <= 440 V 38 A - 220 V DC low cons coil

LC1D38ML

! Discontinued on: 10 Oct 2020

! Discontinued

EAN Code: 3389110051568

Main

Range	TeSys
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load Motor control
Utilisation Category	AC-1 AC-3 AC-4
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC
[le] Rated Operational Current	50 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 38 A (at <60 °C) at <= 440 V AC AC-3 for power circuit
[Uc] Control Circuit Voltage	220 V DC

Complementary

Motor Power Kw	18.5 kW at 500 V AC 50/60 Hz (AC-3) 18.5 kW at 660690 V AC 50/60 Hz (AC-3)	
	7.5 kW at 400 V AC 50/60 Hz (AC-4)	
	18.5 kW at 380400 V AC 50/60 Hz (AC-3)	
	9 kW at 220230 V AC 50/60 Hz (AC-3)	
	18.5 kW at 415440 V AC 50/60 Hz (AC-3)	
Motor Power Hp	10 hp at 230/240 V AC 50/60 Hz for 3 phases motors	
	10 hp at 200/208 V AC 50/60 Hz for 3 phases motors	
	5 hp at 240 V AC 50/60 Hz for 1 phase motors	
	20 hp at 480 V AC 50/60 Hz for 3 phases motors	
	25 hp at 600 V AC 50/60 Hz for 3 phases motors	
Compatibility Code	LC1D	
Pole Contact Composition	3 NO	
Contact Compatibility	M5	
Protective Cover	With	
[Ith] Conventional Free Air	10 A (at 60 °C) for signalling circuit	
Thermal Current	50 A (at 60 °C) for power circuit	
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1	
	250 A DC for signalling circuit conforming to IEC 60947-5-1	
	550 A at 440 V for power circuit conforming to IEC 60947	
Rated Breaking Capacity	550 A at 440 V for power circuit conforming to IEC 60947	

[Icw] Rated Short-Time Withstand	60 A 40 °C - 10 min for power circuit
Current	430 A 40 °C - 1 s for power circuit
	150 A 40 °C - 1 min for power circuit
	310 A 40 °C - 10 s for power circuit
	·
	100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
Associated Fuse Pating	40 A a C for a invalidate aire it confermine to IEC 00047 E 4
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
	63 A gG at <= 690 V coordination type 1 for power circuit
	63 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2 mOhm - Ith 50 A 50 Hz for power circuit
Power Dissipation Per Pole	5 W AC-1
. ette. 2.00.pa.io et . ete	
	3 W AC-3
[Ui] Rated Insulation Voltage	Power circuit: 600 V CSA certified
[]go	Power circuit: 600 V UL certified
	Signalling circuit: 690 V conforming to IEC 60947-1
	Signalling circuit: 600 V CSA certified
	Signalling circuit: 600 V UL certified
	Power circuit: 690 V conforming to IEC 60947-4-1
Overvoltage Category	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1
	B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO
	13849-1
	13049-1
Mechanical Durability	30 Mcycles
Electrical Durability	1.4 Mcycles 50 A AC-1 at Ue <= 440 V
	1.4 Mcycles 38 A AC-3 at Ue <= 440 V
	1.4 Micycles 30 A AC-3 at Ge \- 440 V
Control Circuit Type	DC low consumption
Coil Technology	Built-in bidirectional peak limiting diode suppressor
Control Circuit Voltage Limits	0.10.3 Uc (-4070 °C):drop-out DC
	0.81.25 Uc (-4060 °C):operational DC
	11.25 Uc (6070 °C):operational DC
Inrush Power In W	2.4 W (at 20 °C)
Hold-In Power Consumption In W	2.4 W at 20 °C
Operating Time	77 ±15 % ms closing
epo. duning rinno	· · · · · · · · · · · · · · · · · · ·
	25 ±20 % ms opening
Time Constant	40 mg
	40 ms
Maximum Operating Rate	3600 cyc/h 60 °C
	ooo oyun oo O

Connections - Terminals	Control circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible without
	cable end Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: flexible without cable end
	Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible with cable
	end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: solid without cable end
	Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without cable end
	Power circuit: screw clamp terminals 1 2.510 mm² - cable stiffness: flexible without cable end
	Power circuit: screw clamp terminals 2 2.510 mm² - cable stiffness: flexible without cable end
	Power circuit: screw clamp terminals 1 110 mm² - cable stiffness: flexible with cable end
	Power circuit: screw clamp terminals 2 1.56 mm² - cable stiffness: flexible with cable end
	Power circuit: screw clamp terminals 1 1.510 mm² - cable stiffness: solid without cable end
	Power circuit: screw clamp terminals 2 2.510 mm² - cable stiffness: solid without cable end
Tightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver Philips No 2
Auxiliary Contact Composition	1 NO + 1 NC
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1
Signalling Circuit Frequency	25400 Hz
Minimum Switching Voltage	17 V for signalling circuit
Minimum Switching Current	5 mA for signalling circuit
Insulation Resistance	> 10 MOhm for signalling circuit
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Mounting Support	Plate Rail
Environment	
Standards	CSA C22.2 No 14
	EN 60947-4-1 EN 60947-5-1
	IEC 60947-4-1
	IEC 60947-5-1 UL 508
Product Certifications	LROS (Lloyds register of shipping)
	GOST RINA
	CSA UL
	GL
	CCC DNV
	BV
Ip Degree Of Protection	IP20 front face conforming to IEC 60529
Protective Treatment	TH conforming to IEC 60068-2-30
Climatic Withstand	conforming to IACS E10 exposure to damp heat conforming to IEC 60947-1 Annex Q category D exposure to damp heat
Permissible Ambient Air Temperature Around The Device	-4060 °C 6070 °C with derating

Operating Altitude	03000 m	
Fire Resistance	850 °C conforming to IEC 60695-2-1	
Flame Retardance	V1 conforming to UL 94	
Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz) Vibrations contactor closed (4 Gn, 5300 Hz) Shocks contactor closed (15 Gn for 11 ms) Shocks contactor open (8 Gn for 11 ms)	
Height	85 mm	
Width	45 mm	
Depth	101 mm	
Net Weight	0.54 kg	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.9 cm
Package 1 Width	11.1 cm
Package 1 Length	8.9 cm
Package 1 Weight	424 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information Yes	
9	Pvc Free	

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information