Product datasheet

Specifications





TeSys D contactor - 4P(2 NO + 2 NC) - AC-1 <= 440 V 60 A 200 V AC 50/60 Hz coil

LC1D40008L7

() Discontinued on: 29 Dec 2022

① Discontinued

EAN Code: 3389110070460

Main

Range	TeSys
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load
Utilisation Category	AC-1
Poles Description	4P
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC
[le] Rated Operational Current	60 A (at <60 °C) at <= 440 V AC AC-1 for power circuit
[Uc] Control Circuit Voltage	200 V AC 50/60 Hz

Complementary

• •	
Compatibility Code	LC1D
Pole Contact Composition	2 NO + 2 NC
Protective Cover	Without
[Ith] Conventional Free Air Thermal Current	60 A (at 60 °C) for power circuit
Irms Rated Making Capacity	800 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	800 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	320 A 40 $^{\circ}$ C - 10 s for power circuit 720 A 40 $^{\circ}$ C - 1 s for power circuit 72 A 40 $^{\circ}$ C - 10 min for power circuit 165 A 40 $^{\circ}$ C - 1 min for power circuit
Associated Fuse Rating	80 A gG at <= 690 V coordination type 1 for power circuit 80 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	1.5 mOhm - Ith 60 A 50 Hz for power circuit
Power Dissipation Per Pole	5.4 W AC-1
[Ui] Rated Insulation Voltage	Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Power circuit: 690 V conforming to IEC 60947-4-1
Overvoltage Category	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947

Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	6 Mcycles
Electrical Durability	1.4 Mcycles 60 A AC-1 at Ue <= 440 V
Control Circuit Type	AC at 50/60 Hz
Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz 0.81.1 Uc (-4060 °C):operational AC 50 Hz 0.851.1 Uc (-4060 °C):operational AC 60 Hz 11.1 Uc (6070 °C):operational AC 50/60 Hz
Inrush Power In Va	140 VA 60 Hz cos phi 0.75 (at 20 °C) 160 VA 50 Hz cos phi 0.75 (at 20 °C)
Hold-In Power Consumption In Va	13 VA 60 Hz cos phi 0.3 (at 20 °C) 15 VA 50 Hz cos phi 0.3 (at 20 °C)
Heat Dissipation	45 W at 50/60 Hz
Operating Time	419 ms opening 1226 ms closing
Maximum Operating Rate	3600 cyc/h 60 °C
Connections - Terminals	Control circuit: screw clamp terminals 2 12.5 mm ² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 14 mm ² - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 1 14 mm ² - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 14 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 14 mm ² - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 2 125 mm ² - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 1 135 mm ² - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 1 135 mm ² - cable stiffness: flexible without cable end Power circuit: screw clamp terminals 1 135 mm ² - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 2 125 mm ² - cable stiffness: flexible with cable end Power circuit: screw clamp terminals 2 125 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 125 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 125 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 125 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 125 mm ² - cable stiffness: solid without cable end Power circuit: screw clamp terminals 2 125 mm ² - cable stiffness: solid without cable end
Tightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 8 N.m - on screw clamp terminals - cable 2535 mm ² hexagonal screw head 4 mm Power circuit: 5 N.m - on screw clamp terminals - cable 125 mm ² hexagonal screw head 4 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2
Mounting Support	Plate Rail

Environment

Standards		

CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508

Product Certifications	CSA CCC RINA LROS (Lloyds register of shipping) GOST BV DNV GL UL
Ip Degree Of Protection	IP20 front face conforming to IEC 60529
Protective Treatment	TH conforming to IEC 60068-2-30
Climatic Withstand	conforming to IACS E10 exposure to damp heat
Permissible Ambient Air Temperature Around The Device	-4060 °C 6070 °C with derating
Operating Altitude	03000 m
Fire Resistance	850 °C conforming to IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Shocks contactor open (8 Gn for 11 ms) Shocks contactor closed (10 Gn for 11 ms) Vibrations contactor opened (2 Gn, 5300 Hz) Vibrations contactor closed (4 Gn, 5300 Hz)
Height	127 mm
Width	85 mm
Depth	125 mm
Net Weight	1.44 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.1 cm
Package 1 Width	12.6 cm
Package 1 Length	13.2 cm
Package 1 Weight	1.464 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations