# **Product datasheet**

Specifications

#### Green Premium<sup>™</sup>



## TeSys D contactor - 3P(3 NO) -AC-3 - <= 440 V 40 A - 24 V DC standard coil

LC1D40ABD

EAN Code: 3389119408486

#### Main

Range	TeSys TeSys Deca
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Resistive load Motor control
Utilisation Category	AC-4 AC-1 AC-3 AC-3e
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC
[le] Rated Operational Current	60 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 40 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 40 A (at <60 °C) at <= 440 V AC AC-3e for power circuit
[Uc] Control Circuit Voltage	24 V DC

### Complementary

Motor Power Kw	18.5 kW at 380400 V AC 50/60 Hz (AC-3)
	11 kW at 220230 V AC 50/60 Hz (AC-3)
	22 kW at 415440 V AC 50/60 Hz (AC-3)
	22 kW at 500 V AC 50/60 Hz (AC-3)
	30 kW at 660690 V AC 50/60 Hz (AC-3)
	9 kW at 400 V AC 50/60 Hz (AC-4)
	18.5 kW at 380400 V AC 50/60 Hz (AC-3e)
	11 kW at 220230 V AC 50/60 Hz (AC-3e)
	22 kW at 415440 V AC 50/60 Hz (AC-3e)
	22 kW at 500 V AC 50/60 Hz (AC-3e)
	30 kW at 660690 V AC 50/60 Hz (AC-3e)
Motor Power Hp	5 hp at 230/240 V AC 50/60 Hz for 1 phase motors
	10 hp at 230/240 V AC 50/60 Hz for 3 phases motors
	30 hp at 575/600 V AC 50/60 Hz for 3 phases motors
	10 hp at 200/208 V AC 50/60 Hz for 3 phases motors
	3 hp at 115 V AC 50/60 Hz for 1 phase motors
	30 hp at 460/480 V AC 50/60 Hz for 3 phases motors
Compatibility Code	LC1D
Pole Contact Composition	3 NO
Protective Cover	With
[Ith] Conventional Free Air	10 A (at 60 °C) for signalling circuit
Thermal Current	60 A (at 60 °C) for power circuit

Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1	
	250 A DC for signalling circuit conforming to IEC 60947-5-1	
	800 A at 440 V for power circuit conforming to IEC 60947	
Rated Breaking Capacity	800 A at 440 V for power circuit conforming to IEC 60947	
[Icw] Rated Short-Time Withstand	320 A 40 °C - 10 s for power circuit	
Current	720 A 40 °C - 1 s for power circuit	
	72 A 40 °C - 10 min for power circuit	
	165 A 40 °C - 1 min for power circuit	
	100 A - 1 s for signalling circuit	
	120 A - 500 ms for signalling circuit	
	140 A - 100 ms for signalling circuit	
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1	
	80 A gG at <= 690 V coordination type 1 for power circuit	
	80 A gG at <= 690 V coordination type 2 for power circuit	
Average Impedance	1.5 mOhm - Ith 60 A 50 Hz for power circuit	
Power Dissipation Per Pole	2.4 W AC-3	
	5.4 W AC-1	
	2.4 W AC-3e	
[Ui] Rated Insulation Voltage	Power circuit: 600 V CSA certified	
	Power circuit: 600 V UL certified	
	Signalling circuit: 690 V conforming to IEC 60947-1	
	Signalling circuit: 600 V CSA certified	
	Signalling circuit: 600 V UL certified	
	Power circuit: 690 V conforming to IEC 60947-4-1	
Overvoltage Category	III	
Pollution Degree	3	
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947	
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1	
Mechanical Durability	10 Mcycles	
Electrical Durability	0.7 Mcycles 60 A AC-1 at Ue <= 440 V	
	1.5 Mcycles 40 A AC-3 at Ue <= 440 V	
	1.5 Mcycles 40 A AC-3e at Ue <= 440 V	
Control Circuit Type	DC standard	
Coil Technology	Built-in bidirectional peak limiting diode suppressor	
Control Circuit Voltage Limits	0.10.3 Uc (-4070 °C):drop-out DC	
	0.751.25 Uc (-4060 °C):operational DC	
	11.25 Uc (6070 °C):operational DC	
Inrush Power In W	19 W (at 20 °C)	
Hold-In Power Consumption In W	7.4 W at 20 °C	
Operating Time	50 ±15 % ms closing	
	20 ±20 % ms opening	
Time Constant	34 ms	
Maximum Operating Rate	3600 cyc/h 60 °C	
	·····y····· <del>·</del>	

Connections - Terminals	Control circuit: screw clamp terminals 2 12.5 mm <sup>2</sup> - cable stiffness: flexible with	
	cable end	
	Control circuit: screw clamp terminals 1 14 mm <sup>2</sup> - cable stiffness: flexible without	
	cable end	
	Control circuit: screw clamp terminals 2 14 mm <sup>2</sup> - cable stiffness: flexible without cable end	
	Control circuit: screw clamp terminals 1 14 mm <sup>2</sup> - cable stiffness: flexible with cable end	
	Control circuit: screw clamp terminals 1 14 mm <sup>2</sup> - cable stiffness: solid without cable end	
	Control circuit: screw clamp terminals 2 14 mm <sup>2</sup> - cable stiffness: solid without cable end	
	Power circuit: screw connection 1 135 mm <sup>2</sup> - cable stiffness: flexible without cable end	
	Power circuit: screw connection 2 125 mm <sup>2</sup> - cable stiffness: flexible without cable end	
	Power circuit: screw connection 1 135 mm <sup>2</sup> - cable stiffness: flexible with cable end Power circuit: screw connection 2 125 mm <sup>2</sup> - cable stiffness: flexible with cable end Power circuit: screw connection 1 135 mm <sup>2</sup> - cable stiffness: solid without cable end	
	Power circuit: screw connection 2 125 mm <sup>2</sup> - cable stiffness: solid without cable end	
Tightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 8 N.m - on EverLink BTR screw connectors - cable 2535 mm <sup>2</sup> hexagonal screw head 4 mm	
	Power circuit: 5 N.m - on EverLink BTR screw connectors - cable 125 mm <sup>2</sup>	
	hexagonal screw head 4 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2 Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver pozidriv No 2	
Auxiliary Contact Composition	1 NO + 1 NC	
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1	
Signalling Circuit Frequency	25400 Hz	
Minimum Switching Voltage	17 V for signalling circuit	
Minimum Switching Current	5 mA for signalling circuit	
Insulation Resistance	> 10 MOhm for signalling circuit	
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact	
Mounting Support	Rail	
	Plate	

#### Environment

Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 IEC 60335-1	
Product Certifications	CCC CSA GOST UL	
Ip Degree Of Protection	IP20 front face conforming to IEC 60529	
Protective Treatment	TH conforming to IEC 60068-2-30	
Climatic Withstand	conforming to IACS E10 exposure to damp heat conforming to IEC 60947-1 Annex Q category D exposure to damp heat	
Permissible Ambient Air Temperature Around The Device	-4060 °C 6070 °C with derating	
Operating Altitude	03000 m	

Fire Resistance	850 °C conforming to IEC 60695-2-1	
Flame Retardance	V1 conforming to UL 94	
Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz) Vibrations contactor closed (4 Gn, 5300 Hz) Shocks contactor closed (15 Gn for 11 ms) Shocks contactor open (10 Gn for 11 ms)	
Height	122 mm	
Width	55 mm	
Depth	120 mm	
Net Weight	0.925 kg	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.200 cm
Package 1 Width	13.700 cm
Package 1 Length	15.200 cm
Package 1 Weight	979.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	10
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	10.080 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	160
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	179.280 kg

## **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes
Pvc Free


#### **Certifications & Standards**

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	End of Life Information	

### **Product datasheet**

#### **Dimensions Drawings**

#### Dimensions



#### (1) Minimum electrical clearance

LC1		D40AD65A
а		55
b1	with LAD 4BB3	136
ומ	with LA4 DF, DT	157
	without cover or add-on blocks	118
c	with cover, without add-on blocks	120
c1	with LAD N (1 contact)	-
CI	with LAD N or C (2 or 4 contacts)	150
c2	with LA6 DK10	163
c3	with LAD T, R, S	171
	with LAD T, R, S and sealing cover	175

### **Product datasheet**

Connections and Schema

Wiring

