Product datasheet

Specifications





(!) Discontinued

TeSys D contactor - 3P(3 NO) -AC-3 - <= 440 V 50 A - 36 V DC standard coil

LC1D50A6CD

() Discontinued on: 18 Oct 2020

EAN Code: 3389118328082

Main

Range	TeSys TeSys Deca
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Motor control Resistive load
Utilisation Category	AC-4 AC-1 AC-3 AC-3e
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC
[le] Rated Operational Current	50 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 80 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 50 A (at <60 °C) at <= 440 V AC AC-3e for power circuit
[Uc] Control Circuit Voltage	36 V DC

Complementary

Motor Power Kw	15 kW at 220230 V AC 50/60 Hz (AC-3)
	22 kW at 380400 V AC 50/60 Hz (AC-3)
	30 kW at 500 V AC 50/60 Hz (AC-3)
	33 kW at 660690 V AC 50/60 Hz (AC-3)
	25 kW at 415 V AC 50/60 Hz (AC-3)
	30 kW at 440 V AC 50/60 Hz (AC-3)
	11 kW at 400 V AC 50/60 Hz (AC-4)
	15 kW at 220230 V AC 50/60 Hz (AC-3e)
	22 kW at 380400 V AC 50/60 Hz (AC-3e)
	30 kW at 500 V AC 50/60 Hz (AC-3e)
	33 kW at 660690 V AC 50/60 Hz (AC-3e)
	25 kW at 415 V AC 50/60 Hz (AC-3e)
	30 kW at 440 V AC 50/60 Hz (AC-3e)
Motor Power Hp	3 hp at 115 V AC 50/60 Hz for 1 phase motors
	7.5 hp at 230/240 V AC 50/60 Hz for 1 phase motors
	15 hp at 200/208 V AC 50/60 Hz for 3 phases motors
	15 hp at 230/240 V AC 50/60 Hz for 3 phases motors
	40 hp at 460/480 V AC 50/60 Hz for 3 phases motors
	40 hp at 575/600 V AC 50/60 Hz for 3 phases motors
Compatibility Code	LC1D
Pole Contact Composition	3 NO
Protective Cover	With

[Ith] Conventional Free Air Thermal Current	10 A (at 60 °C) for signalling circuit 80 A (at 60 °C) for power circuit
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 900 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	900 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	400 A 40 °C - 10 s for power circuit 810 A 40 °C - 1 s for power circuit 84 A 40 °C - 10 min for power circuit 208 A 40 °C - 1 min for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 100 A gG at <= 690 V coordination type 1 for power circuit 100 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	1.5 mOhm - Ith 80 A 50 Hz for power circuit
Power Dissipation Per Pole	3.7 W AC-3 9.6 W AC-1 3.7 W AC-3e
[Ui] Rated Insulation Voltage	Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified Power circuit: 690 V conforming to IEC 60947-4-1
Overvoltage Category	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	10 Mcycles
Electrical Durability	1.45 Mcycles 50 A AC-3 at Ue <= 440 V 0.5 Mcycles 80 A AC-1 at Ue <= 440 V 1.45 Mcycles 50 A AC-3e at Ue <= 440 V
Control Circuit Type	DC standard
Coil Technology	Built-in bidirectional peak limiting diode suppressor
Control Circuit Voltage Limits	0.10.3 Uc (-4070 °C):drop-out DC 0.751.25 Uc (-4060 °C):operational DC 11.25 Uc (6070 °C):operational DC
Inrush Power In W	19 W (at 20 °C)
Hold-In Power Consumption In W	7.4 W at 20 °C
Operating Time	42.557.5 ms closing 1624 ms opening
Time Constant	34 ms
Maximum Operating Rate	3600 cyc/h 60 °C
Connections - Terminals	Control circuit: lugs-ring terminals - external diameter: 8 mm Power circuit: lugs-ring terminals - external diameter: 16.5 mm
Tightening Torque	Control circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver flat Ø 6 mm M3.5 Control circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver Philips No 2 M3.5 Power circuit: 6 N.m - on lugs-ring terminals hexagonal screw head 10 mm M6 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2 Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver pozidriv No 2
Auxiliary Contact Composition	1 NO + 1 NC

Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1
Signalling Circuit Frequency	25400 Hz
Minimum Switching Voltage	17 V for signalling circuit
Minimum Switching Current	5 mA for signalling circuit
Insulation Resistance	> 10 MOhm for signalling circuit
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Mounting Support	Rail Plate

Environment

Standards	CSA C22.2 No 14
	EN 60947-4-1
	EN 60947-5-1
	IEC 60947-4-1
	IEC 60947-5-1
	UL 508
	IEC 60335-1
Product Certifications	LROS (Lloyds register of shipping)
	DNV
	GL
	CCC
	RINA
	CSA
	UL
	GOST
	BV
Ip Degree Of Protection	IP20 front face conforming to IEC 60529
Protective Treatment	TH conforming to IEC 60068-2-30
Climatic Withstand	conforming to IACS E10 exposure to damp heat
	conforming to IEC 60947-1 Annex Q category D exposure to damp heat
Permissible Ambient Air	-4060 °C
Temperature Around The Device	6070 °C with derating
Operating Altitude	03000 m
Fire Resistance	
	850 °C conforming to IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz)
	Vibrations contactor closed (4 Gn, 5300 Hz)
	Shocks contactor closed (15 Gn for 11 ms)
	Shocks contactor open (10 Gn for 11 ms)
Height	122 mm
Width	55 mm
Depth	120 mm
Net Weight	0.93 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6 cm
Package 1 Width	14 cm
Package 1 Length	15 cm

Package 1 Weight

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information