
# **Product datasheet**

Specifications

Sreen Premium<sup>™</sup>



① Discontinued

# TeSys D contactor - 3P(3 NO) -AC-3 - <= 440 V 65 A - 42 V AC 50/60 Hz coil

LC1D65A3D7

Discontinued on: 10 Oct 2020

#### EAN Code: 3389118328259

#### Main

Range	TeSys
Range Of Product	TeSys Deca
Product Or Component Type	Contactor
Device Short Name	LC1D
Contactor Application	Motor control Resistive load
Utilisation Category	AC-3 AC-4 AC-1
Poles Description	3P
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC
[le] Rated Operational Current	80 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 65 A (at <60 °C) at <= 440 V AC AC-3 for power circuit
[Uc] Control Circuit Voltage	42 V AC 50/60 Hz

#### Complementary

Motor Power Kw	11 kW at 400 V AC 50/60 Hz (AC-4) 18.5 kW at 220230 V AC 50/60 Hz (AC-3) 30 kW at 380400 V AC 50/60 Hz (AC-3) 37 kW at 500 V AC 50/60 Hz (AC-3) 37 kW at 660690 V AC 50/60 Hz (AC-3) 18.5 kW at 220230 V AC 50/60 Hz (AC-3e) 30 kW at 380400 V AC 50/60 Hz (AC-3e) 37 kW at 500 V AC 50/60 Hz (AC-3e) 37 kW at 500 V AC 50/60 Hz (AC-3e) 37 kW at 660690 V AC 50/60 Hz (AC-3e)	
Motor Power Hp	40 hp at 460/480 V AC 50/60 Hz for 3 phases motors 5 hp at 115 V AC 50/60 Hz for 1 phase motors 10 hp at 230/240 V AC 50/60 Hz for 1 phase motors 20 hp at 200/208 V AC 50/60 Hz for 3 phases motors 20 hp at 230/240 V AC 50/60 Hz for 3 phases motors 50 hp at 575/600 V AC 50/60 Hz for 3 phases motors	
Compatibility Code	LC1D	
Pole Contact Composition	3 NO	
Protective Cover	With	
[Ith] Conventional Free Air Thermal Current	10 A (at 60 °C) for signalling circuit 80 A (at 60 °C) for power circuit	
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 1000 A at 440 V for power circuit conforming to IEC 60947	

Rated Breaking Capacity	1000 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	640 A 40 °C - 10 s for power circuit 900 A 40 °C - 1 s for power circuit 110 A 40 °C - 10 min for power circuit 260 A 40 °C - 1 min for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 125 A gG at <= 690 V coordination type 1 for power circuit 125 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	1.5 mOhm - Ith 80 A 50 Hz for power circuit
Power Dissipation Per Pole	9.6 W AC-1 6.3 W AC-3
[Ui] Rated Insulation Voltage	Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified Power circuit: 690 V conforming to IEC 60947-4-1
Overvoltage Category	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	6 Mcycles
Electrical Durability	1.4 Mcycles 80 A AC-1 at Ue <= 440 V 1.45 Mcycles 65 A AC-3 at Ue <= 440 V
Control Circuit Type	AC at 50/60 Hz
Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz 0.81.1 Uc (-4060 °C):operational AC 50 Hz 0.851.1 Uc (-4060 °C):operational AC 60 Hz 11.1 Uc (6070 °C):operational AC 50/60 Hz
Inrush Power In Va	140 VA 60 Hz cos phi 0.75 (at 20 °C) 160 VA 50 Hz cos phi 0.75 (at 20 °C)
Hold-In Power Consumption In Va	13 VA 60 Hz cos phi 0.3 (at 20 °C) 15 VA 50 Hz cos phi 0.3 (at 20 °C)
Heat Dissipation	45 W at 50/60 Hz
Operating Time	419 ms opening 1226 ms closing
Maximum Operating Rate	3600 cyc/h 60 °C
Connections - Terminals	Control circuit: spring terminals 1 2.5 mm <sup>2</sup> - cable stiffness: flexible without cable end Control circuit: spring terminals 2 2.5 mm <sup>2</sup> - cable stiffness: flexible without cable end Power circuit: EverLink BTR screw connectors 1 135 mm <sup>2</sup> - cable stiffness: flexible without cable end Power circuit: EverLink BTR screw connectors 2 125 mm <sup>2</sup> - cable stiffness: flexible without cable end Power circuit: EverLink BTR screw connectors 1 135 mm <sup>2</sup> - cable stiffness: flexible with cable end Power circuit: EverLink BTR screw connectors 2 125 mm <sup>2</sup> - cable stiffness: flexible with cable end Power circuit: EverLink BTR screw connectors 2 125 mm <sup>2</sup> - cable stiffness: flexible with cable end Power circuit: EverLink BTR screw connectors 1 135 mm <sup>2</sup> - cable stiffness: solid without cable end Power circuit: EverLink BTR screw connectors 2 125 mm <sup>2</sup> - cable stiffness: solid without cable end Power circuit: EverLink BTR screw connectors 2 125 mm <sup>2</sup> - cable stiffness: solid without cable end

Tightening Torque	Power circuit: 8 N.m - on EverLink BTR screw connectors - cable 2535 mm <sup>2</sup> hexagonal screw head 4 mm Power circuit: 5 N.m - on EverLink BTR screw connectors - cable 2.525 mm <sup>2</sup> hexagonal screw head 4 mm
Auxiliary Contact Composition	1 NO + 1 NC
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1
Signalling Circuit Frequency	25400 Hz
Minimum Switching Voltage	17 V for signalling circuit
Minimum Switching Current	5 mA for signalling circuit
Insulation Resistance	> 10 MOhm for signalling circuit
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Mounting Support	Plate Rail

#### Environment

Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1
	IEC 60947-5-1 UL 508
Product Certifications	UL CSA GOST CCC
Ip Degree Of Protection	IP20 front face conforming to IEC 60529
Protective Treatment	TH conforming to IEC 60068-2-30
Climatic Withstand	conforming to IACS E10 exposure to damp heat conforming to IEC 60947-1 Annex Q category D exposure to damp heat
Permissible Ambient Air Temperature Around The Device	-4060 °C 6070 °C with derating
Operating Altitude	03000 m
Fire Resistance	850 °C conforming to IEC 60695-2-1
Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz) Vibrations contactor closed (4 Gn, 5300 Hz) Shocks contactor closed (15 Gn for 11 ms) Shocks contactor open (10 Gn for 11 ms)
Height	122 mm
Width	55 mm
Depth	120 mm
Net Weight	0.86 kg

#### Environmental

Flame Retardance

V1 conforming to UL 94

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6 cm

Package 1 Width	14 cm
Package 1 Length	15 cm
Package 1 Weight	850 g

### **Contractual warranty**

Warranty

18 months

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information