Product datasheet

Specification





TeSys D contactor - 4P(4 NO) - AC-1 - <= 440 V 20 A - 110 V AC 50/60 Hz coil

Local distributor code: 386105124

LC1DT20F7

EAN Code: 3389110298406

Main

Range	TeSys TeSys Deca	
Range Of Product	TeSys Deca	
Product Or Component Type	Contactor	
Device Short Name	LC1D	
Contactor Application	Resistive load	
Utilisation Category	AC-1	
Poles Description	4P	
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC	
[le] Rated Operational Current	20 A (at <60 °C) at <= 440 V AC AC-1 for power circuit	
[Uc] Control Circuit Voltage	110 V AC 50/60 Hz	

Complementary

,	
Compatibility Code	LC1D
Pole Contact Composition	4 NO
Protective Cover	With
[Ith] Conventional Free Air Thermal Current	10 A (at 60 °C) for signalling circuit 20 A (at 60 °C) for power circuit
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 250 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	250 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand Current	30 A 40 °C - 10 min for power circuit 61 A 40 °C - 1 min for power circuit 105 A 40 °C - 10 s for power circuit 210 A 40 °C - 1 s for power circuit 210 A 40 °C - 1 s for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 25 A gG at <= 690 V coordination type 1 for power circuit 20 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2.5 mOhm - Ith 20 A 50 Hz for power circuit
Power Dissipation Per Pole	1.56 W AC-1

[Ui] Rated Insulation Voltage Overvoltage Category	Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified
	Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified
	Signalling circuit: 600 V CSA certified
	Signalling circuit: 600 V UL certified
	Power circuit: 690 V conforming to IEC 60947-4-1
overvortage Gategory	<u> </u>
	III
Pollution Degree	3
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	15 Mcycles
Control Circuit Type	AC at 50/60 Hz
Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz
-	0.81.1 Uc (-4060 °C):operational AC 50 Hz
	0.851.1 Uc (-4060 °C):operational AC 60 Hz 11.1 Uc (6070 °C):operational AC 50/60 Hz
Inrush Power In Va	70 VA 60 Hz cos phi 0.75 (at 20 °C)
	70 VA 50 Hz cos phi 0.75 (at 20 °C)
Hold-In Power Consumption In Va	7.5 VA 60 Hz cos phi 0.3 (at 20 °C) 7 VA 50 Hz cos phi 0.3 (at 20 °C)
Heat Dissipation	23 W at 50/60 Hz
Operating Time	419 ms opening
	1222 ms closing
Maximum Operating Rate	3600 cyc/h 60 °C
Connections - Terminals	Control circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: flexible with cable end
	Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible without cable end
	Control circuit: screw clamp terminals 2 14 mm² - cable stiffness: flexible without
	cable end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible with cable
	end Control circuit: screw clamp terminals 1 14 mm² - cable stiffness: solid without
	cable end Control circuit: screw clamp terminals 2 14 mm ² - cable stiffness: solid without
	cable end
	Power circuit: screw clamp terminals 1 14 mm ² - cable stiffness: flexible without cable end
	Power circuit: screw clamp terminals 2 14 mm² - cable stiffness: flexible without cable end
	Power circuit: screw clamp terminals 1 14 mm² - cable stiffness: flexible with cable
	end Power circuit: screw clamp terminals 2 12.5 mm² - cable stiffness: flexible with
	cable end Power circuit: screw clamp terminals 1 14 mm² - cable stiffness: solid without cable
	end
	Power circuit: screw clamp terminals 2 14 mm² - cable stiffness: solid without cable end
Tightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm
	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2
	Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2
	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2
	Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2
Auxiliary Contact Composition	1 NO + 1 NC
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1

Minimum Switching Voltage	17 V for signalling circuit	
Minimum Switching Current	5 mA for signalling circuit	
Insulation Resistance	> 10 MOhm for signalling circuit	
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact	
Mounting Support	Rail Plate	

Environment

Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1
	UL 508 IEC 60335-1
Product Certifications	BV GOST LROS (Lloyds register of shipping) DNV UL CSA GL RINA CCC
Ip Degree Of Protection	IP20 front face conforming to IEC 60529
Protective Treatment	TH conforming to IEC 60068-2-30
Climatic Withstand	conforming to IACS E10 exposure to damp heat conforming to IEC 60947-1 Annex Q category D exposure to damp heat
Permissible Ambient Air Temperature Around The Device	-4060 °C 6070 °C with derating
Operating Altitude	03000 m
Fire Resistance	850 °C conforming to IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open (2 Gn, 5300 Hz) Vibrations contactor closed (4 Gn, 5300 Hz) Shocks contactor closed (15 Gn for 11 ms) Shocks contactor open (10 Gn for 11 ms)
Height	85 mm
Width	45 mm
Depth	92 mm
Net Weight	0.365 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	9.5 cm
Package 1 Length	12.0 cm
Package 1 Weight	386.0 g

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information