



TeSys D contactor - 4P(4 NO) -AC-1 - <= 440 V 40 A - 220 V AC 50/60 Hz coil

Local distributor code: 402837017

LC1DT406M7

! Discontinued on: 9 Feb 2023

! Discontinued

EAN Code: 3389110339222

Main

| Range | TeSys TeSys Deca |
|--------------------------------|---|
| Range Of Product | TeSys Deca |
| Product Or Component Type | Contactor |
| Device Short Name | LC1D |
| Contactor Application | Resistive load |
| Utilisation Category | AC-1 AC-3 AC-3e AC-4 |
| Poles Description | 4P |
| [Ue] Rated Operational Voltage | Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC |
| [le] Rated Operational Current | 40 A (at <60 °C) at <= 440 V AC AC-1 for power circuit |
| [Uc] Control Circuit Voltage | 220 V AC 50/60 Hz |

Complementary

| Compatibility Code | LC1D |
|--|---|
| Pole Contact Composition | 4 NO |
| Protective Cover | With |
| [Ith] Conventional Free Air Thermal Current | 10 A (at 60 °C) for signalling circuit 40 A (at 60 °C) for power circuit |
| Irms Rated Making Capacity | 140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 450 A at 440 V for power circuit conforming to IEC 60947 |
| Rated Breaking Capacity | 450 A at 440 V for power circuit conforming to IEC 60947 |
| [Icw] Rated Short-Time Withstand Current | 50 A 40 °C - 10 min for power circuit 120 A 40 °C - 1 min for power circuit 240 A 40 °C - 10 s for power circuit 380 A 40 °C - 1 s for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit |
| Associated Fuse Rating | 10 A gG for signalling circuit conforming to IEC 60947-5-1 63 A gG at <= 690 V coordination type 1 for power circuit 40 A gG at <= 690 V coordination type 2 for power circuit |
| Average Impedance | 2 mOhm - Ith 40 A 50 Hz for power circuit |
| Power Dissipation Per Pole | 3.2 W AC-1 |

| [Ui] Rated Insulation Voltage | Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified |
|--|---|
| | Power circuit: 690 V conforming to IEC 60947-4-1 |
| Overvoltage Category | III. |
| Pollution Degree | 3 |
| [Uimp] Rated Impulse Withstand Voltage | 6 kV conforming to IEC 60947 |
| Safety Reliability Level | B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1 |
| Mechanical Durability | 15 Mcycles |
| Electrical Durability | 1.4 Mcycles 40 A AC-1 at Ue <= 440 V |
| Control Circuit Type | AC at 50/60 Hz |
| Coil Technology | Without built-in suppressor module |
| Control Circuit Voltage Limits | 0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz 0.81.1 Uc (-4060 °C):operational AC 50 Hz 0.851.1 Uc (-4060 °C):operational AC 60 Hz 11.1 Uc (6070 °C):operational AC 50/60 Hz |
| Inrush Power In Va | 70 VA 60 Hz cos phi 0.75 (at 20 °C) 70 VA 50 Hz cos phi 0.75 (at 20 °C) |
| Hold-In Power Consumption In Va | 7.5 VA 60 Hz cos phi 0.3 (at 20 °C) 7 VA 50 Hz cos phi 0.3 (at 20 °C) |
| Heat Dissipation | 23 W at 50/60 Hz |
| Operating Time | 419 ms opening 1222 ms closing |
| Maximum Operating Rate | 3600 cyc/h 60 °C |
| Connections - Terminals | Control circuit: lugs-ring terminals - external diameter: 8 mm Power circuit: lugs-ring terminals - external diameter: 8 mm |
| Tightening Torque | Control circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver flat Ø 6 mm M3.5 Control circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver Philips No 2 M3.5 Control circuit: 1.7 N.m - on lugs-ring terminals - with screwdriver pozidriv No 2 M3.5 Power circuit: 1.8 N.m - on lugs-ring terminals - with screwdriver flat Ø 6 mm M3.5 Power circuit: 1.8 N.m - on lugs-ring terminals - with screwdriver Philips No 2 M3.5 Power circuit: 1.8 N.m - on lugs-ring terminals - with screwdriver pozidriv No 2 M3.5 |
| Auxiliary Contact Composition | 1 NO + 1 NC |
| Auxiliary Contacts Type | type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1 |
| Signalling Circuit Frequency | 25400 Hz |
| Minimum Switching Voltage | 17 V for signalling circuit |
| Minimum Switching Current | 5 mA for signalling circuit |
| Insulation Resistance | > 10 MOhm for signalling circuit |
| Non-Overlap Time | 1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact |
| Mounting Support | Plate Rail |

Environment

| Standards | CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 IEC 60335-1 | |
|--|--|--|
| Product Certifications | GL CCC BV LROS (Lloyds register of shipping) RINA GOST DNV UL CSA | |
| Ip Degree Of Protection | IP20 front face conforming to IEC 60529 | |
| Protective Treatment | TH conforming to IEC 60068-2-30 | |
| Climatic Withstand | conforming to IACS E10 exposure to damp heat conforming to IEC 60947-1 Annex Q category D exposure to damp heat | |
| Permissible Ambient Air Temperature Around The Device | -4060 °C 6070 °C with derating | |
| Operating Altitude | 03000 m | |
| Fire Resistance | 850 °C conforming to IEC 60695-2-1 | |
| Flame Retardance | V1 conforming to UL 94 | |
| Mechanical Robustness | Vibrations contactor open (2 Gn, 5300 Hz) Vibrations contactor closed (4 Gn, 5300 Hz) Shocks contactor closed (15 Gn for 11 ms) Shocks contactor open (8 Gn for 11 ms) | |
| Height | 91 mm | |
| Width | 45 mm | |
| Depth | 99 mm | |
| Net Weight | 0.425 kg | |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|---------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.3 cm |
| Package 1 Width | 9.5 cm |
| Package 1 Length | 11.7 cm |
| Package 1 Weight | 460.0 g |

Contractual warranty

Warranty 18 months

Sustainability Screen Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Reach Free Of Svhc



Pvc Free

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |

17 May 2024