Product datasheet

Specification





REVERSING CONTACTOR 575VAC 9A IEC

Local distributor code: 381822583

LC2D09BL

EAN Code: 3389110541410

Main

mam	
Range	TeSys
	TeSys Deca
Product Name	TeSys D
	TeSys Deca
	•
Product Or Component Type	Reversing contactor
Device Short Name	LC2D
Contrator Application	B. C. J. J.
Contactor Application	Resistive load Motor control
	indica control
Utilisation Category	AC-3
	AC-1 AC-3e
	A0-06
Device Presentation	Preassembled with reversing power busbar
Poles Description	3P
Power Pole Contact Composition	3 NO
[Ue] Rated Operational Voltage	Power circuit; <= 690 V AC 25400 Hz
[oc] Nated Operational Voltage	Power circuit: <= 300 V DC
[le] Rated Operational Current	9 A (at <60 °C) at <= 440 V AC AC-3 for power circuit
	25 A (at <60 °C) at <= 440 V AC AC-1 for power circuit
Motor Power Kw	2.2 kW at 220230 V AC 5060 Hz
	4 kW at 380400 V AC 5060 Hz
	4 kW at 415 V AC 5060 Hz
	4 kW at 440 V AC 5060 Hz
	5.5 kW at 500 V AC 5060 Hz 5.5 kW at 660690 V AC 5060 Hz
Motor Power Hp (UI / Csa)	0.5 hp at 115 V AC 60 Hz for 1 phase motors
	1 hp at 230/240 V AC 60 Hz for 1 phase motors
	2 hp at 200/208 V AC 60 Hz for 3 phases motors 2 hp at 230/240 V AC 60 Hz for 3 phases motors
	5 hp at 460/480 V AC 60 Hz for 3 phases motors
	7.5 hp at 575/600 V AC 60 Hz for 3 phases motors
Control Circuit Type	DC low consumption
[Uc] Control Circuit Voltage	24 V DC
Auxiliary Contact Composition	1 NO + 1 NC
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947
Overvoltage Category	III
[Ith] Conventional Free Air Thermal Current	10 A (at 60 °C) for signalling circuit 25 A (at 60 °C) for power circuit
	23 A (at 00 G) for power circuit
Irms Rated Making Capacity	250 A at 440 V for power circuit conforming to IEC 60947
	140 A AC for signalling circuit conforming to IEC 60947-5-1
	250 A DC for signalling circuit conforming to IEC 60947-5-1
Rated Breaking Capacity	250 A at 440 V for power circuit conforming to IEC 60947
	200 v for power or out of many to 120 00047

[Icw] Rated Short-Time Withstand Current	30 A 40 °C - 10 min for power circuit 61 A 40 °C - 1 min for power circuit 105 A 40 °C - 10 s for power circuit 210 A 40 °C - 1 s for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit				
Associated Fuse Rating	25 A gG at <= 690 V coordination type 1 for power circuit 20 A gG at <= 690 V coordination type 2 for power circuit 10 A gG for signalling circuit conforming to IEC 60947-5-1				
Average Impedance	2.5 mOhm - Ith 25 A 50 Hz for power circuit				
[Ui] Rated Insulation Voltage	Power circuit: 690 V conforming to IEC 60947-4-1 Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified				
Electrical Durability	0.6 Mcycles 25 A AC-1 at Ue <= 440 V 2 Mcycles 9 A AC-3 at Ue <= 440 V 2 Mcycles 9 A AC-3e at Ue <= 440 V				
Power Dissipation Per Pole	0.2 W AC-3 1.56 W AC-1 0.2 W AC-3e				
Front Cover	With				
Interlocking Type	Mechanical				
Mounting Support	Rail Plate				
Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 IEC 60335-1				
Product Certifications	DNV CSA CCC UL GL LROS (Lloyds register of shipping) BV RINA GOST UKCA				
Connections - Terminals	Power circuit: screw clamp terminals 1 cable(s) 14 mm²flexible without cable end Power circuit: screw clamp terminals 2 cable(s) 14 mm²flexible without cable end Power circuit: screw clamp terminals 1 cable(s) 14 mm²flexible with cable end Power circuit: screw clamp terminals 2 cable(s) 12 mm²flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 14 mm²solid Power circuit: screw clamp terminals 2 cable(s) 14 mm²solid Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 12.5 mm²flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²solid Control circuit: screw clamp terminals 2 cable(s) 14 mm²solid				
Tightening Torque	Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Power circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2 Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver pozidriv No 2				
Operating Time	65.4588.55 ms closing 2030 ms opening				

Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1			
Mechanical Durability	30 Mcycles			
Maximum Operating Rate	3600 cyc/h 60 °C			

Complementary

Coil Technology	Built-in bidirectional peak limiting diode suppressor		
Control Circuit Voltage Limits	0.10.3 Uc (-4070 °C):drop-out DC 0.81.25 Uc (-4060 °C):operational DC 11.25 Uc (6070 °C):operational DC		
Time Constant	40 ms		
Inrush Power In W	2.4 W (at 20 °C)		
Hold-In Power Consumption In W	2.4 W at 20 °C		
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1		
Signalling Circuit Frequency	25400 Hz		
Minimum Switching Current	5 mA for signalling circuit		
Minimum Switching Voltage	17 V for signalling circuit		
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact		
Insulation Resistance	> 10 MOhm for signalling circuit		

Environment

Ip Degree Of Protection	IP20 front face conforming to IEC 60529			
Climatic Withstand	conforming to IACS E10 conforming to IEC 60947-1 Annex Q category D			
Protective Treatment	TH conforming to IEC 60068-2-30			
Pollution Degree	3			
Ambient Air Temperature For Operation	mperature For -4060 °C 6070 °C with derating			
Ambient Air Temperature For -6080 °C Storage				
Operating Altitude	03000 m			
Fire Resistance	850 °C conforming to IEC 60695-2-1			
Flame Retardance	V1 conforming to UL 94			
Mechanical Robustness	Vibrations contactor open: 2 Gn, 5300 Hz Vibrations contactor closed: 4 Gn, 5300 Hz Shocks contactor open: 10 Gn for 11 ms Shocks contactor closed: 15 Gn for 11 ms			
Height	77 mm			
Width 90 mm				
Depth 95 mm				
Net Weight	1.017 kg			

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	9.500 cm
Package 1 Width	11.200 cm
Package 1 Length	14.000 cm
Package 1 Weight	1.141 kg
Unit Type Of Package 2	S02
Number Of Units In Package 2	6
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	7.140 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	96
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	122.240 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Pvc Free	


Certifications & Standards


Reach Regulation	REACh Declaration				
Eu Rohs Directive	Compliant with Exemptions				
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information				
Environmental Disclosure	Product Environmental Profile				
Circularity Profile	End of Life Information				

LC2D09BL

Dimensions Drawings

Dimensions





LC2 or 2 x LC1	а	b	c ⁽¹⁾	e1	e2	G
D09 to D18 (AC)	90	77	86	4	1.5	80
D093 to D123 (AC)	90	99	86	_	_	80
D09 to D18 (DC)	90	77	95	4	1.5	80
D093 to D123 (DC)	90	99	95	_	_	80
D25 to D38 (AC)	90	85	92	9	5	80
D183 to D383 (AC)	90	99	92	_	_	80
D25 to D32 (DC)	90	85	101	9	5	80
D183 to D383 (DC)	90	99	101	_	_	80

e1 and e2: including cabling.

(1) With safety cover, without add-on block.

Product datasheet

LC2D09BL

Connections and Schema

Wiring

