



# TeSys F contactor - 3P (3 NO) - AC-3 - <= 440 V 115 A - coil 115 V AC

LC1F115FE5

! Discontinued on: 10 Oct 2020

① Discontinued

EAN Code: 3389110074826

#### Main

Range	TaCira	
nange	TeSys	
Range Of Product	TeSys F	
Product Or Component Type	Contactor	
Device Short Name	LC1F	
Contactor Application	Resistive load Motor control	
Utilisation Category	AC-1 AC-4 AC-3	
Poles Description	3P	
[Ue] Rated Operational Voltage	<= 690 V AC 50/60 Hz <= 460 V DC	
[Uc] Control Circuit Voltage	115 V AC 50 Hz	
[le] Rated Operational Current	200 A (at <40 °C) at <= 440 V AC-1 115 A (at <55 °C) at <= 440 V AC-3	

### Complementary

Fillian 2 Data di Imanda a Milita da di	
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ith] Conventional Free Air Thermal Current	200 A (at 40 °C)
Rated Breaking Capacity	920 A conforming to IEC 60947-4-1
[Icw] Rated Short-Time Withstand	1100 A 40 °C - 10 s
Current	640 A 40 °C - 30 s
	520 A 40 °C - 1 min
	400 A 40 °C - 3 min
	320 A 40 °C - 10 min
Associated Fuse Rating	125 A aM at <= 440 V
	200 A gG at <= 440 V
Average Impedance	0.37 mOhm - Ith 200 A 50 Hz
[Ui] Rated Insulation Voltage	1000 V conforming to IEC 60947-4-1
	1500 V conforming to VDE 0110 group C
Power Dissipation Per Pole	15 W AC-1
	5 W AC-3
Overvoltage Category	III
Power Pole Contact Composition	3 NO

Motor Power Kw	55 kW at 380400 V AC 50/60 Hz (AC-3)
	59 kW at 415 V AC 50/60 Hz (AC-3)
	59 kW at 440 V AC 50/60 Hz (AC-3)
	75 kW at 500 V AC 50/60 Hz (AC-3)
	80 kW at 660690 V AC 50/60 Hz (AC-3)
	30 kW at 220230 V AC 50/60 Hz (AC-3)
	18.5 kW at 400 V AC 50/60 Hz (AC-4)
Control Circuit Voltage Limits	Operational: 0.851.1 Uc 50/60 Hz (at 55 °C)
-	Drop-out: 0.350.55 Uc 50/60 Hz (at 55 °C)
Mechanical Durability	10 Mcycles
Inrush Power In Va	550 VA, 50 Hz cos phi 0.3 (at 20 °C)
Hold-In Power Consumption In Va	45 VA, 50 Hz cos phi 0.3 (at 20 °C)
Maximum Operating Rate	2400 cyc/h 55 °C
Operating Time	2335 ms closing
	515 ms opening
Connections - Terminals	Power circuit: bar 2 cable(s) - busbar cross section: 20 x 3 mm
	Power circuit: lugs-ring terminals 1 cable(s) 95 mm²
	Power circuit: connector 1 cable(s) 95 mm <sup>2</sup>
	Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible without cable end
	Control circuit: screw clamp terminals 2 cable(s) 14 mm²flexible without cable end
	Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible with cable end
	Control circuit: screw clamp terminals 2 cable(s) 12.5 mm²flexible with cable end
	Control circuit: screw clamp terminals 1 cable(s) 14 mm²solid without cable end
	Control circuit: screw clamp terminals 2 cable(s) 14 mm²solid without cable end
	Power circuit: bolted connection
Tightening Torque	Power circuit: 10 N.m
	Control circuit: 1.2 N.m
Mounting Support	Plate
Heat Dissipation	1216 W
Standards	JIS C8201-4-1
	IEC 60947-4-1
	EN 60947-4-1
	IEC 60947-1
	EN 60947-1
Product Certifications	CCC
	BV
	RMRoS
	DNV
	CB
	RINA
	ABS
	LROS (Lloyds register of shipping)
	UL
Compatibility Code	LC1F
Control Circuit Type	AC at 50 Hz
Environment	
Ip Degree Of Protection	IP2X front face with shrouds conforming to IEC 60529 IP2X front face with shrouds conforming to VDE 0106
Protective Treatment	тн
Ambient Air Temperature For	-4060 °C
Operation  Ambient Air Temperature For	-6080 °C
Storage	
Permissible Ambient Air Temperature Around The Device	6070 °C at Uc
Height	162 mm

163.3 mm

171 mm

Width

Depth

Operating Altitude	3000 m without derating
Net Weight	3.43 kg

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.5 cm
Package 1 Width	21 cm
Package 1 Length	24.5 cm
Package 1 Weight	4.112 kg

## **Contractual warranty**

Warranty 18 months

## Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information