# **Product datasheet**

Specification





TeSys F contactor - 3P (3 NO) - AC-3 - <= 440 V 115 A - coil 200...208 V AC

LC1F115L6

! Discontinued on: 22 Dec 2020

(!) Discontinued

EAN Code: 3389110226553

#### Main

Range	TeSys	
Range Of Product	TeSys F	
Product Or Component Type	Contactor	
Device Short Name	LC1F	
Contactor Application	Motor control Resistive load	
Utilisation Category	AC-3 AC-4 AC-1	
Poles Description	3P	
[Ue] Rated Operational Voltage	<= 690 V AC 50/60 Hz <= 460 V DC	
[Uc] Control Circuit Voltage	200208 V AC 60 Hz	
[le] Rated Operational Current	200 A (at <40 °C) at <= 440 V AC-1 115 A (at <55 °C) at <= 440 V AC-3	

### Complementary

[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ith] Conventional Free Air Thermal Current	200 A (at 40 °C)
Rated Breaking Capacity	920 A conforming to IEC 60947-4-1
[Icw] Rated Short-Time Withstand Current	1100 A 40 °C - 10 s 640 A 40 °C - 30 s 520 A 40 °C - 1 min 400 A 40 °C - 3 min 320 A 40 °C - 10 min
Associated Fuse Rating	125 A aM at <= 440 V 200 A gG at <= 440 V
Average Impedance	0.37 mOhm - Ith 200 A 50 Hz
[Ui] Rated Insulation Voltage	1000 V conforming to IEC 60947-4-1 1500 V conforming to VDE 0110 group C
Power Dissipation Per Pole	15 W AC-1 5 W AC-3
Overvoltage Category	III
Power Pole Contact Composition	3 NO

Motor Power Kw	55 kW at 380400 V AC 50/60 Hz (AC-3) 59 kW at 415 V AC 50/60 Hz (AC-3) 59 kW at 440 V AC 50/60 Hz (AC-3) 75 kW at 500 V AC 50/60 Hz (AC-3)
	80 kW at 660690 V AC 50/60 Hz (AC-3) 30 kW at 220230 V AC 50/60 Hz (AC-3) 18.5 kW at 400 V AC 50/60 Hz (AC-4)
Control Circuit Voltage Limits	Operational: 0.851.1 Uc 50/60 Hz (at 55 °C) Drop-out: 0.350.55 Uc 50/60 Hz (at 55 °C)
Mechanical Durability	10 Mcycles
Inrush Power In Va	660 VA, 60 Hz cos phi 0.3 (at 20 °C)
Hold-In Power Consumption In Va	55 VA, 60 Hz cos phi 0.3 (at 20 °C)
Maximum Operating Rate	2400 cyc/h 55 °C
Operating Time	2335 ms closing 515 ms opening
Connections - Terminals	Power circuit: bar 2 cable(s) - busbar cross section: 20 x 3 mm  Power circuit: lugs-ring terminals 1 cable(s) 95 mm²  Power circuit: connector 1 cable(s) 95 mm²  Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 125 mm²flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²solid without cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm²solid without cable end Power circuit: bolted connection
Tightening Torque	Power circuit: 10 N.m Control circuit: 1.2 N.m
Mounting Support	Plate
Heat Dissipation	1216 W
Standards	IEC 60947-4-1 JIS C8201-4-1 IEC 60947-1 EN 60947-4-1 EN 60947-1
Product Certifications	CB RINA LROS (Lloyds register of shipping) CCC BV UL DNV RMRoS ABS
Compatibility Code	LC1F
Control Circuit Type	AC at 60 Hz
Environment	
Ip Degree Of Protection	IP2X front face with shrouds conforming to IEC 60529 IP2X front face with shrouds conforming to VDE 0106
Protective Treatment	TH
Ambient Air Temperature For Operation	-4060 °C
Ambient Air Temperature For Storage	-6080 °C
Permissible Ambient Air Temperature Around The Device	6070 °C at Uc
Hoight	400

162 mm

163.3 mm

171 mm

Height

Width

Depth

Operating Altitude	3000 m without derating
Net Weight	3.43 kg

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21 cm
Package 1 Width	22 cm
Package 1 Length	24 cm
Package 1 Weight	3.43 kg

## **Contractual warranty**

Warranty 18 months

## Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information