Product datasheet

Specifications

Sreen Premium[™]



TeSys D reversing contactor -3P(3 NO) - AC-3 - <= 440 V 25 A -415 V AC coil

LC2D25N7

Discontinued on: 10 Oct 2020

① Discontinued

EAN Code: 3389110391268

Main

Range	TeSys	
Product Name	TeSys Deca	
Product Or Component Type	Reversing contactor	
Device Short Name	LC2D	
Contactor Application	Resistive load	
	Motor control	
Utilisation Category	AC-1	
	AC-3	
Device Presentation	Preassembled with reversing power busbar	
Poles Description	3P	
Power Pole Contact Composition	3 NO	
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC	
[1a] Dated On anational Oursent		
[Ie] Rated Operational Current	25 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 40 A (at <60 °C) at <= 440 V AC AC-1 for power circuit	
Motor Power Kw	5.5 kW at 220230 V AC 50 Hz	
	11 kW at 380400 V AC 50 Hz	
	11 kW at 415440 V AC 50 Hz	
	15 kW at 500 V AC 50 Hz	
	15 kW at 660690 V AC 50 Hz	
Motor Power Hp (UI / Csa)	3 hp at 230/240 V AC 60 Hz for 1 phase motors	
	5 hp at 200/208 V AC 60 Hz for 3 phases motors	
	2 hp at 115 V AC 60 Hz for 1 phase motors	
	7.5 hp at 230/240 V AC 60 Hz for 3 phases motors	
	15 hp at 460/480 V AC 60 Hz for 3 phases motors	
	20 hp at 575/600 V AC 60 Hz for 3 phases motors	
Control Circuit Type	AC at 50/60 Hz	
[Uc] Control Circuit Voltage	415 V AC 50/60 Hz	
Auxiliary Contact Composition	1 NO + 1 NC	
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947	
Overvoltage Category	III	
[Ith] Conventional Free Air	10 A (at 60 °C) for signalling circuit	
Thermal Current	40 A (at 60 °C) for power circuit	
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1	
	250 A DC for signalling circuit conforming to IEC 60947-5-1	
	450 A at 440 V for power circuit conforming to IEC 60947	
Rated Breaking Capacity	450 A at 440 V for power circuit conforming to IEC 60947	

[Icw] Rated Short-Time Withstand Current	50 A 40 °C - 10 min for power circuit 120 A 40 °C - 1 min for power circuit 240 A 40 °C - 10 s for power circuit
	380 A 40 °C - 1 s for power circuit
	100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
J	63 A gG at <= 690 V coordination type 1 for power circuit
	40 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2 mOhm - Ith 40 A 50 Hz for power circuit
[Ui] Rated Insulation Voltage	Power circuit: 690 V conforming to IEC 60947-4-1 Power circuit: 600 V CSA certified
	Power circuit: 600 V UL certified
	Signalling circuit: 690 V conforming to IEC 60947-1
	Signalling circuit: 600 V CSA certified
	Signalling circuit: 600 V UL certified
Electrical Durability	1.65 Mcycles 25 A AC-3 at Ue <= 440 V 1.4 Mcycles 40 A AC-1 at Ue <= 440 V
Power Dissipation Per Pole	1.25 W AC-3
	3.2 W AC-1
Front Cover	With
Interlocking Type	Mechanical
Mounting Support	Plate Rail
Standards	CSA C22.2 No 14
	EN 60947-4-1 EN 60947-5-1
	IEC 60947-4-1
	IEC 60947-5-1
	UL 508
Product Certifications	BV RINA
	LROS (Lloyds register of shipping)
	CCC
	DNV
	GL UL
	GOST
	CSA
Connections - Terminals	Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible without cable end
	Control circuit: screw clamp terminals 2 cable(s) 14 mm ² flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm ² flexible with cable end
	Control circuit: screw clamp terminals 2 cable(s) 12.5 mm ² flexible with cable end
	Control circuit: screw clamp terminals 1 cable(s) 14 mm ² solid
	Control circuit: screw clamp terminals 2 cable(s) 14 mm ² solid
	Power circuit: screw clamp terminals 1 cable(s) 2.510 mm ² flexible without cable end
	Power circuit: screw clamp terminals 2 cable(s) 2.510 mm ² flexible without cable
	end
	Power circuit: screw clamp terminals 1 cable(s) 110 mm ² flexible with cable end Power circuit: screw clamp terminals 2 cable(s) 1.56 mm ² flexible with cable end
	Power circuit: screw clamp terminals 2 cable(s) 1.510 mm ² solid
	Power circuit: screw clamp terminals 2 cable(s) 2.510 mm ² solid
Tightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm
	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2
	Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver Philips No 2
Operating Time	1222 ms closing
	419 ms opening
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1
	B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	15 Mcycles

Complementary

Coil Technology	Without built-in suppressor module	
Control Circuit Voltage Limits	0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz	
	0.81.1 Uc (-4060 °C):operational AC 50 Hz	
	0.851.1 Uc (-4060 °C):operational AC 60 Hz	
	11.1 Uc (6070 °C):operational AC 50/60 Hz	
Inrush Power In Va	70 VA 60 Hz cos phi 0.75 (at 20 °C)	
	70 VA 50 Hz cos phi 0.75 (at 20 °C)	
Hold-In Power Consumption In Va	7.5 VA 60 Hz cos phi 0.3 (at 20 °C)	
	7 VA 50 Hz cos phi 0.3 (at 20 °C)	
Heat Dissipation	23 W at 50/60 Hz	
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1	
	type mirror contact 1 NC conforming to IEC 60947-4-1	
Signalling Circuit Frequency	25400 Hz	
Minimum Switching Current	5 mA for signalling circuit	
Minimum Switching Voltage	17 V for signalling circuit	
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact	
	1.5 ms on energisation between NC and NO contact	
Insulation Resistance	> 10 MOhm for signalling circuit	

Environment

Ip Degree Of Protection	IP20 front face conforming to IEC 60529	
Climatic Withstand	conforming to IACS E10 conforming to IEC 60947-1 Annex Q category D	
Protective Treatment	TH conforming to IEC 60068-2-30	
Pollution Degree	3	
Ambient Air Temperature For Operation	-4060 °C 6070 °C with derating	
Ambient Air Temperature For Storage	-6080 °C	
Operating Altitude	03000 m	
Fire Resistance	850 °C conforming to IEC 60695-2-1	
Flame Retardance	V1 conforming to UL 94	
Mechanical Robustness	Vibrations contactor open: 2 Gn, 5300 Hz Vibrations contactor closed: 4 Gn, 5300 Hz Shocks contactor closed: 15 Gn for 11 ms Shocks contactor open: 8 Gn for 11 ms	
Height	85 mm	
Width	90 mm	
Depth	92 mm	
Net Weight	0.787 kg	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.9 cm

Package 1 Width	11.4 cm
Package 1 Length	11.8 cm
Package 1 Weight	815 g

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information