# **Product datasheet**

Specification





# TeSys D reversing contactor - 3P(3 NO) - AC-3 - <= 440 V 25 A - 230 V AC coil

Local distributor code: 381823414

LC2D25P7

EAN Code: 3389110391275

#### Main

wain					
Range	TeSys TeSys Deca				
Product Name	TeSys D TeSys Deca				
Product Or Component Type	Reversing contactor				
Device Short Name	LC2D				
Contactor Application	Motor control Resistive load				
Utilisation Category	AC-1 AC-3 AC-3e				
Device Presentation	Preassembled with reversing power busbar				
Poles Description	3P				
Power Pole Contact Composition	3 NO				
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC				
[le] Rated Operational Current	25 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 40 A (at <60 °C) at <= 440 V AC AC-1 for power circuit				
Motor Power Kw	5.5 kW at 220230 V AC 5060 Hz 11 kW at 380400 V AC 5060 Hz 11 kW at 415 V AC 5060 Hz 11 kW at 440 V AC 5060 Hz 15 kW at 500 V AC 5060 Hz 15 kW at 660690 V AC 5060 Hz				
Motor Power Hp (UI / Csa)	3 hp at 230/240 V AC 60 Hz for 1 phase motors 5 hp at 200/208 V AC 60 Hz for 3 phases motors 2 hp at 115 V AC 60 Hz for 1 phase motors 7.5 hp at 230/240 V AC 60 Hz for 3 phases motors 15 hp at 460/480 V AC 60 Hz for 3 phases motors 20 hp at 575/600 V AC 60 Hz for 3 phases motors				
Control Circuit Type	AC at 50/60 Hz				
[Uc] Control Circuit Voltage	230 V AC 50/60 Hz				
Auxiliary Contact Composition	1 NO + 1 NC				
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947				
Overvoltage Category	III				
[lth] Conventional Free Air Thermal Current	10 A (at 60 °C) for signalling circuit 40 A (at 60 °C) for power circuit				
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 450 A at 440 V for power circuit conforming to IEC 60947				
Rated Breaking Capacity	450 A at 440 V for power circuit conforming to IEC 60947				

[Icw] Rated Short-Time Withstand Current	50 A 40 °C - 10 min for power circuit 120 A 40 °C - 1 min for power circuit 240 A 40 °C - 10 s for power circuit 380 A 40 °C - 1 s for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit				
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 63 A gG at <= 690 V coordination type 1 for power circuit 40 A gG at <= 690 V coordination type 2 for power circuit				
Average Impedance	2 mOhm - Ith 40 A 50 Hz for power circuit				
[Ui] Rated Insulation Voltage	Power circuit: 690 V conforming to IEC 60947-4-1 Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified				
Electrical Durability	1.65 Mcycles 25 A AC-3 at Ue <= 440 V 1.4 Mcycles 40 A AC-1 at Ue <= 440 V 1.65 Mcycles 25 A AC-3e at Ue <= 440 V				
Power Dissipation Per Pole	1.25 W AC-3 3.2 W AC-1 1.25 W AC-3e				
Front Cover	With				
Interlocking Type	Mechanical				
Mounting Support	Rail Plate				
Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 IEC 60335-1				
Product Certifications	DNV CSA CCC UL GL LROS (Lloyds register of shipping) BV RINA GOST UKCA CB				
Connections - Terminals	Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 12.5 mm²flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²solid Control circuit: screw clamp terminals 2 cable(s) 14 mm²solid Power circuit: screw clamp terminals 1 cable(s) 2.510 mm²flexible without cable end Power circuit: screw clamp terminals 2 cable(s) 2.510 mm²flexible without cable end Power circuit: screw clamp terminals 1 cable(s) 110 mm²flexible with cable end Power circuit: screw clamp terminals 2 cable(s) 1.56 mm²flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 1.510 mm²solid Power circuit: screw clamp terminals 2 cable(s) 2.510 mm²solid				
Tightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver Philips No 2 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2 Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver pozidriv No 2				
Operating Time	1222 ms closing 419 ms opening				

Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1	
Mechanical Durability	15 Mcycles	
Maximum Operating Rate	3600 cyc/h 60 °C	

# Complementary

Coil Technology	Without built-in suppressor module				
Control Circuit Voltage Limits	0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz 0.81.1 Uc (-4060 °C):operational AC 50 Hz 0.851.1 Uc (-4060 °C):operational AC 60 Hz 11.1 Uc (6070 °C):operational AC 50/60 Hz				
Inrush Power In Va	70 VA 60 Hz cos phi 0.75 (at 20 °C) 70 VA 50 Hz cos phi 0.75 (at 20 °C)				
Hold-In Power Consumption In Va	7.5 VA 60 Hz cos phi 0.3 (at 20 °C) 7 VA 50 Hz cos phi 0.3 (at 20 °C)				
Heat Dissipation	23 W at 50/60 Hz				
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1				
Signalling Circuit Frequency	25400 Hz				
Minimum Switching Current	5 mA for signalling circuit				
Minimum Switching Voltage	17 V for signalling circuit				
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact				
nsulation Resistance > 10 MOhm for signalling circuit					

## **Environment**

IP20 front face conforming to IEC 60529				
conforming to IACS E10 conforming to IEC 60947-1 Annex Q category D				
TH conforming to IEC 60068-2-30				
3				
-4060 °C 6070 °C with derating				
-6080 °C				
03000 m				
850 °C conforming to IEC 60695-2-1				
V1 conforming to UL 94				
Vibrations contactor open: 2 Gn, 5300 Hz Vibrations contactor closed: 4 Gn, 5300 Hz Shocks contactor closed: 15 Gn for 11 ms Shocks contactor open: 8 Gn for 11 ms				
85 mm				
90 mm				
92 mm				
0.787 kg				

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.500 cm
Package 1 Width	11.500 cm
Package 1 Length	14.600 cm
Package 1 Weight	942.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	5
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.115 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Reach Free Of Svhc



Pvc Free


#### **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

## LC2D25P7

#### **Dimensions Drawings**

#### **Dimensions**





LC2 or 2 x LC1	а	b	c <sup>(1)</sup>	e1	e2	G
D09 to D18 (AC)	90	77	86	4	1.5	80
D093 to D123 (AC)	90	99	86	_	_	80
D09 to D18 (DC)	90	77	95	4	1.5	80
D093 to D123 (DC)	90	99	95	_	_	80
D25 to D38 (AC)	90	85	92	9	5	80
D183 to D383 (AC)	90	99	92	_	_	80
D25 to D32 (DC)	90	85	101	9	5	80
D183 to D383 (DC)	90	99	101	_	_	80

e1 and e2: including cabling.

(1) With safety cover, without add-on block.

Connections and Schema

Wiring

