# **Product datasheet**

Specification





# REVERSING CONTACTOR 575VAC 32A IEC

Local distributor code: 381823443

LC2D32B7

EAN Code: 3389110391459

#### Main

Mani					
Range	TeSys TeSys Deca				
Product Name	TeSys D TeSys Deca				
Product Or Component Type	Reversing contactor				
Device Short Name	LC2D				
Contactor Application	Resistive load Motor control				
Utilisation Category	AC-1 AC-3 AC-3e				
Device Presentation	Preassembled with reversing power busbar				
Poles Description	3P				
Power Pole Contact Composition	3 NO				
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC				
[le] Rated Operational Current	32 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 50 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 32 A (at <60 °C) at <= 440 V AC AC-3e for power circuit				
Motor Power Kw	7.5 kW at 220230 V AC 5060 Hz 15 kW at 380400 V AC 5060 Hz 15 kW at 415 V AC 5060 Hz 15 kW at 440 V AC 5060 Hz 18.5 kW at 500 V AC 5060 Hz 18.5 kW at 660690 V AC 5060 Hz				
Motor Power Hp (UI / Csa)	2 hp at 115 V AC 60 Hz for 1 phase motors 5 hp at 230/240 V AC 60 Hz for 1 phase motors 10 hp at 200/208 V AC 60 Hz for 3 phases motors 10 hp at 230/240 V AC 60 Hz for 3 phases motors 20 hp at 460/480 V AC 60 Hz for 3 phases motors 30 hp at 575/600 V AC 60 Hz for 3 phases motors				
Control Circuit Type	AC at 50/60 Hz				
[Uc] Control Circuit Voltage	24 V AC 50/60 Hz				
Auxiliary Contact Composition	1 NO + 1 NC				
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947				
Overvoltage Category	III				
[Ith] Conventional Free Air Thermal Current	10 A (at 60 °C) for signalling circuit 50 A (at 60 °C) for power circuit				
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 550 A at 440 V for power circuit conforming to IEC 60947				

Rated Breaking Capacity	550 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand	60 A 40 °C - 10 min for power circuit
Current	138 A 40 °C - 1 min for power circuit
	260 A 40 °C - 10 s for power circuit
	430 A 40 °C - 1 s for power circuit
	100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
	63 A gG at <= 690 V coordination type 1 for power circuit
	63 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2 mOhm - Ith 50 A 50 Hz for power circuit
[Ui] Rated Insulation Voltage	Power circuit: 690 V conforming to IEC 60947-4-1
	Power circuit: 600 V CSA certified
	Power circuit: 600 V UL certified
	Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified
	Signalling circuit: 600 V UL certified
Electrical Durability	1.65 Mcycles 32 A AC-3 at Ue <= 440 V
•	1.4 Mcycles 50 A AC-1 at Ue <= 440 V
	1.65 Mcycles 32 A AC-3e at Ue <= 440 V
Power Dissipation Per Pole	2 W AC-3
	5 W AC-1
	2 W AC-3e
Front Cover	With
Interlocking Type	Mechanical
Mounting Support	Rail Plate
Standards	CSA C22.2 No 14
	EN 60947-4-1
	EN 60947-5-1
	IEC 60947-4-1
	IEC 60947-5-1
	UL 508 IEC 60335-1
Does does to Combiff a string a	
Product Certifications	UL CSA
	RINA
	GOST
	CCC
	DNV
	LROS (Lloyds register of shipping)
	GL
	BV
	UKCA CB
Connections - Terminals	Control circuit screw clamp terminals 1 coble(s) 1 . 4 mm²/lovible without coble and
Connections - Terminals	Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm²flexible without cable end
	Control circuit: screw clamp terminals 2 cable(s) 14 mm resible without cable end
	Control circuit: screw clamp terminals 1 cable(s) 12.5 mm²flexible with cable end
	Control circuit: screw clamp terminals 1 cable(s) 14 mm²solid
	Control circuit: screw clamp terminals 2 cable(s) 14 mm²solid
	Power circuit: screw clamp terminals 1 cable(s) 2.510 mm²flexible without cable
	end
	Power circuit: screw clamp terminals 2 cable(s) 2.510 mm²flexible without cable
	end  Power circuit: cerew clamp terminals 1 cable(s) 1 10 mm²flevible with cable and
	Power circuit: screw clamp terminals 1 cable(s) 110 mm²flexible with cable end Power circuit: screw clamp terminals 2 cable(s) 1.56 mm²flexible with cable end
	Power circuit: screw clamp terminals 2 cable(s) 1.510 mm²solid  Power circuit: screw clamp terminals 1 cable(s) 1.510 mm²solid
	Power circuit: screw clamp terminals 2 cable(s) 2.510 mm²solid
Tightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm
	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2
	Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm
	Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver Philips No 2
	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2
	Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver pozidriv No 2

Operating Time	1222 ms closing 419 ms opening
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	15 Mcycles
Maximum Operating Rate	3600 cyc/h 60 °C

# Complementary

Coil Technology	Without built-in suppressor module				
Control Circuit Voltage Limits	0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz 0.81.1 Uc (-4060 °C):operational AC 50 Hz 0.851.1 Uc (-4060 °C):operational AC 60 Hz 11.1 Uc (6070 °C):operational AC 50/60 Hz				
Inrush Power In Va	70 VA 60 Hz cos phi 0.75 (at 20 °C) 70 VA 50 Hz cos phi 0.75 (at 20 °C)				
Hold-In Power Consumption In Va	7.5 VA 60 Hz cos phi 0.3 (at 20 °C) 7 VA 50 Hz cos phi 0.3 (at 20 °C)				
Heat Dissipation	23 W at 50/60 Hz				
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1				
Signalling Circuit Frequency	25400 Hz				
Minimum Switching Current	5 mA for signalling circuit				
Minimum Switching Voltage	17 V for signalling circuit				
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact     1.5 ms on energisation between NC and NO contact				
Insulation Resistance	> 10 MOhm for signalling circuit				

## **Environment**

Ip Degree Of Protection	IP20 front face conforming to IEC 60529			
Climatic Withstand	conforming to IACS E10 conforming to IEC 60947-1 Annex Q category D			
Protective Treatment	TH conforming to IEC 60068-2-30			
Pollution Degree	3			
Ambient Air Temperature For Operation	-4060 °C 6070 °C with derating			
Ambient Air Temperature For Storage	-6080 °C			
Operating Altitude	03000 m			
Fire Resistance	850 °C conforming to IEC 60695-2-1			
Flame Retardance	V1 conforming to UL 94			
Mechanical Robustness	Vibrations contactor open: 2 Gn, 5300 Hz Vibrations contactor closed: 4 Gn, 5300 Hz Shocks contactor closed: 15 Gn for 11 ms Shocks contactor open: 8 Gn for 11 ms			
Height	85 mm			
Width	90 mm			
Depth	92 mm			
Net Weight	0.797 kg			

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	12.5 cm
Package 1 Length	14.0 cm
Package 1 Weight	952.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	5
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.09 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Reach Free Of Svhc



Pvc Free


#### **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

## LC2D32B7

#### **Dimensions Drawings**

#### **Dimensions**





LC2 or 2 x LC1	а	b	c <sup>(1)</sup>	e1	e2	G
D09 to D18 (AC)	90	77	86	4	1.5	80
D093 to D123 (AC)	90	99	86	_	_	80
D09 to D18 (DC)	90	77	95	4	1.5	80
D093 to D123 (DC)	90	99	95	_	_	80
D25 to D38 (AC)	90	85	92	9	5	80
D183 to D383 (AC)	90	99	92	_	_	80
D25 to D32 (DC)	90	85	101	9	5	80
D183 to D383 (DC)	90	99	101	_	_	80

e1 and e2: including cabling.

(1) With safety cover, without add-on block.

Connections and Schema

Wiring

