Product datasheet

Specifications





REVERSING CONTACTOR 575VAC 25A IEC

Local distributor code: 381823236

LC2D25BL

EAN Code: 3389110543193

Main

Range	TeSys TeSys Deca
Product Name	TeSys D TeSys Deca
Product Or Component Type	Reversing contactor
Device Short Name	LC2D
Contactor Application	Resistive load Motor control
Utilisation Category	AC-1 AC-3 AC-3e
Device Presentation	Preassembled with reversing power busbar
Poles Description	3P
Power Pole Contact Composition	3 NO
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC
[le] Rated Operational Current	25 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 40 A (at <60 °C) at <= 440 V AC AC-1 for power circuit
Motor Power Kw	5.5 kW at 220230 V AC 5060 Hz 11 kW at 380400 V AC 5060 Hz 11 kW at 415 V AC 5060 Hz 11 kW at 440 V AC 5060 Hz 15 kW at 500 V AC 5060 Hz 15 kW at 660690 V AC 5060 Hz
Motor Power Hp (UI / Csa)	3 hp at 230/240 V AC 60 Hz for 1 phase motors 5 hp at 200/208 V AC 60 Hz for 3 phases motors 2 hp at 115 V AC 60 Hz for 1 phase motors 7.5 hp at 230/240 V AC 60 Hz for 3 phases motors 15 hp at 460/480 V AC 60 Hz for 3 phases motors 20 hp at 575/600 V AC 60 Hz for 3 phases motors
Control Circuit Type	DC low consumption
[Uc] Control Circuit Voltage	24 V DC
Auxiliary Contact Composition	1 NO + 1 NC
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947
Overvoltage Category	111
[Ith] Conventional Free Air Thermal Current	10 A (at 60 °C) for signalling circuit 40 A (at 60 °C) for power circuit
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 450 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	450 A at 440 V for power circuit conforming to IEC 60947

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Icw] Rated Short-Time Withstand Current	50 A 40 °C - 10 min for power circuit 120 A 40 °C - 1 min for power circuit 240 A 40 °C - 10 s for power circuit 380 A 40 °C - 1 s for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 63 A gG at <= 690 V coordination type 1 for power circuit 40 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2 mOhm - Ith 40 A 50 Hz for power circuit
[Ui] Rated Insulation Voltage	Power circuit: 690 V conforming to IEC 60947-4-1 Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified
Electrical Durability	1.65 Mcycles 25 A AC-3 at Ue <= 440 V 1.4 Mcycles 40 A AC-1 at Ue <= 440 V 1.65 Mcycles 25 A AC-3e at Ue <= 440 V
Power Dissipation Per Pole	1.25 W AC-3 3.2 W AC-1 1.25 W AC-3e
Front Cover	With
Interlocking Type	Mechanical
Mounting Support	Rail Plate
Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 IEC 60335-1
Product Certifications	DNV CSA CCC UL GL LROS (Lloyds register of shipping) BV RINA GOST UKCA CB
Connections - Terminals	Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 12.5 mm²flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm²flexible without cable end Power circuit: screw clamp terminals 2 cable(s) 2.510 mm²flexible without cable end Power circuit: screw clamp terminals 1 cable(s) 2.510 mm²flexible without cable end Power circuit: screw clamp terminals 1 cable(s) 110 mm²flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 110 mm²flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 110 mm²flexible with cable end Power circuit: screw clamp terminals 2 cable(s) 1.56 mm²flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 1.510 mm²flexible with cable end Power circuit: screw clamp terminals 2 cable(s) 1.510 mm²flexible with cable end Power circuit: screw clamp terminals 2 cable(s) 1.510 mm²flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 1.510 mm²solid
Tightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver Philips No 2 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2 Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver pozidriv No 2
Operating Time	65.4588.55 ms closing 2030 ms opening

Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	30 Mcycles
Maximum Operating Rate	3600 cyc/h 60 °C

Complementary

Coil Technology	Built-in bidirectional peak limiting diode suppressor					
Control Circuit Voltage Limits	0.10.3 Uc (-4070 °C):drop-out DC 0.81.25 Uc (-4060 °C):operational DC 11.25 Uc (6070 °C):operational DC					
Time Constant	40 ms					
Inrush Power In W	2.4 W (at 20 °C)					
Hold-In Power Consumption In W	2.4 W at 20 °C					
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1					
Signalling Circuit Frequency	25400 Hz					
Minimum Switching Current	5 mA for signalling circuit					
Minimum Switching Voltage	17 V for signalling circuit					
Non-Overlap Time	 1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact 					
Insulation Resistance	> 10 MOhm for signalling circuit					

Environment

Ip Degree Of Protection	IP20 front face conforming to IEC 60529			
Climatic Withstand	conforming to IACS E10 conforming to IEC 60947-1 Annex Q category D			
Protective Treatment	TH conforming to IEC 60068-2-30			
Pollution Degree	3			
Ambient Air Temperature For Operation	-4060 °C 6070 °C with derating			
Ambient Air Temperature For Storage	-6080 °C			
Operating Altitude	03000 m			
Fire Resistance	850 °C conforming to IEC 60695-2-1			
Flame Retardance	V1 conforming to UL 94			
Mechanical Robustness	Vibrations contactor open: 2 Gn, 5300 Hz Vibrations contactor closed: 4 Gn, 5300 Hz Shocks contactor closed: 15 Gn for 11 ms Shocks contactor open: 8 Gn for 11 ms			
Height	85 mm			
Width	90 mm			
Depth	101 mm			
Net Weight	1.117 kg			

Packing Units

Unit Type Of Package 1	
------------------------	--

PCE

Package 1 Height	14.0 cm
Package 1 Width	11.4 cm
Package 1 Length	11.4 cm
Package 1 Weight	1.275 kg
Unit Type Of Package 2	S02
Number Of Units In Package 2	5
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.714 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance




Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Product datasheet

Dimensions Drawings

Dimensions





LC2 or 2 x LC1	а	b	c ⁽¹⁾	e1	e2	G
D09 to D18 (AC)	90	77	86	4	1.5	80
D093 to D123 (AC)	90	99	86	-	-	80
D09 to D18 (DC)	90	77	95	4	1.5	80
D093 to D123 (DC)	90	99	95	-	-	80
D25 to D38 (AC)	90	85	92	9	5	80
D183 to D383 (AC)	90	99	92	-	-	80
D25 to D32 (DC)	90	85	101	9	5	80
D183 to D383 (DC)	90	99	101	-	-	80
e1 and e2: including cabling.						
(1) With safety cover, without add-on block.						

Product datasheet

Connections and Schema

Wiring

