# **Product datasheet**

Specification





# TeSys D reversing contactor - 3P(3 NO) - AC-3 - <= 440 V 40 A - 110 V AC coil

Local distributor code: 393512865

LC2D40AF7

EAN Code: 3389119409490

### Main

IVIAIII	
Range	TeSys TeSys Deca
Product Name	TeSys D TeSys Deca
Product Or Component Type	Reversing contactor
Device Short Name	LC2D
Contactor Application	Resistive load Motor control
Utilisation Category	AC-3 AC-1 AC-3e
Device Presentation	Preassembled with reversing power busbar
Poles Description	3P
Power Pole Contact Composition	3 NO
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC
[le] Rated Operational Current	40 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 60 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 40 A (at <60 °C) at <= 440 V AC AC-3e for power circuit
Motor Power Kw	11 kW at 220230 V AC 5060 Hz 18.5 kW at 380400 V AC 5060 Hz 22 kW at 415 V AC 5060 Hz 22 kW at 440 V AC 5060 Hz 22 kW at 500 V AC 5060 Hz 30 kW at 660690 V AC 5060 Hz
Motor Power Hp (UI / Csa)	5 hp at 230/240 V AC 60 Hz for 1 phase motors 10 hp at 230/240 V AC 60 Hz for 3 phases motors 30 hp at 575/600 V AC 60 Hz for 3 phases motors 10 hp at 200/208 V AC 60 Hz for 3 phases motors 3 hp at 115 V AC 60 Hz for 1 phase motors 30 hp at 460/480 V AC 60 Hz for 3 phases motors
Control Circuit Type	AC at 50/60 Hz
[Uc] Control Circuit Voltage	110 V AC 50/60 Hz
Auxiliary Contact Composition	1 NO + 1 NC
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947
Overvoltage Category	III
[Ith] Conventional Free Air Thermal Current	10 A (at 60 °C) for signalling circuit 60 A (at 60 °C) for power circuit
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 800 A at 440 V for power circuit conforming to IEC 60947

[Icw] Rated Short-Time Withstand Current	800 A at 440 V for power circuit conforming to IEC 60947  72 A 40 °C - 10 min for power circuit
Current	72 A 40 °C - 10 min for power circuit
Current	
	165 A 40 °C - 1 min for power circuit
	320 A 40 °C - 10 s for power circuit
	720 A 40 °C - 1 s for power circuit
	100 A - 1 s for signalling circuit
	120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
	140 A - 100 ms for signaling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
	80 A gG at <= 690 V coordination type 1 for power circuit
	80 A gG at <= 690 V coordination type 2 for power circuit
<u> </u>	1.5 mOhm - Ith 60 A 50 Hz for power circuit
	Power circuit: 690 V conforming to IEC 60947-4-1
I	Power circuit: 600 V CSA certified
I	Power circuit: 600 V UL certified
:	Signalling circuit: 690 V conforming to IEC 60947-1
;	Signalling circuit: 600 V CSA certified
:	Signalling circuit: 600 V UL certified
Electrical Durability	4.5 Marriage 40.4.4.0.2 at the 45-440.1/
	1.5 Mcycles 40 A AC-3 at Ue <= 440 V
	1.4 Mcycles 60 A AC-1 at Ue <= 440 V
	1.5 Mcycles 40 A AC-3e at Ue <= 440 V
Power Dissipation Per Pole	2.4 W AC-3
·	5.4 W AC-1
	2.4 W AC-3e
Front Cover	With
Interlocking Type	Mechanical
Mounting Support	Plate
	Rail
Standards	OOA OOO O N. 44
	CSA C22.2 No 14
	EN 60947-4-1
	EN 60947-5-1
	IEC 60947-4-1
	IEC 60947-5-1
	UL 508
l	IEC 60335-1
Product Certifications	UL
	CSA
	RINA
	GOST
	CCC
	DNV
	LROS (Lloyds register of shipping)
	GL
	BV
	UKCA
Connections - Terminals	Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible without cable end
	Control circuit: screw clamp terminals 2 cable(s) 14 mm²flexible without cable end
	Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible with cable end
	Control circuit: screw clamp terminals 2 cable(s) 12.5 mm²flexible with cable end
	Control circuit: screw clamp terminals 1 cable(s) 14 mm²solid
	Control circuit: screw clamp terminals 2 cable(s) 14 mm²solid
	Power circuit: EverLink BTR screw connectors 1 cable(s) 135 mm²flexible without
	1 Owor Ground Evertain Dirt Screw Connectors I cable(s) 100 min healble without
	cable end
	cable end  Power circuit: Evert ink RTP screw connectors 2 cable(s) 1 25 mm²flevible without
	Power circuit: EverLink BTR screw connectors 2 cable(s) 125 mm²flexible without
	Power circuit: EverLink BTR screw connectors 2 cable(s) 125 mm²flexible without cable end
	Power circuit: EverLink BTR screw connectors 2 cable(s) 125 mm²flexible without cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 135 mm²flexible with
	Power circuit: EverLink BTR screw connectors 2 cable(s) 125 mm²flexible without cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 135 mm²flexible with cable end
	Power circuit: EverLink BTR screw connectors 2 cable(s) 125 mm²flexible without cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 135 mm²flexible with cable end Power circuit: EverLink BTR screw connectors 2 cable(s) 125 mm²flexible with
	Power circuit: EverLink BTR screw connectors 2 cable(s) 125 mm²flexible without cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 135 mm²flexible with cable end Power circuit: EverLink BTR screw connectors 2 cable(s) 125 mm²flexible with cable end
	Power circuit: EverLink BTR screw connectors 2 cable(s) 125 mm²flexible without cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 135 mm²flexible with cable end Power circuit: EverLink BTR screw connectors 2 cable(s) 125 mm²flexible with

Tightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 8 N.m - on EverLink BTR screw connectors - cable 2535 mm² hexagonal screw head 4 mm Power circuit: 5 N.m - on EverLink BTR screw connectors - cable 125 mm² hexagonal screw head 4 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2 Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver pozidriv No 2
Operating Time	419 ms opening 1226 ms closing
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	6 Mcycles
Maximum Operating Rate	3600 cyc/h 60 °C

## Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz 0.81.1 Uc (-4060 °C):operational AC 50 Hz 0.851.1 Uc (-4060 °C):operational AC 60 Hz 11.1 Uc (6070 °C):operational AC 50/60 Hz
Inrush Power In Va	140 VA 60 Hz cos phi 0.75 (at 20 °C) 160 VA 50 Hz cos phi 0.75 (at 20 °C)
Hold-In Power Consumption In Va	13 VA 60 Hz cos phi 0.3 (at 20 °C) 15 VA 50 Hz cos phi 0.3 (at 20 °C)
Heat Dissipation	45 W at 50/60 Hz
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1
Signalling Circuit Frequency	25400 Hz
Minimum Switching Current	5 mA for signalling circuit
Minimum Switching Voltage	17 V for signalling circuit
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact     1.5 ms on energisation between NC and NO contact
Insulation Resistance	> 10 MOhm for signalling circuit

## **Environment**

Ip Degree Of Protection	IP20 front face conforming to IEC 60529
Climatic Withstand	conforming to IACS E10 conforming to IEC 60947-1 Annex Q category D
Protective Treatment	TH conforming to IEC 60068-2-30
Pollution Degree	3
Ambient Air Temperature For Operation	-4060 °C 6070 °C with derating
Ambient Air Temperature For Storage	-6080 °C
Operating Altitude	03000 m
Fire Resistance	850 °C conforming to IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94
Mechanical Robustness	Vibrations contactor open: 2 Gn, 5300 Hz Vibrations contactor closed: 4 Gn, 5300 Hz Shocks contactor open: 10 Gn for 11 ms Shocks contactor closed: 15 Gn for 11 ms

Height	122 mm	
Width	119 mm	
Depth	120 mm	
Net Weight	1.87 kg	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.300 cm
Package 1 Width	16.000 cm
Package 1 Length	19.500 cm
Package 1 Weight	2.088 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	4
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.789 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	32
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	78.312 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance


<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Pro-active China RoHS declaration (out of China RoHS legal scope)  Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

**Dimensions Drawings** 

### **Dimensions**



Connections and Schema

Wiring

