# **Product datasheet**

Specification





### REVERSING CONTACTOR 575VAC 25A IEC

LC2D25U7

Local distributor code: 381823430

EAN Code: 3389110391305

#### Main

mam		
Range	TeSys	
	TeSys Deca	
Product Name	TeSys D	
	TeSys Deca	
Product Or Component Type	Reversing contactor	
Device Short Name	LC2D	
Contactor Application	Motor control	
	Resistive load	
Utilisation Category	AC-1	
	AC-3	
	AC-3e	
Device Presentation	Preassembled with reversing power busbar	
Poles Description	3P	
Power Pole Contact Composition	3 NO	
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz	
	Power circuit: <= 300 V DC	
[le] Rated Operational Current	25 A (at <60 °C) at <= 440 V AC AC-3 for power circuit	
	40 A (at <60 °C) at <= 440 V AC AC-1 for power circuit	
Motor Power Kw	5.5 kW at 220230 V AC 5060 Hz	
	11 kW at 380400 V AC 5060 Hz	
	11 kW at 415 V AC 5060 Hz	
	11 kW at 440 V AC 5060 Hz	
	15 kW at 500 V AC 5060 Hz 15 kW at 660690 V AC 5060 Hz	
Motor Power Hp (UI / Csa)	0 hr -4 000/040 VAO 00 Hz for 4 zh - 2 zavetan	
Motor Fower Hp (Or Csa)	3 hp at 230/240 V AC 60 Hz for 1 phase motors	
	5 hp at 200/208 V AC 60 Hz for 3 phases motors 2 hp at 115 V AC 60 Hz for 1 phase motors	
	7.5 hp at 230/240 V AC 60 Hz for 3 phases motors	
	15 hp at 460/480 V AC 60 Hz for 3 phases motors	
	20 hp at 575/600 V AC 60 Hz for 3 phases motors	
Control Circuit Type	AC at 50/60 Hz	
[Uc] Control Circuit Voltage	240 V AC 50/60 Hz	
Auxiliary Contact Composition	1 NO + 1 NC	
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947	
Overvoltage Category	Ш	
[Ith] Conventional Free Air	10 A (at 60 °C) for signalling circuit	
Thermal Current	40 A (at 60 °C) for power circuit	
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1	
	250 A DC for signalling circuit conforming to IEC 60947-5-1	
	450 A at 440 V for power circuit conforming to IEC 60947	
Rated Breaking Capacity	450 A at 440 V for power circuit conforming to IEC 60947	

[Icw] Rated Short-Time Withstand Current	50 A 40 °C - 10 min for power circuit 120 A 40 °C - 1 min for power circuit 240 A 40 °C - 10 s for power circuit 380 A 40 °C - 1 s for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 63 A gG at <= 690 V coordination type 1 for power circuit 40 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	2 mOhm - Ith 40 A 50 Hz for power circuit
[Ui] Rated Insulation Voltage	Power circuit: 690 V conforming to IEC 60947-4-1 Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified
Electrical Durability	1.65 Mcycles 25 A AC-3 at Ue <= 440 V 1.4 Mcycles 40 A AC-1 at Ue <= 440 V 1.65 Mcycles 25 A AC-3e at Ue <= 440 V
Power Dissipation Per Pole	1.25 W AC-3 3.2 W AC-1 1.25 W AC-3e
Front Cover	With
Interlocking Type	Mechanical
Mounting Support	Rail Plate
Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 IEC 60335-1
Product Certifications	UL CSA RINA GOST CCC DNV LROS (Lloyds register of shipping) GL BV UKCA CB
Connections - Terminals	Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 12.5 mm²flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²solid Control circuit: screw clamp terminals 2 cable(s) 14 mm²solid Power circuit: screw clamp terminals 1 cable(s) 2.510 mm²flexible without cable end Power circuit: screw clamp terminals 2 cable(s) 2.510 mm²flexible without cable end Power circuit: screw clamp terminals 1 cable(s) 110 mm²flexible with cable end Power circuit: screw clamp terminals 2 cable(s) 1.56 mm²flexible with cable end Power circuit: screw clamp terminals 1 cable(s) 1.510 mm²solid Power circuit: screw clamp terminals 2 cable(s) 1.510 mm²solid
Tightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver Philips No 2 Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2 Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver pozidriv No 2
Operating Time	1222 ms closing 419 ms opening

Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical Durability	15 Mcycles
Maximum Operating Rate	3600 cyc/h 60 °C

## Complementary

Coil Technology	Without built-in suppressor module	
Control Circuit Voltage Limits	0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz	
	0.81.1 Uc (-4060 °C):operational AC 50 Hz	
	0.851.1 Uc (-4060 °C):operational AC 60 Hz	
	11.1 Uc (6070 °C):operational AC 50/60 Hz	
Inrush Power In Va	70 VA 60 Hz cos phi 0.75 (at 20 °C)	
	70 VA 50 Hz cos phi 0.75 (at 20 °C)	
Hold-In Power Consumption In Va	7.5 VA 60 Hz cos phi 0.3 (at 20 °C)	
	7 VA 50 Hz cos phi 0.3 (at 20 °C)	
Heat Dissipation	23 W at 50/60 Hz	
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1	
	type mirror contact 1 NC conforming to IEC 60947-4-1	
Signalling Circuit Frequency	25400 Hz	
Minimum Switching Current	5 mA for signalling circuit	
Minimum Switching Voltage	17 V for signalling circuit	
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact	
	1.5 ms on energisation between NC and NO contact	
Insulation Resistance	> 10 MOhm for signalling circuit	

#### **Environment**

IP20 front face conforming to IEC 60529	
conforming to IACS E10 conforming to IEC 60947-1 Annex Q category D	
TH conforming to IEC 60068-2-30	
3	
-4060 °C 6070 °C with derating	
-6080 °C	
03000 m	
850 °C conforming to IEC 60695-2-1	
V1 conforming to UL 94	
Vibrations contactor open: 2 Gn, 5300 Hz Vibrations contactor closed: 4 Gn, 5300 Hz Shocks contactor closed: 15 Gn for 11 ms Shocks contactor open: 8 Gn for 11 ms	
85 mm	
90 mm	
92 mm	
0.787 kg	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.9 cm
Package 1 Width	11.4 cm
Package 1 Length	11.8 cm
Package 1 Weight	815.0 g

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Reach Free Of Svhc



Pvc Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information