Product datasheet

Specification





TeSys D reversing contactor - 3P(3 NO) - AC-3 - <= 440 V 95 A - 110 V AC coil

Local distributor code: 381824604

LC2D95F7

EAN Code: 3389110458268

Main

Mairi					
Range	TeSys				
Product Name	TeSys Deca				
Product Or Component Type	Reversing contactor				
Device Short Name	LC2D				
Contactor Application	Motor control Resistive load				
Utilisation Category	AC-1				
	AC-3				
	AC-3e				
	AC-4				
Device Presentation	Preassembled with reversing power busbar				
Poles Description	3P				
Power Pole Contact Composition	3 NO				
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz				
E. J	Power circuit: <= 300 V DC				
[Io] Pated Operational Current	425 A /24 460 °C\ 24 42 600 \ AC 4 for naving signifit				
[le] Rated Operational Current	125 A (at <60 °C) at <= 690 V AC-1 for power circuit				
	95 A (at <60 °C) at <= 440 V AC-3 for power circuit				
	95 A (at <60 °C) at <= 440 V AC-3e for power circuit				
	66.7 A (at <60 °C) at <= 400 V AC-4 for power circuit				
Motor Power Kw	25 kW at 220230 V AC 50 Hz (AC-3)				
	45 kW at 380400 V AC 50 Hz (AC-3)				
	45 kW at 415440 V AC 50 Hz (AC-3)				
	55 kW at 500 V AC 50 Hz (AC-3)				
	45 kW at 660690 V AC 50 Hz (AC-3)				
	15 kW at 400 V AC 50 Hz (AC-4)				
	25 kW at 220230 V AC 50 Hz (AC-3e)				
	45 kW at 380400 V AC 50 Hz (AC-3e)				
	45 kW at 415440 V AC 50 Hz (AC-3e)				
	55 kW at 500 V AC 50 Hz (AC-3e)				
	45 kW at 660690 V AC 50 Hz (AC-3e)				
Motor Power Hp (UI / Csa)	20 hp at 200/208 V AC 60 Hz for 3 phases motors				
	7.5 hp at 115 V AC 60 Hz for 1 phase motors				
	15 hp at 230/240 V AC 60 Hz for 1 phase motors				
	25 hp at 230/240 V AC 60 Hz for 3 phases motors				
	60 hp at 460/480 V AC 60 Hz for 3 phases motors				
	60 hp at 575/600 V AC 60 Hz for 3 phases motors				
Control Circuit Type	AC at 50/60 Hz				
[Uc] Control Circuit Voltage	110 V AC 50/60 Hz				
Auxiliary Contact Composition	2 NO + 2 NC				
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947				
Overvoltage Category	III				
[Ith] Conventional Free Air	10 A (at 60 °C) for signalling circuit				
Thermal Current	125 A (at 60 °C) for power circuit				

Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1
	250 A DC for signalling circuit conforming to IEC 60947-5-1 1100 A at 440 V for power circuit conforming to IEC 60947
Rated Breaking Capacity	1100 A at 440 V for power circuit conforming to IEC 60947
[Icw] Rated Short-Time Withstand	135 A 40 °C - 10 min for power circuit
Current	400 A 40 °C - 1 min for power circuit
	800 A 40 °C - 10 s for power circuit
	1100 A 40 °C - 1 s for power circuit
	100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit
	140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1
	200 A gG at <= 690 V coordination type 1 for power circuit
	160 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	0.8 mOhm - Ith 125 A 50 Hz for power circuit
[Ui] Rated Insulation Voltage	Power circuit: 1000 V conforming to IEC 60947-4-1
	Signalling circuit: 690 V conforming to IEC 60947-1
	Power circuit: 600 V CSA certified Power circuit: 600 V UL certified
	Signalling circuit: 600 V CSA certified
	Signalling circuit: 600 V UL certified
Electrical Durability	1.2 Mcycles 95 A AC-3
-	1.3 Mcycles 125 A AC-1
	1.2 Mcycles 95 A AC-3e
Power Dissipation Per Pole	12.5 W AC-1
	7.2 W AC-3
	7.2 W AC-3e
Front Cover	With
Interlocking Type	Mechanical
Mounting Support	Rail Plate
Standards	EN/IEC 60947-1
	EN/IEC 60947-4-1
	EN/IEC 60947-5-1
	UL 60947-4-1 UL 60947-5-1
	CSA C22.2 No 60947-4-1
	CSA C22.2 No 60947-5-1
	GB/T 14048.4
Product Certifications	UL
	CSA
	RINA GOST
	CCC
	DNV
	LROS (Lloyds register of shipping)
	GL BV
	UKCA
Connections - Terminals	Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible without cable end
	Control circuit: screw clamp terminals 2 cable(s) 14 mm²flexible without cable end
	Control circuit: screw clamp terminals 2 cable(s) 12.5 mm²flexible with cable end
	Control circuit: screw clamp terminals 1 cable(s) 14 mm²solid Control circuit: screw clamp terminals 2 cable(s) 14 mm²solid
	Control circuit: screw clamp terminals 2 cable(s) 14 mm solid Control circuit: screw clamp terminals 1 cable(s) 12.5 mm²flexible with cable end
	Power circuit: connector 1 cable(s) 450 mm²flexible without cable end
	Power circuit: connector 2 cable(s) 425 mm²flexible without cable end
	Power circuit: connector 1 cable(s) 450 mm²flexible with cable end Power circuit: connector 2 cable(s) 416 mm²flexible with cable end
	Power circuit: connector 2 cable(s) 416 mm ⁻ nexible with cable end Power circuit: connector 1 cable(s) 450 mm ² solid
	Power circuit: connector 2 cable(s) 425 mm²solid
Tightening Torque	Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm
	Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver Philips No 2
	Power circuit: 12 N.m - on connector - with screwdriver flat Ø 6 to Ø 8 mm
	Power circuit: 12 N.m - on connector hexagonal screw head 4 mm Control circuit: 1.2 N.m - on screw clamp terminals - with screwdriver pozidriv No 2
	position position (10 Z

Operating Time	2035 ms closing 620 ms opening				
Safety Reliability Level	B10d = 1.3 Mcycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20 Mcycles contactor with mechanical load conforming to EN/ISO 13849-1				
Mechanical Durability	4 Mcycles				
Maximum Operating Rate	3600 cyc/h 60 °C				

Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz
	0.81.1 Uc (-4055 °C):operational AC 50 Hz
	0.851.1 Uc (-4055 °C):operational AC 60 Hz
	11.1 Uc (5570 °C):operational AC 50/60 Hz
Inrush Power In Va	245 VA 60 Hz cos phi 0.75 (at 20 °C)
	245 VA 50 Hz cos phi 0.75 (at 20 °C)
Hold-In Power Consumption In Va	26 VA 60 Hz cos phi 0.3 (at 20 °C)
	26 VA 50 Hz cos phi 0.3 (at 20 °C)
Heat Dissipation	610 W at 50/60 Hz
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1
	type mirror contact 1 NC conforming to IEC 60947-4-1
Signalling Circuit Frequency	25400 Hz
Minimum Switching Current	5 mA for signalling circuit
Minimum Switching Voltage	17 V for signalling circuit
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact
	1.5 ms on energisation between NC and NO contact
Insulation Resistance	> 10 MOhm for signalling circuit

Environment

Ip Degree Of Protection	Protection IP20 front face conforming to IEC 60529				
Climatic Withstand	conforming to IACS E10				
Protective Treatment	TH conforming to IEC 60068-2-30				
Pollution Degree	3				
Ambient Air Temperature For Operation -4060 °C 6070 °C with derating					
Ambient Air Temperature For Storage	-6080 °C				
Operating Altitude	03000 m				
Fire Resistance	850 °C conforming to IEC 60695-2-1				
Flame Retardance	V1 conforming to UL 94				
Mechanical Robustness	Vibrations contactor open: 2 Gn, 5300 Hz Shocks contactor open: 8 Gn for 11 ms Vibrations contactor closed: 3 Gn, 5300 Hz Shocks contactor closed: 10 Gn for 11 ms				
Height	127 mm				
Width 182 mm					
Depth	158 mm				
Net Weight	3.2 kg				

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.400 cm
Package 1 Width	18.600 cm
Package 1 Length	25.200 cm
Package 1 Weight	3.738 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	2
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	7.963 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
②	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Compliant EU RoHS Declaration				
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)				
Environmental Disclosure	Product Environmental Profile				
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins				
Circularity Profile	No need of specific recycling operations				

Dimensions Drawings

Dimensions



LC2 or 2 x LC1	а	b	С	e1	e2	G	G1
D80 and D95 (AC)	182	127	158	13	_	57	96
c, e1 and e2: including cabling.							

Connections and Schema

Wiring

