# **Product datasheet**

Specification





# TeSys D reversing contactor - 3P(3 NO) - AC-3 - <= 440 V 65 A - 48 V AC coil

Local distributor code: 393514342

LC2D65AE7

EAN Code: 3389119409629

### Main

Mani		
Range	TeSys TeSys Deca	
Product Name	TeSys D TeSys Deca	
Product Or Component Type	Reversing contactor	
Device Short Name	LC2D	
Contactor Application	Resistive load Motor control	
Utilisation Category	AC-1 AC-3 AC-3e	
Device Presentation	Preassembled with reversing power busbar	
Poles Description	3P	
Power Pole Contact Composition	3 NO	
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC 25400 Hz Power circuit: <= 300 V DC	
[le] Rated Operational Current	80 A (at <60 °C) at <= 440 V AC AC-1 for power circuit 65 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 65 A (at <60 °C) at <= 440 V AC AC-3e for power circuit	
Motor Power Kw	18.5 kW at 220230 V AC 50 Hz 30 kW at 380400 V AC 50 Hz 37 kW at 415440 V AC 50 Hz 37 kW at 500 V AC 50 Hz 37 kW at 660690 V AC 50 Hz	
Motor Power Hp (UI / Csa)	40 hp at 460/480 V AC 60 Hz for 3 phases motors 5 hp at 115 V AC 60 Hz for 1 phase motors 10 hp at 230/240 V AC 60 Hz for 1 phase motors 20 hp at 200/208 V AC 60 Hz for 3 phases motors 20 hp at 230/240 V AC 60 Hz for 3 phases motors 50 hp at 575/600 V AC 60 Hz for 3 phases motors	
Control Circuit Type	AC at 50/60 Hz	
[Uc] Control Circuit Voltage 48 V AC 50/60 Hz		
Auxiliary Contact Composition	1 NO + 1 NC	
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947	
Overvoltage Category	III	
[Ith] Conventional Free Air Thermal Current	10 A (at 60 °C) for signalling circuit 80 A (at 60 °C) for power circuit	
Irms Rated Making Capacity	140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 1000 A at 440 V for power circuit conforming to IEC 60947	
Rated Breaking Capacity	1000 A at 440 V for power circuit conforming to IEC 60947	

[Icw] Rated Short-Time Withstand Current	520 A 40 °C - 10 s for power circuit 900 A 40 °C - 1 s for power circuit 110 A 40 °C - 10 min for power circuit 260 A 40 °C - 1 min for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Associated Fuse Rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 125 A gG at <= 690 V coordination type 1 for power circuit 125 A gG at <= 690 V coordination type 2 for power circuit
Average Impedance	1.5 mOhm - Ith 80 A 50 Hz for power circuit
[Ui] Rated Insulation Voltage	Power circuit: 690 V conforming to IEC 60947-4-1 Power circuit: 600 V CSA certified Power circuit: 600 V UL certified Signalling circuit: 690 V conforming to IEC 60947-1 Signalling circuit: 600 V CSA certified Signalling circuit: 600 V UL certified
Electrical Durability	1.45 Mcycles 65 A AC-3 at Ue <= 440 V 1.4 Mcycles 80 A AC-1 at Ue <= 440 V 1.45 Mcycles 65 A AC-3e at Ue <= 440 V
Power Dissipation Per Pole	9.6 W AC-1 6.3 W AC-3 6.3 W AC-3e
Front Cover	With
Interlocking Type	Mechanical
Mounting Support	Plate Rail
Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 IEC 60335-1
Product Certifications	UL CSA RINA GOST CCC DNV LROS (Lloyds register of shipping) GL BV UKCA
Connections - Terminals	Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 2 cable(s) 14 mm²flexible without cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²flexible with cable end Control circuit: screw clamp terminals 2 cable(s) 12.5 mm²flexible with cable end Control circuit: screw clamp terminals 1 cable(s) 14 mm²solid Control circuit: screw clamp terminals 2 cable(s) 14 mm²solid Power circuit: EverLink BTR screw connectors 1 cable(s) 135 mm²flexible without cable end Power circuit: EverLink BTR screw connectors 2 cable(s) 125 mm²flexible without cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 135 mm²flexible with cable end Power circuit: EverLink BTR screw connectors 2 cable(s) 125 mm²flexible with cable end Power circuit: EverLink BTR screw connectors 2 cable(s) 125 mm²flexible with cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 135 mm²flexible with cable end Power circuit: EverLink BTR screw connectors 1 cable(s) 135 mm²solid Power circuit: EverLink BTR screw connectors 2 cable(s) 125 mm²solid
Tightening Torque	Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit: 8 N.m - on EverLink BTR screw connectors - cable 2535 mm² hexagonal screw head 4 mm Power circuit: 5 N.m - on EverLink BTR screw connectors - cable 125 mm² hexagonal screw head 4 mm Control circuit: 1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2 Power circuit: 2.5 N.m - on screw clamp terminals - with screwdriver pozidriv No 2

Operating Time	419 ms opening 1226 ms closing	
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1	
Mechanical Durability	6 Mcycles	
Maximum Operating Rate	3600 cyc/h 60 °C	

## Complementary

Coil Technology	Without built-in suppressor module	
Control Circuit Voltage Limits	0.30.6 Uc (-4070 °C):drop-out AC 50/60 Hz 0.81.1 Uc (-4060 °C):operational AC 50 Hz 0.851.1 Uc (-4060 °C):operational AC 60 Hz 11.1 Uc (6070 °C):operational AC 50/60 Hz	
Inrush Power In Va	140 VA 60 Hz cos phi 0.75 (at 20 °C) 160 VA 50 Hz cos phi 0.75 (at 20 °C)	
Hold-In Power Consumption In Va	13 VA 60 Hz cos phi 0.3 (at 20 °C) 15 VA 50 Hz cos phi 0.3 (at 20 °C)	
Heat Dissipation	45 W at 50/60 Hz	
Auxiliary Contacts Type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1	
Signalling Circuit Frequency	25400 Hz	
Minimum Switching Current	5 mA for signalling circuit	
Minimum Switching Voltage	17 V for signalling circuit	
Non-Overlap Time	1.5 ms on de-energisation between NC and NO contact     1.5 ms on energisation between NC and NO contact	
Insulation Resistance	> 10 MOhm for signalling circuit	

## **Environment**

Ip Degree Of Protection	IP20 front face conforming to IEC 60529	
Climatic Withstand	conforming to IACS E10 conforming to IEC 60947-1 Annex Q category D	
Protective Treatment	TH conforming to IEC 60068-2-30	
Pollution Degree	3	
Ambient Air Temperature For Operation	-4060 °C 6070 °C with derating	
Ambient Air Temperature For Storage	nperature For -6080 °C	
Operating Altitude	03000 m	
Fire Resistance	850 °C conforming to IEC 60695-2-1	
Flame Retardance	V1 conforming to UL 94	
Wechanical Robustness  Vibrations contactor open: 2 Gn, 5300 Hz  Vibrations contactor closed: 4 Gn, 5300 Hz  Shocks contactor open: 10 Gn for 11 ms  Shocks contactor closed: 15 Gn for 11 ms		
Height	122 mm	
Width	119 mm	
Depth	120 mm	
Net Weight	1.89 kg	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.000 cm
Package 1 Width	16.500 cm
Package 1 Length	19.500 cm
Package 1 Weight	2.084 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	4
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.795 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance


<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Pvc Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

## **Dimensions Drawings**

### **Dimensions**



Connections and Schema

Wiring

