

Product datasheet

Specifications



reversing contactor TeSys LC2-D - 3 poles - AC-3 440V 95 A - coil 24 V AC

LC2D95B5

EAN Code: 3389110458114

ⓘ Discontinued

Main

Range Of Product	TeSys D
Product Or Component Type	Reversing contactor
Device Short Name	LC2D
Contactor Application	Motor control
Utilisation Category	AC-2 AC-4 AC-3
Control Circuit Type	AC
Coil Type	Standard
Poles Description	3P
Pole Contact Composition	3 NO

Complementary

Assembly Style	Ready assembled
Coil Technology	Without built-in bidirectional peak limiting diode suppressor
Protective Cover	With
Auxiliary Contact Composition	1 NO + 1 NC
Interlocking Type	Mechanical
Overvoltage Category	III
Mounting Support	Rail Plate
Associated Fuse Rating	10 A gG for control circuit conforming to IEC 60947-5-1
Mechanical Durability	4000000 cycles 10000000 cycles
Height	140 mm
Width	182 mm
Depth	158 mm
Net Weight	3.2 kg

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	EN 60947-4-1 IEC 60947-5-1 CSA C22.2 No 14 UL 508 EN 60947-5-1 IEC 60947-4-1
Product Certifications	RINA DNV CCC GL GOST BV LROS (Lloyds register of shipping)
Ambient Air Temperature For Operation	-5...60 °C
Ambient Air Temperature For Storage	-60...80 °C

Contractual warranty

Warranty	18 months
----------	-----------