# **Product datasheet**

Specifications





Compact NSXm-switch disconnector- 50A 4P - 1.28(Icm) 0.9(Icw) - compression lug

LV426660

() Discontinued on: 30 Jun 2023

Important message: This product has been switched to new ComPacT range and is no longer commercialized. EAN Code: 3606481176554

#### Main

Range	ComPact
Product Name	ComPact NSXm
Product Or Component Type	Switch disconnector
Device Application	Distribution

### Complementary

complementary	
[In] Rated Current	50 A
Poles Description	4P
Neutral Position	Left
Control Type	Toggle
Mounting Mode	Clip-on (35 mm symmetrical DIN rail) By screws (plate)
Network Type	AC
Network Frequency	50/60 Hz
[le] Rated Operational Current	50 A - utilisation category AC-23 AC 50/60 Hz 50 A - utilisation category AC-22 AC 50/60 Hz
[Ui] Rated Insulation Voltage	800 V conforming to IEC 60947-2
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz conforming to IEC 60947-2
[Icw] Rated Short-Time Withstand Current	0.9 kA during 3 s conforming to IEC 60947-3
[Icm] Rated Short-Circuit Making Capacity	1.28 kA
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
Suitability For Isolation	Yes conforming to IEC 60947-2
Utilisation Category	Category A
Mechanical Durability	20000 cycles conforming to IEC 947-1 Annex K ed 5.2 In
Electrical Durability	10000 cycles conforming to IEC 947-1 Annex F ed 5.2 for In at 440 V
Contact Position Indicator	Yes
Connection Pitch	27 mm 35 mm with spreaders
Local Signalling	Flag (green) for presence of auxiliary contacts
Toggle Padlocking (With Accessories)	Padlock in OFF or ON position

Connections - Terminals	compression lug/busbar
Tightening Torque	5 N.m for 2.510 mm <sup>2</sup> 9 N.m for 1695 mm <sup>2</sup>
Thread Type	M6
Number Of Slots	1 slot(s) for auxiliary switch OF (plug-in) 1 slot(s) for alarm switch SD (plug-in) 1 slot(s) for voltage release MN or MX (plug-in)
Thickness	8 mm
Power Wire Stripping Length	20 mm
Quality Labels	CE
Standards	EN/IEC 60947
Colour	Grey (RAL 7016)
Operating Altitude	2000 m without derating 5000 m with derating
9 Mm Pitches	12
Height	137 mm
Width	108 mm
Depth	80 mm
Net Weight	1.42 kg
Quantity Per Set	Set of 1

# Environment

Product Certifications	CCC EAC Marine
Ip Degree Of Protection	Front face: IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Pollution Degree	3 conforming to IEC 60947-1
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-5085 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.5 cm
Package 1 Width	11.7 cm
Package 1 Length	22 cm
Package 1 Weight	1.6 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	6
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	10.19 kg

Unit Type Of Package 3	P12
Number Of Units In Package 3	144
Package 3 Height	110 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	254.49 kg

## **Contractual warranty**

Warranty

18 months

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

### Well-being performance

Mercury Free

Rohs Exemption Information Yes

### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins