Product datasheet

Specification





Advanced control unit, TeSys U, 1.25-5A, 3P motors, protection & diagnostic, class 10, coil 110-240V AC/DC

Local distributor code:

387988793 LUCB05FU

EAN Code: 3389110364262

Main

| IVIAIII | |
|--------------------------------------|---|
| Range | TeSys |
| Range Of Product | TeSys Ultra |
| Product Name | TeSys Ultra |
| Device Short Name | LUCB |
| Product Or Component Type | Advanced control unit |
| Device Application | Motor control Motor protection |
| Product Specific Application | Basic protection and advanced functions, communication |
| Main Function Available | Protection against overload and short-circuit Earth fault protection Protection against phase failure and phase imbalance Manual reset |
| Product Compatibility | Power base LUB12 Power base LUB32 Power base LUB38 Power base LUB120 Power base LUB320 Power base LUB380 Reversing contactor breaker LU2B12FU Reversing contactor breaker LU2B32FU Reversing contactor breaker LU2B38FU |
| [Ue] Rated Operational Voltage | 690 V AC |
| Network Frequency | 4060 Hz |
| Load Type | 3-phase motor - cooling: self-cooled |
| Utilisation Category | AC-41 AC-44 AC-43 |
| Motor Power Kw | 1.5 kW at 400440 V AC 50/60 Hz 2.2 kW at 500 V AC 50/60 Hz 3 kW at 690 V AC 50/60 Hz |
| Rated Motor Current Adjustment Range | 1.255 A |
| Thermal Overload Class | Class 10 - frequency limit: 4060 Hz - temperature compensation: -2570 °C conforming to IEC 60947-6-2 Class 10 - frequency limit: 4060 Hz - temperature compensation: -2570 °C conforming to UL 508 |
| Tripping Threshold | 14.2 x lr +/- 20 % |
| Phase Failure Sensitivity | Yes |
| [Uc] Control Circuit Voltage | 110240 V AC 110220 V DC |



Complementary

Ambient Air Temperature For Storage

| 88264 V for AC circuit 110240 V in operation |
|---|
| 88242 V for DC circuit 110240 V in operation |
| 55 V for AC circuit 110240 V drop-out |
| 55 V for DC circuit 110220 V drop-out |
| 280 mA at 110240 V AC I maximum while closing with LUB12 |
| 280 mA at 110240 V AC I maximum while closing with LUB32 |
| 280 mA at 110240 V AC I maximum while closing with LUB38 |
| 280 mA at 110220 V DC I maximum while closing with LUB12 280 mA at 110220 V DC I maximum while closing with LUB32 |
| 280 mA at 110220 V DC I maximum while closing with LUB38 |
| 35 mA at 110240 V AC I rms sealed with LUB12 |
| 25 mA at 110240 V AC I rms sealed with LUB32 |
| 25 mA at 110240 V AC I rms sealed with LUB38 |
| 35 mA at 110220 V DC I rms sealed with LUB12 25 mA at 110220 V DC I rms sealed with LUB32 |
| 25 mA at 110220 V DC I rms sealed with LUB38 |
| 2 W for control circuit with LUB12 |
| 3 W for control circuit with LUB32 |
| 3 W for control circuit with LUB38 |
| 35 ms opening with LUB12 for control circuit |
| 35 ms opening with LUB32 for control circuit 35 ms opening with LUB38 for control circuit |
| 50 ms closing with LUB38 for control circuit |
| 50 ms closing with LUB32 for control circuit |
| 50 ms closing with LUB38 for control circuit |
| Manual reset |
| EN 60947-6-2 |
| IEC 60947-6-2 |
| UL 60947-4-1, with phase barrier CSA C22.2 No 60947-4-1, with phase barrier |
| CE |
| UL |
| CSA |
| CCC |
| EAC ASEFA |
| ATEX |
| Marine |
| 690 V conforming to IEC 60947-6-2 |
| 600 V conforming to UL 60947-4-1 |
| 600 V conforming to CSA C22.2 No 60947-4-1 |
| 6 kV conforming to IEC 60947-6-2 |
| 400 V SELV between the control and auxiliary circuits conforming to IEC 60947-1 |
| 400 V SELV between the control or auxiliary circuit and the main circuit conforming to |
| IEC 60947-1 |
| Plug-in (front face) |
| 45 mm |
| 66 mm |
| 60 mm |
| LUCB |
| |
| |
| IP20 front panel and wired terminals conforming to IEC 60947-1 |
| IP20 other faces conforming to IEC 60947-1 IP40 front panel outside connection zone conforming to IEC 60947-1 |
| |
| TH conforming to IEC 60068 |
| TH conforming to IEC 60068 -2570 °C |
| |

-40...85 °C

| Operating Altitude | 2000 m |
|--|--|
| Fire Resistance | 960 °C parts supporting live components conforming to IEC 60695-2-12 650 °C conforming to IEC 60695-2-12 |
| Shock Resistance | 10 gn power poles open conforming to IEC 60068-2-27 15 gn power poles closed conforming to IEC 60068-2-27 |
| Vibration Resistance | 2 gn, 5300 Hz, power poles open conforming to IEC 60068-2-6 4 gn, 5300 Hz, power poles closed conforming to IEC 60068-2-6 |
| Resistance To Electrostatic Discharge | 8 kV level 3 in open air conforming to IEC 61000-4-2 8 kV level 4 on contact conforming to IEC 61000-4-2 |
| Non-Dissipating Shock Wave | 1 kV serial mode conforming to IEC 60947-6-2 2 kV common mode conforming to IEC 60947-6-2 |
| Resistance To Radiated Fields | 10 V/m 3 conforming to IEC 61000-4-3 |
| Resistance To Fast Transients | 2 kV class 3 serial link conforming to IEC 61000-4-4 4 kV class 4 all circuits except for serial link conforming to IEC 61000-4-4 |
| Immunity To Radioelectric Fields | 10 V conforming to IEC 61000-4-6 |
| Immunity To Microbreaks | 3 ms |
| Immunity To Voltage Dips | 70 % / 500 ms conforming to IEC 61000-4-11 |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|----------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.0 cm |
| Package 1 Width | 8.1 cm |
| Package 1 Length | 8.7 cm |
| Package 1 Weight | 116.0 g |
| Unit Type Of Package 2 | S02 |
| Number Of Units In Package 2 | 23 |
| Package 2 Height | 15.0 cm |
| Package 2 Width | 30.0 cm |
| Package 2 Length | 40.0 cm |
| Package 2 Weight | 2.986 kg |

Contractual warranty

Warranty 18 months

Sustainability Screen Premium*

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| Ø | Mercury Free |
|----------|------------------------------------|
| ⊘ | Rohs Exemption Information Yes |
| Ø | Pvc Free |
| ⊘ | Halogen Free Plastic Parts Product |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |