



## Main

Device short name	MX
Product or component type	Voltage release
Device application	Control
Range compatibility	Compact NSX EasyPact CVS PowerPact Multistandard
Voltage release type	Shunt trip release
[Uc] control circuit voltage	380...415 V AC 50 Hz 440...480 V AC 60 Hz

## Complementary

Control signal type	Maintained Impulse
Impulse duration	$\geq 20$ ms
Threshold tripping voltage	$0.7 \dots 1.1 \times U_n$ opening
Supply inrush power	10 VA
Mounting mode	Fixed
Response time	50 ms
Auxiliary connection terminal	Screw terminal $0 \dots 1.5 \text{ mm}^2$

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	Yes

China RoHS Regulation	<a href="#">Download RoHS China Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------