Product datasheet

Specifications





TeSys D - contactor coil - LX1D8 -415 V AC 50/60 Hz for 115 & 150

A contactor Local distributor code:

386424931

LX1D8N7

EAN Code: 3389118355255

Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX1D8
Control Circuit Type	AC at 50/60 Hz
[Uc] Control Circuit Voltage	415 V AC 50/60 Hz
Average Resistance	21011 Ohm at 20 °C
Inductance Of Closed Circuit	482.42 H
Product Compatibility	LC1D115 LC1D150
Mechanical Durability	8 Mcycles
Maximum Operating Rate	1200 cyc/h 60 °C

Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Drop-out: 0.30.5 Uc at 50/60 Hz (at <55 °C) Operational: 0.81.15 Uc at 50/60 Hz (at <55 °C)
Inrush Power In Va	280350 VA 60 Hz cos phi 0.9 (at 20 °C) 280350 VA 50 Hz cos phi 0.9 (at 20 °C)
Hold-In Power Consumption In Va	218 VA 60 Hz cos phi 0.9 (at 20 °C) 218 VA 50 Hz cos phi 0.9 (at 20 °C)
Heat Dissipation	34.5 W at 50/60 Hz

Environment

Ambient Air Temperature For -5...60 °C Operation

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	11.5 cm
Package 1 Length	17.0 cm
Package 1 Weight	290.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	20

Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.285 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations