

Product datasheet

Specifications



TeSys F - contactor coil - LX4FL - 110 V DC

Local distributor code:
380914586

LX4FL110

⚠ Discontinued on: 29 Sept 2023

EAN Code: 3389110083729

⚠ To be discontinued

Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX4FL
Range Compatibility	TeSys TeSys F LC1F contactor
Product Compatibility	LC1F1250 LC1F630
Control Circuit Type	DC low consumption
[Uc] Control Circuit Voltage	110 V DC
Inductance Of Closed Circuit	180 H
Average Resistance	8.1 Ohm inrush at 20 °C 1680 Ohm holding at 20 °C
Operating Time	40...50 ms opening 60...70 ms closing
Mechanical Durability	5 Mcycles
Maximum Operating Rate	1200 cyc/h 55 °C

Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Drop-out: 0.2...0.35 Uc (at 55 °C) Operational: 0.85...1.1 Uc (at 55 °C)
Inrush Power In W	1600 W (at 20 °C)
Hold-In Power Consumption In W	9 W at 20 °C

Environment

Ambient Air Temperature For Operation	-5...55 °C
Net Weight	1.45 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.500 cm
Package 1 Width	13.000 cm
Package 1 Length	23.300 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	1.467 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	6
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	9.229 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration	