Product datasheet

Specifications

 → Green Premium[™]



Insulating mounting plate, thickness 25 mm, For boxes of H175W150 mm

Local distributor code: 387529107

NSYAMPA1916TB

EAN Code: 3606480166129

Main

Range	Thalassa
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	-
Mounting Location	Back studs
Mounting Plate Description	Insulating
Range Compatibility	Thalassa Thalassa TBS Thalassa Thalassa TBP
Device Composition	1 mounting plate
Material	Polyester
Colour	Grey

Complementary

Fixing Mode	By screws - screw type M4 self tapping - on back studs location
Height	192 mm nominal: 140 mm real:
Width	164 mm nominal: 1685 mm real:
Thickness	3 mm
Net Weight	0.1 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.3 cm
Package 1 Width	14.0 cm
Package 1 Length	16.9 cm
Package 1 Weight	100.0 g

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations