# **Product datasheet**

Specifications





# Insulating mounting plate, thickness 25 mm, For boxes of H275W225 mm

Local distributor code: 387529123

NSYAMPA2924TB

EAN Code: 3606480166143

#### Main

Range	Thalassa	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Mounting plate	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	-	
Mounting Location	Back studs	
Mounting Plate Description	Insulating	
Range Compatibility	Thalassa Thalassa TBS Thalassa Thalassa TBP	
Device Composition	1 mounting plate	
Material	Polyester	
Colour	Grey	

### Complementary

Fixing Mode	By screws - screw type M4 self tapping - on back studs location
Height	291 mm nominal: 215 mm real:
Width	241 mm nominal: 265 mm real:
Thickness	3 mm
Net Weight	0.26 kg

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.3 cm
Package 1 Width	25.0 cm
Package 1 Length	30.0 cm
Package 1 Weight	260.0 g

#### **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations