


Product datasheet

Specifications



TeSys F - specific contactor coil - 48 V AC 40...400 Hz low consumption

Local distributor code:
402992716

LX9FF048

⚠ Discontinued on: 29 Sept 2023

EAN Code: 3389110083927

⚠ To be discontinued

Main

Range	TeSys
Product Or Component Type	Specific contactor coil
Device Short Name	LX9FF
Range Compatibility	TeSys TeSys F LC1F contactor
Product Compatibility	LC1F150 LC1F115
Control Circuit Type	AC at 40...400 Hz low consumption
[Uc] Control Circuit Voltage	48 V AC 40...400 Hz
Inductance Of Closed Circuit	0.3 H
Average Resistance	3.03 Ohm inrush at 20 °C 80.2 Ohm holding at 20 °C
Operating Time	130 ms opening 35 ms closing
Mechanical Durability	10 Mcycles
Maximum Operating Rate	2400 cyc/h 55 °C

Complementary

Coil Technology	Without built-in suppressor module
Control Circuit Voltage Limits	Operational: 0.85...1.1 Uc (at 55 °C) Drop-out: 0.2...0.55 Uc (at 55 °C)
Inrush Power In Va	690...855 VA 40...400 Hz (at 20 °C)
Hold-In Power Consumption In Va	6.6...8.1 VA 40...400 Hz (at 20 °C)
Heat Dissipation	5.9...7.2 W

Environment

Ambient Air Temperature For Operation	-5...55 °C
Net Weight	0.43 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	8.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	16 cm
Package 1 Weight	539 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	14
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	7.986 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation		China RoHS declaration