Product datasheet

Specifications

Ğreen Premium™



Spacial SF brush flexible cable entry gaskets - 25 mm - 1000 mm enclosure

Local distributor code: 22145053

NSYBCE10

EAN Code: 3606485130002

Main

Range	Spacial
Product Or Component Type	Brush gasket
Accessory / Separate Part Category	Cable management accessory
Device Application	Multi-purpose
Range Compatibility	Spacial Spacial SF suitable enclosure
Device Composition	2 gasket
Quantity Per Set	Set of 1

Complementary

Mounting Support	Cable gland plate	
Cable Entry	1 or 2 entries	
Fixing Mode	Clipped	
Height	40 mm	
Width	Nominal: 1000 mm Real: 855 mm	
Depth	25 mm	

Packing Units

.	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.0 cm
Package 1 Width	8.0 cm
Package 1 Length	96.0 cm
Package 1 Weight	506.0 g
Unit Type Of Package 2	РАМ
Number Of Units In Package 2	80
Package 2 Height	85.0 cm
Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	53.0 kg

Logistical informations

Country	Of	Origin	
---------	----	--------	--

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	No need of specific recycling operations	