Product datasheet

Specification





ClimaSys CC - thermostat 250V - range of temperature +5...60°C - 1 NO/NC - °C

Local distributor code: 388826922

NSYCCOTHI

EAN Code: 3606480152559

Main

Range	ClimaSys
Product Name	ClimaSys CC
Product Or Component Type	Thermostat
Temperature Setting Range	560 °C
Information Displayed	Temperature in °C

Complementary

Complementary	
Input Voltage	250 V
Sensor Type	Bimetal
Contacts Type And Composition	1 NO/NC
Contact Resistance	10 mOhm
Service Life In Cycles	100000 cycles
Maximum Switching Capacity	4 A 250 V AC inductive pf: 0.6 30 W DC 10 A 250 V AC inductive
Electrical Connection	4 terminals, clamping capacity: 2.5 mm ²
Mounting Mode	Clipped
Height	68 mm external:
Width	56 mm external:
Depth	44 mm external:
Net Weight	100 g
Mounting Location	Cross rails On mounting plate 35 mm DIN rail Spacial upright
Ambient Air Temperature For Operation	-2080 °C
Ip Degree Of Protection	IP20
Hysteresis	7 K +/- 0.4K
Number Of Outputs	1 heating function 1 ventilation function
Material	PC
Colour	Light grey
Flame Retardance	Self-extinguishing conforming to UL94 (material V0)
Product Certifications	UL

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	5.5 cm
Package 1 Length	7 cm
Package 1 Weight	80 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	75
Package 2 Height	26 cm
Package 2 Width	41.5 cm
Package 2 Length	32.5 cm
Package 2 Weight	7.428 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	3000
Package 3 Height	198 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	311 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations