Product datasheet





ClimaSys Exchanger air-water 1750W sides of enclosure

Local distributor code:

402653932 NSYCEW1K8

EAN Code: 3606480620713

Main

Range	ClimaSys
Product Name	ClimaSys CE
Product Or Component Type	Air-water exchanger
Mounting Type	Sides of enclosure
Cooling Power	1750 W

Complementary

Pressure	5 bar for water
Pressure Drop	0.1 bar
Water Flow	Internal circuit: 150 l/h
Flow Rate	External circuit: 570 m3/h
Control Type	Thermostat
Temperature Setting Range	2046 °C
Ambient Air Temperature For Operation	170 °C outside the enclosure: 2060 °C inside the enclosure:
Controlled Fluid	Water
Fluid Connection Type	G 1/2 (female)
Input Voltage	230 V 50/60 Hz
[In] Rated Current	0.36 A
Power Consumption In W	75 W
Height	901 mm external:
Width	398 mm external:
Depth	137 mm external:
Net Weight	18 kg
Noise Level	58 dB conforming to EN/ISO 3746
Protection Type	Thermal protection: T 2 A
Material	Steel
Colour	Grey (RAL 7035)

Environment

Ip Degree Of Protection IP55 conforming to IEC 60529 (on the internal circuit) IP55 conforming to IEC 60529 (on the external circuit)

Life Is On Schneider 6 May 2024

Product Certifications	CE
Directives	2006/95/EC - low voltage directive 2004/108/EC - electromagnetic compatibility 2006/42/EC - machinery
Standards	EN 60335-2-40 EN 60204-1 EN/ISO 12100 EN 60335-1

Packing Units

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.7 cm
Package 1 Width	39.8 cm
Package 1 Length	90.1 cm
Package 1 Weight	18.0 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	7
Package 2 Height	116.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	167.0 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information